






PLATING CONTACT AREA:		ERICSSON P/N
DASH NR:	PERFORMANCE LEVEL	SEE NOTE 7
-1YYLF	CUSTOMER SPECIAL	
-7YYLF	CUSTOMER SPECIAL	RNV 604 1111/1

DASH NR	CONFIGURATION						PCB THICKN.	DIM A	DIM B	DIM C	DIM D	
		COLUMN #										
	ROW #	6	5	4	3	2						1
-X01LF	D	+	+	+	+	+	+	2.4	14.14	3.50	0.54	17.64
	C	+	+	+	+	+	+					
	B	+	+	+	+	+	+					
	A	+	+	+	+	+	+					
"+" POSITION LOADED												



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

- NOTES:
1. BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
 2. TERMINAL MATERIAL: PHOSPHOR BRONZE.
 3. PLATING SOLDER TAILS 2-8 μ m
PURE Sn FOR LEAD FREE.
 4. LOAD IN THIS DIRECTION (E.G. THROUGH CODING) 30 NEWTON MAXIMUM PER CONNECTOR.
 5. LOAD IN THIS DIRECTION 15 NEWTON MAXIMUM PER CONNECTOR.
 6. TO ENSURE PROPER ALIGNMENT OF MULTIPLE MODULES ON A BOARD THE USE OF A FIXTURE IS RECOMMENDED.
 7. PRODUCT MARKING: ERICSSON PARTNUMBER & BATCH I.D.
 8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 9. THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

mat'l. code	tolerances unless otherwise specified	CUSTOMER COPY	projection	title
lit. ech. no. d. r. date				
A. H80210 [PHE] 980403	linear			STR SIGN RCP
B. H80380 [PHE] 980816				STB + WAFER 12mm
C. 0001-0101 [Glu] 041228	origines			product family METRAL (cm)
D. 0001-0001 [Glu] 041228	origines			code
E. 0009-0171 [TER] 0410/08 [eng] W. van Aalst	980403			size dvg no
F. 0010-0001 [Glu] 0410/08 [eng] W. van Aalst	980403			213
sheet index	revision	scale	size	sheet
1	F	1:1	A1	1 of 1