


Unimate Range – Pitch 5.08

Pin headers


PCB connection			
 Solder connection Double level connection offset		SLA 90 250 V / 17.5 A 	G.2
		SLA 180 250 V / 17.5 A 	G.3
		SLAD 90 250 V / 9.5 A 	G.4
		SLAD 180 250 V / 9.5 A 	G.5
PCB connection			
 Clamping yoke connection for rail mounting		SLAS 250 V / 16 A 2.5 mm ² / AWG 12 	G.6
		SLAS ... mit RF15 250 V / 16 A 2.5 mm ² / AWG 12 	G.8

Socket connectors

Cable connection			
 Clamping yoke connection		BLA 250 V / 17,5 A 2.5 mm ² / AWG 12 	G.10
	 TOP clamp connection	BLAT 250 V / 15 A 2.5 mm ² / AWG 14 	G.12
	 Crimp connection	BLAC 250 V / 17,5 A 2.5 mm ² / AWG 14 	G.14




With the most frequently used pcb's worldwide being single layer 1.6 mm (0.062 inch) and 2.0 mm (0.079 inch) thick, the solder pin length of pcb terminals and connectors needs to be at least 3.2 mm (0.126 inch) long in order to provide problem-free soldering.

SLA 90
SLA 180

- 250 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 10 A (UL)

SLA 90



G

Rated data acc. to IEC 664-1 / VDE 0110 (4.97)				
Clamping range, max.	mm ²			
Solid H05(07) V-U	mm ²			
Stranded H07 V-R	mm ²			
Flexible H05(07) V-K	mm ²			
Flexible with ferrule	mm ²			
Ferrule with plastic collar	mm ²			
Stripping length	mm			
Rated current			20°C	40°C
at ambient temperature		A	17.5	15.0
Overvoltage category			III	III
Pollution severity			3	2
Rated voltage	V		250	320
Rated impulse voltage	kV		4.0	4.0
UL 1059 rated data - E60693			B	C
Rated voltage	V		300	300
Rated current	A		10.0	10.0
AWG conductor				
CSA C22.2 rated data - LR12400 B			B	C
Rated voltage	V		300	300
Rated current	A		10.0	10.0
AWG conductor				
Material data				
Type of insulating material			PBT GF	
Flammability class acc. UL94			V-0	
Contact base material			CuSn	
Contact plating			tin plated	
Information				

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current refers to rated cross-section and min. number of poles
- Drawing information P = Pitch


[illegible]

Pitch 5.08 mm				
Poles	L1 mm	(inch)	Qty.	Order no.
2	5.08	(0.200)	100	1238060000
3	10.16	(0.400)	100	1238160000
4	15.24	(0.600)	100	1238260000
5	20.32	(0.800)	50	1238360000
6	25.40	(1.000)	50	1238460000
7	30.48	(1.200)	50	1238560000
8	35.56	(1.400)	50	1238660000
9	40.64	(1.600)	50	1238760000
10	45.72	(1.800)	50	1238860000
11	50.80	(2.000)	50	1238960000
12	55.88	(2.200)	50	1239060000
13	60.96	(2.400)	50	1239160000
14	66.04	(2.600)	50	1239260000
15	71.12	(2.800)	50	1239360000
16	76.20	(3.000)	50	1239460000
17	81.28	(3.200)	20	1271760000
18	86.36	(3.400)	20	1271860000
19	91.44	(3.600)	20	1271960000
20	96.52	(3.800)	20	1272060000
21	101.60	(4.000)	20	1272160000
22	106.68	(4.200)	20	1315960000
23	111.76	(4.400)	20	1316060000
24	116.84	(4.600)	20	1316160000

Status indicator see page L.17

**Unimate Range
Pitch 5.08**

SLA 180B



Ordering data

Solder pin length	3.2 mm
Colour	orange

[illegible]


Pitch 5.08 mm				
Poles	L1 mm	(inch)	Qty.	Order no.
2	5.08	(0.200)	100	1242560000
3	10.16	(0.400)	100	1242660000
4	15.24	(0.600)	100	1242760000
5	20.32	(0.800)	50	1242860000
6	25.40	(1.000)	50	1242960000
7	30.48	(1.200)	50	1243060000
8	35.56	(1.400)	50	1243160000
9	40.64	(1.600)	50	1243260000
10	45.72	(1.800)	50	1243360000
11	50.80	(2.000)	50	1243460000
12	55.88	(2.200)	50	1243560000
13	60.96	(2.400)	50	1243660000
14	66.04	(2.600)	50	1243760000
15	71.12	(2.800)	50	1243860000
16	76.20	(3.000)	50	1243960000
17	81.28	(3.200)	20	1270760000
18	86.36	(3.400)	20	1270860000
19	91.44	(3.600)	20	1270960000
20	96.52	(3.800)	20	1271060000
21	101.60	(4.000)	20	1271160000
22	106.68	(4.200)	20	1315360000
23	111.76	(4.400)	20	1315460000
24	116.84	(4.600)	20	1315560000

24	110.04 (1000)	20		1010000000
----	---------------	----	--	------------

G.3



Solder connection pin headers

SLAD 90
SLAD 180




- 250 V (IEC) / 300 V (UL)
- 9.5 A (IEC) / 10 A (UL)

SLAD 90



SLAD 90B



Technical data

Rated data acc. to IEC 664-1 / VDE 0110 (4.97)

Clamping range, max.	mm ²
Solid H05(07) V-U	mm ²
Stranded H07 V-R	mm ²
Flexible H05(07) V-K	mm ²
Flexible with ferrule	mm ²
Ferrule with plastic collar	mm ²
Stripping length	mm

**Rated current
at ambient temperature**

Transition temperature	A	9.5	8.0
------------------------	---	-----	-----

Overvoltage category

Pollution severity	3	2	2
--------------------	---	---	---

Rated voltage

Rated voltage	V	250	325	400
Rated impulse voltage	kV	4.0	4.0	4.0

UL 1059 rated data - E60693

Bated voltage	V	300	300
---------------	---	-----	-----

Rated current

AWG conductor

CSA C22.2 rated data - LR12400 B

Rated voltage	V	300	300
---------------	---	-----	-----

Rated current

AWG conductor

Material data

Type of insulating material	PBT GF
-----------------------------	--------

Flammability class acc. UL94

Contact base material	CuSn
-----------------------	------

Contact plating

- ### Information
- Additional colours on request
 - Rated current refers to rated cross-section and min. number of poles
 - Distance between the rows: see pcb layout diagram
 - Drawing information P = Pitch

Ordering data

Solder pin length	3.2 mm
Colour	orange

[illegible]

Pitch 5.08 mm

Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
4	5.08	(0.200)	50		1320060000
6	10.16	(0.400)	50		1320160000
8	15.24	(0.600)	50		1372460000
10	20.32	(0.800)	50		1372560000
12	25.40	(1.000)	50		1372660000
14	30.48	(1.200)	20		1372760000
16	35.56	(1.400)	20		1372860000
18	40.64	(1.600)	20		1372960000
20	45.72	(1.800)	20		1373060000
22	50.80	(2.000)	10		1373160000
24	55.88	(2.200)	10		1373260000
26	60.96	(2.400)	10		1373360000
28	66.04	(2.600)	10		1373460000
30	71.12	(2.800)	10		1373560000
32	76.20	(3.000)	10		1373660000
34	81.28	(3.200)	10		1373760000
36	86.36	(3.400)	10		1373860000
38	91.44	(3.600)	10		1373960000
40	96.52	(3.800)	10		1374060000
42	101.60	(4.000)	10		1374160000
44	106.68	(4.200)	10		1374260000
46	111.76	(4.400)	10		1374360000
48	116.84	(4.600)	10		1374460000

Ordering data

Solder pin length	3.2 mm
Colour	orange


[illegible]

Pitch 5.08 mm

Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
4	5.08	(0.200)	50		1320660000
6	10.16	(0.400)	50		1320760000
8	15.24	(0.600)	50		1388560000
10	20.32	(0.800)	50		1388660000
12	25.40	(1.000)	50		1388760000
14	30.48	(1.200)	20		1388860000
16	35.56	(1.400)	20		1388960000
18	40.64	(1.600)	20		1389060000
20	45.72	(1.800)	20		1389160000
22	50.80	(2.000)	10		1389260000
24	55.88	(2.200)	10		1389360000
26	60.96	(2.400)	10		1390660000
28	66.04	(2.600)	10		1390760000
30	71.12	(2.800)	10		1390860000
32	76.20	(3.000)	10		1390960000
34	81.28	(3.200)	10		1391060000
36	86.36	(3.400)	10		1391160000
38	91.44	(3.600)	10		1391260000
40	96.52	(3.800)	10		1391360000
42	101.60	(4.000)	10		1391460000
44	106.68	(4.200)	10		1391560000
46	111.76	(4.400)	10		1391660000
48	116.84	(4.600)	10		1391760000

**Unimate Range
Pitch 5.08**

Accessories



See page L.10



See page L.7

Ordering data

Solder pin length	3.2 mm
Colour	orange


[illegible]

Pitch 5.08 mm

Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
4	5.08	(0.200)	50		1321460000
6	10.16	(0.400)	50		1321560000
8	15.24	(0.600)	50		1392760000
10	20.32	(0.800)	50		1392860000
12	25.40	(1.000)	50		1392960000
14	30.48	(1.200)	20		1393060000
16	35.56	(1.400)	20		1393160000
18	40.64	(1.600)	20		1393260000
20	45.72	(1.800)	20		1393360000
22	50.80	(2.000)	20		1393460000
24	55.88	(2.200)	10		1393560000
26	60.96	(2.400)	10		1394860000
28	66.04	(2.600)	10		1394960000
30	71.12	(2.800)	10		1395060000
32	76.20	(3.000)	10		1395160000
34	81.28	(3.200)	10		1395260000
36	86.36	(3.400)	10		1395360000
38	91.44	(3.600)	10		1395460000
40	96.52	(3.800)	10		1395560000
42	101.60	(4.000)	10		1395660000
44	106.68	(4.200)	10		1395760000
46	111.76	(4.400)	10		1395860000
48	116.84	(4.600)	10		1395960000






See page L.24



See page L.11





Clamping yoke connection pin headers

Accessories


Coding element

See page L.10




Fixing block

See page L.8



Marking strips

See page L.24



Screwdriver


See page L.22

Part no. 9008390000




Clamping yoke connection pin connectors for rail mounting

SLAS B
Including locking foot




- 0.13 – 3.31 mm² (IEC) / 26 – 12 AWG (UL)
- 250 V (IEC) / 300 V (UL)
- 16 A (IEC) / 10 A (UL)

SLAS B mit RF15



SLAS B mit KF



Technical data

Rated data acc. to IEC 664-1 / VDE 0110 (4.97)

Clamping range, max.	mm²	0.08...3.30
Solid H05(07) V-U	mm²	0.50...2.50
Stranded H07 V-R	mm²	
Flexible H05(07) V-K	mm²	0.50...1.50
Flexible with ferrule	mm²	0.50...1.50
Ferrule with plastic collar	mm²	0.50...1.50
Stripping length	mm	7.0

**Rated current
at ambient temperature**

at ambient temperature	A	16.0	14.0
------------------------	---	------	------

Overvoltage category

Overvoltage category	III	III	II
Pollution severity	3	2	2

Bated voltage	V	250	320	400
---------------	---	-----	-----	-----

Rated voltage	V	250	320	400
Rated impulse voltage	kV	4.0	4.0	4.0

UL 1059 rated data - E60693

Rated voltage	V	300	300
---------------	---	-----	-----

Rated voltage	V	300	300
Rated current	A	10.0	10.0

Rated current	A	10.0	10.0
AWG conductor		26-12	

CSA C22.2 rated data - LR12400 B

Bated voltage	V	300	300
---------------	---	-----	-----

Rated voltage	V	500	500
Rated current	A	10.0	10.0

AWG conductor	26-12
---------------	-------

Material data

Type of insulating material	PBT GF
-----------------------------	--------

Flammability class acc. UL94	V-0
------------------------------	-----

Contact base material	CuSn
-----------------------	------

Contact plating	tin plated
-----------------	------------

Information

- Rated current refers to rated cross-section and min. number of poles
- ferrule without plastic collar acc. to DIN 46228/1
- Ferrule with plastic collar acc. to DIN 46228/4
- Drawing information P = Pitch

Ordering data

Solder pin length

Colour	orange
--------	--------

[illegible]

Pitch 5.08 mm

Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
4	15.24	(0.600)	20	1845900000	
6	25.40	(1.000)	20	1845910000	
8	35.56	(1.400)	10	1845920000	
10	45.72	(1.800)	10	1845930000	
12	55.88	(2.200)	10	1845940000	
16	76.20	(3.000)	5	1845950000	
20	96.52	(3.800)	5	1763310000	
24	116.84	(4.600)	5	1845960000	

Ordering data

Solder pin length

Colour	orange
--------	--------

[illegible]

Pitch 5.08 mm

Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
20	96.52	(3.800)	5	1766140000	

Clamping yoke connection pin connectors for rail mounting

Accessories


Coding element

See page L.10




Fixing block

See page L.8



Marking strips

See page L.24



Screwdriver



See page L.22

Part no. 9008390000



Unimate Range
Pitch 5.08

- BLA



Rated data acc. to IEC 664-1 / VDE 0110 (4.97)

Rated current at ambient temperature	20°C	40°C
A	17.5	15.0

Rated voltage	V	250	320	400
Rated impulse voltage	kV	4.0	4.0	4.0

CSA C22.2 rated data - LR12400 B		B	C	D
Rated voltage	V	300		300
Rated current	A	10.0		10.0
AWG conductor		26-12		

Material data	
Type of insulating material	PBT GF
Flammability class acc. UL94	V-0
Contact base material	CuSn
Contact plating	tin plated

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current refers to rated cross-section and min. number of poles
- ferrule without plastic collar acc. to DIN 46228/1
- Ferrule with plastic collar acc. to DIN 46228/4
- Drawing information P = Pitch

Solder pin length

Colour	orange
--------	--------

[illegible]

Poles	L1 mm (inch)	Qty.	Order no.	Order no.
2	5.08 (0.200)	100	1281760000	
3	10.16 (0.400)	100	1281860000	
4	15.24 (0.600)	100	1281960000	
5	20.32 (0.800)	50	1282060000	
6	25.40 (1.000)	50	1282160000	
7	30.48 (1.200)	50	1282260000	
8	35.56 (1.400)	50	1282360000	
9	40.64 (1.600)	50	1282460000	
10	45.72 (1.800)	50	1282560000	
11	50.80 (2.000)	50	1282660000	
12	55.88 (2.200)	50	1282760000	
13	60.96 (2.400)	50	1282860000	
14	66.04 (2.600)	50	1282960000	
15	71.12 (2.800)	50	1283060000	
16	76.20 (3.000)	50	1283160000	
17	81.28 (3.200)	20	1283260000	
18	86.36 (3.400)	20	1283360000	
19	91.44 (3.600)	20	1283460000	
20	96.52 (3.800)	20	1283560000	
21	101.60 (4.000)	20	1283660000	
22	106.68 (4.200)	20	1314260000	
23	111.76 (4.400)	20	1314360000	
24	116.84 (4.600)	20	1314460000	

Solder pin length

Colour	orange
--------	--------

[illegible]

Poles	L1 mm (inch)	Qty.	Order no.	Order no.
2	5.08 (0.200)	100	1356060000	
3	10.16 (0.400)	100	1356160000	
4	15.24 (0.600)	100	1356260000	
5	20.32 (0.800)	50	1356360000	
6	25.40 (1.000)	50	1356460000	
7	30.48 (1.200)	50	1356560000	
8	35.56 (1.400)	50	1356660000	
9	40.64 (1.600)	50	1356760000	
10	45.72 (1.800)	50	1356860000	
11	50.80 (2.000)	50	1356960000	
12	55.88 (2.200)	50	1357060000	
13	60.96 (2.400)	50	1357160000	
14	66.04 (2.600)	50	1357260000	
15	71.12 (2.800)	50	1357360000	
16	76.20 (3.000)	50	1357460000	
17	81.28 (3.200)	20	1357560000	
18	86.36 (3.400)	20	1357660000	
19	91.44 (3.600)	20	1357760000	
20	96.52 (3.800)	20	1357860000	
21	101.60 (4.000)	20	1357960000	
22	106.68 (4.200)	20	1358060000	
23	111.76 (4.400)	20	1358160000	
24	116.84 (4.600)	20	1358260000	

Clamping yoke connection socket connectors

Accessories


Coding element

See page L.10




Fixing block

See page L.7



Marking strips

See page L.24




Screwdriver

See page L.22

Part no. 9008390000





When the clamping screw is turned, the 'heel' clamp in the Weidmueller TOP connection is levered onto the cable. Further turning of the screw presses the cable onto the current bar until the required torque level is achieved; securely fixing the cable.

- 0.13 – 2.5 mm² (IEC) / 26 – 14 AWG (UL)
- 250 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

Rated data acc. to IEC 664-1 / VDE 0110 (4.97)

Clamping range, max.	mm ²	0.13...2.50
Solid H05(07) V-U	mm ²	0.50...2.50
Stranded H07 V-R	mm ²	
Flexible H05(07) V-K	mm ²	0.50...2.50
Flexible with ferrule	mm ²	0.50...1.50
Ferrule with plastic collar	mm ²	0.50...1.50
Stripping length	mm	13.0

**Rated current
at ambient temperature**

at ambient temperature		A	15.0	13.0
Overvoltage category			III	II
Pollution severity			3	2
Rated voltage	V	250	320	400
Rated impulse voltage	kV	4.0	4.0	4.0

UL 1059 rated data - E60693

Rated voltage	V	300	300
Rated current	A	10.0	10.0
AWG conductor		26-14	

CSA C22.2 rated data - LR12400 B


Rated voltage	V	300	300
Rated current	A	10.0	10.0
AWG conductor		26-14	

Material data

Type of insulating material	PBT GF
Flammability class acc. UL94	V-0
Contact base material	CuSn
Contact plating	tin plated

Information

- Additional colours on request
- Gold-plated contact surfaces on request
- Rated current refers to rated cross-section and min. number of poles
- ferrule without plastic collar acc. to DIN 46228/1
- Ferrule with plastic collar acc. to DIN 46228/4
- Drawing information P = Pitch



Solder pin length

Colour	orange
--------	--------


[illegible]

Pitch 5.08 mm

Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
2	5.08	(0.200)	100	1484260000	
3	10.16	(0.400)	100	1484360000	
4	15.24	(0.600)	100	1484460000	
5	20.32	(0.800)	50	1484560000	
6	25.40	(1.000)	50	1484660000	
7	30.48	(1.200)	50	1484760000	
8	35.56	(1.400)	50	1484860000	
9	40.64	(1.600)	50	1484960000	
10	45.72	(1.800)	50	1485060000	
11	50.80	(2.000)	50	1485160000	
12	55.88	(2.200)	50	1485260000	
13	60.96	(2.400)	50	1485360000	
14	66.04	(2.600)	50	1485460000	
15	71.12	(2.800)	50	1485560000	
16	76.20	(3.000)	50	1485660000	
17	81.28	(3.200)	20	1485760000	
18	86.36	(3.400)	20	1485860000	
19	91.44	(3.600)	20	1485960000	
20	96.52	(3.800)	20	1486060000	
21	101.60	(4.000)	20	1486160000	
22	106.68	(4.200)	20	1486260000	
23	111.76	(4.400)	20	1486360000	
24	116.84	(4.600)	20	1486460000	

TOP clamp connection socket connectors

BLAT B



Ordering data

Solder pin length

Colour orange

Pitch 5.08 mm

Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
2	5.08	(0.200)	100	1486560000	
3	10.16	(0.400)	100	1486660000	
4	15.24	(0.600)	100	1486760000	
5	20.32	(0.800)	50	1486860000	
6	25.40	(1.000)	50	1486960000	
7	30.48	(1.200)	50	1487060000	
8	35.56	(1.400)	50	1487160000	
9	40.64	(1.600)	50	1487260000	
10	45.72	(1.800)	50	1487360000	
11	50.80	(2.000)	50	1487460000	
12	55.88	(2.200)	50	1487560000	
13	60.96	(2.400)	50	1487660000	
14	66.04	(2.600)	50	1487760000	
15	71.12	(2.800)	50	1487860000	
16	76.20	(3.000)	50	1487960000	
17	81.28	(3.200)	20	1488060000	
18	86.36	(3.400)	20	1488160000	
19	91.44	(3.600)	20	1488260000	
20	96.52	(3.800)	20	1488360000	
21	101.60	(4.000)	20	1488460000	
22	106.68	(4.200)	20	1488560000	
23	111.76	(4.400)	20	1488660000	
24	116.84	(4.600)	20	1488760000	

Articles with coloured order number are kept permanently in stock at the central warehouse in Germany.
Delivery times see page X.2

Accessories


Coding element

See page L.10



Fixing block

See page L.7



Marking strips

See page L.24



Screwdriver

See page L.22


Part no. 9008390000





Non ratchet tools however rely on the consistency of the operator, and after many crimping operations the crimp quality cannot be guaranteed.

- 0.22 – 2.5 mm² (IEC) / 26 – 14 AWG (UL)
- 250 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 10 A (UL)



Rated data acc. to IEC 664-1 / VDE 0110 (4.97)

Clamping range, max.	mm²	0.22...2.50
Solid H05(07) V-U	mm²	
Stranded H07 V-R	mm²	
Flexible H05(07) V-K	mm²	
Flexible with ferrule	mm²	
Ferrule with plastic collar	mm²	
Stripping length	mm	5.0

**Rated current
at ambient temperature**

	A	17.5		15.0
Overvoltage category		III	III	II
Pollution severity		3	2	2
Rated voltage	V	250	320	500
Rated impulse voltage	kV	4.0	4.0	4.0

UL 1059 rated data - E60693

Rated voltage	V	300	300
Rated current	A	10.0	10.0
AWG conductor		26-14	

CSA C22.2 rated data - LR12400 B

Rated voltage	V	300	300
Rated current	A	10.0	10.0
AWG conductor		26-14	

Material data

Type of insulating material	PBT GF
Flammability class acc. UL94	V-0
Contact base material	Cu alloy
Contact plating	

Information

- Additional colours on request
- Rated current refers to rated cross-section and min. number of poles
- Rated cross-section depends on the crimping contact type used
- Drawing information P = Pitch

Solder pin length

Colour orange



[illegible]

Pitch 5.08 mm

Poles	L1 mm	(inch)	Qty.	Order no.	Order no.
2	5.08	(0.200)	100	1578220000	
3	10.16	(0.400)	100	1477960000	
4	15.24	(0.600)	100	1478060000	
5	20.32	(0.800)	50	1577480000	
6	25.40	(1.000)	50	1478160000	
7	35.56	(1.400)	50	1577490000	
8	35.56	(1.400)	50	1478260000	
9	40.64	(1.600)	50	1577500000	
10	45.72	(1.800)	50	1478360000	
11	45.72	(1.800)	50	1577510000	
12	55.88	(2.200)	50	1478460000	
13	60.96	(2.400)	50	1601120000	
14	66.04	(2.600)	50	1594160000	
15	71.12	(2.800)	50	1601130000	
16	76.20	(3.000)	50	1478560000	
17	81.28	(3.200)	20	1601140000	
18	86.36	(3.400)	20	1601150000	
19	91.44	(3.600)	20	1601160000	
20	96.52	(3.800)	20	1478660000	
21	101.60	(4.000)	20	1601170000	
22	106.68	(4.200)	20	1601180000	
23	111.76	(4.400)	20	1601190000	
24	116.84	(4.600)	20	1478760000	

Crimp connection socket connectors

BLAC BR



Ordering data

Solder pin length

Colour

orange

Pitch 5.08 mm

Poles	L1 mm (inch)	Qty.	Order no.	Order no.
2	5.08 (0.200)	100	1578230000	
3	10.16 (0.400)	100	1478860000	
4	15.24 (0.600)	100	1478960000	
5	20.32 (0.800)	50	1444160000	
6	25.40 (1.000)	50	1479060000	
7	30.48 (1.200)	50	1577430000	
8	35.56 (1.400)	50	1479160000	
9	40.64 (1.600)	50	1577420000	
10	45.72 (1.800)	50	1479260000	
11	55.88 (2.200)	50	1577410000	
12	55.88 (2.200)	50	1479360000	
13	60.96 (2.400)	50	1601280000	
14	66.04 (2.600)	50	1594170000	
15	71.12 (2.800)	50	1601290000	
16	76.20 (3.000)	50	1479460000	
17	81.28 (3.200)	20	1601300000	
18	86.36 (3.400)	20	1601310000	
19	91.44 (3.600)	20	1601320000	
20	96.52 (3.800)	20	1479560000	
21	101.60 (4.000)	20	1601330000	
22	106.68 (4.200)	20	1601340000	
23	111.76 (4.400)	20	1601350000	
24	116.84 (4.600)	20	1479660000	

DFFC

Crimp contacts



Ordering data

Single contacts, tin-plated

For conductor	Qty.	Order no.
0.22 – 0.35 mm² / 24 – 22 AWG	250	1604250000
0.50 – 1.00 mm² / 20 – 17 AWG	250	1567060000
1.50 – 2.50 mm² / 16 – 14 AWG	250	1567070000

Ordering data

Bandolier, tin-plated

For conductor	Qty.	Order no.
0.22 – 0.35 mm² / 24 – 22 AWG	3000	1604230000
0.50 – 1.00 mm² / 20 – 17 AWG	3000	1480000000
1.50 – 2.50 mm² / 16 – 14 AWG	3000	1480100000

Accessories


Coding element

See page L.10



Fixing block

See page L.7



Marking strips

See page L.24



Crimping tool

See page L.20

