




Technical drawing of a mechanical assembly (Fig. 1) showing a side view. The drawing includes the following dimensions and callouts:

- Overall length: 24.2 ± 0.5
- Diameter of the main body: $\varnothing 13.8$
- Diameter of the base: $\varnothing 14.4$
- Callout 1 points to a feature on the main body.
- Callout 4 points to a feature on the base.



Temperature Range: -55 °C to +85 °C

	PART	DESCRIPTION
1	Body	Brass, nickel plated 2.54 μm
2	Ferrule	Brass, nickel plated 2.54 μm
3	Contact	Brass, gold plated 0.076 μm - 0.127 μm
4	Dielectric	POM

Drawing, Address & RoHS Update	JT	5	25 Mar 10
Measurements Updated	KA	4	13 Aug 07
CAD Issue	SN	3	21 Aug 01
Ferrule size changed from 10.7 + 11.8 to 10.9 + 12.4	PDC	2	19 Oct 00
First Issue		1	
DESCRIPTION OF REVISION	APPVD	ISS	DATE



PAGE: 1 of 1