





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
BD	48		F1	REVISED PER ECO-11-004835	11MAR11	RK	HMR




APPLICATION DETAIL



- 1 FOR SATISFACTORY OPERATION THESE DIMENSIONS MUST BE MAINTAINED, .170 DIMENSION SHOULD BE MEASURED AT HEIGHT OF .320 MIN.
- 2 SPRING LATCH ACCOUNTS FOR DESIGN VARIATIONS IN THE ENVELOPE OF POST MOLDED STRAIN RELIEFS.
- 3 WHEN ORDERING SPRING LATCHES SPECIFY NUMBER OF CONNECTORS, QUANTITY SHIPPED WILL BE BASED ON 2 SPRING LATCHES REQUIRED PER CONNECTOR.
- 4 MEASURED FROM END OF CONNECTOR FLANGE TO END OF TAB ON SPRING LATCH.

OBSOLETE	.325	.650	BULK 3	745779-6
	.325	.650	2 PIECE UNIT	745779-5
	.270	.540	BULK 3	745779-3
	.270	.540	2 PIECE UNIT	745779-2
	D	C	KIT PACKAGING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.GERACE	02-24-83	 TE Connectivity									
		CHK J.GERACE	02-24-83										
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R.LEGGETT	NAME		SPRING LATCH, 2 PIECE, AMPLIMATE™							
	0 PLC ± -		PRODUCT SPEC	SIZE				CAGE CODE		DRAWING NO		RESTRICTED TO	
	1 PLC ± -		—										
	2 PLC ± -		APPLICATION SPEC										
	3 PLC ± .010		—										
4 PLC ± -		—											
ANGLES ± 3°													
MATERIAL	FINISH	WEIGHT	—	A2		00779		C=745779		—			
STAINLESS STEEL		—		CUSTOMER DRAWING				SCALE 10:1		SHEET 1 of 1		REV F1	