


THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

BY AMP INCORPORATED, ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
CM	52	P	LTR	DESCRIPTION	DATE	DWN
		G		REV & REDWN PER EC 0L30-0125-97	5-22-97	APVD
						RS



1. 0.00038 MIN SELECTIVE GOLD PLATING ON INSIDE OF RECEPTACLE OVER NICKEL OVER ALL UNDERPLATE.
2. WIRE RANGE: 0.2 - 0.6 MM² (24 - 20 AWG)
3. INSULATION RANGE: 1.14 - 1.78



SECTION A-A



SECTION B-B

MATTE TIN	0.25 BE COPPER	61119-3
PRE-TIN	0.25 PH BRZ	61119-2
△	0.25 BE COPPER	61119-1
FINISH	MATERIAL	PART NUMBER

1.47	.058	2.29	.090	4.11	.162	-	-
1.359	.0535	1.93	.076	2.92	.115	-	-
1.14	.045	1.91	.075	2.79	.110	13.67	.538
0.25	.010	1.78	.070	2.54	.100	13.51	.532
0.13	.005	1.52	.060	2.41	.095	8.38	.330
0.00038	.000015	1.486	.0585	2.31	.091	4.27	.168
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	T. BECK	5-22-97	AMP AMP Incorporated Harrisburg, PA 17105-3608		
		CHK	R. SWING	5-22-97			
		APVD	A. BEDDICK	6-17-97	NAME RECEPTACLE, .058 DIAMETER, 24-20 AWG, .045-.070 INSULATION, RIGHT ANGLE, P.C. CONTACT		
		PRODUCT SPEC		108-1025			
		APPLICATION SPEC		114-1008			
		WEIGHT		-			
		CUSTOMER DRAWING					
		SCALE		10:1			
		SHEET		1			
		REV		G			