



PART NUMBER	COPPER CONDUCTOR SIZE RANGE	STUD HOLE SIZE (IN.)	STUD HOLE SPACING (IN.)	HEX KEY SIZE (IN.)	FIGURE DIMENSIONS (IN.)					TIGHTENING TORQUE (IN.-LBS.)	STD. PKG. QTY.
					L	W	H	T	P		
HL8-2N-X	#4 SOL- #1 STR	1/2	1.75	7/16	3.94	1.00	.90	.22	3.00	100	10
HL13-2N-5	#1 SOL- 2/0 STR	1/2	1.75	9/16	4.25	1.00	1.07	.22	3.00	250	5
HL21-2N-5	2/0 STR- 4/0 STR	1/2	1.75	9/16	4.19	1.25	1.34	.25	3.00	250	5
HL30-2N-2	4/0 STR- 300 kcmil	1/2	1.75	5/8	4.25	1.25	1.46	.31	3.00	350	2

NOTES:

1. CAST FROM HIGH STRENGTH CORROSION RESISTANT COPPER ALLOY TO PROVIDE PREMIUM ELECTRICAL AND MECHANICAL PERFORMANCE.
2. WIRE RANGE-TAKING CAPABILITY MINIMIZES INVENTORY REQUIREMENTS.
3. INTERNAL PRESSURE PLATE PROVIDES UNIFORM CLAMPING FORCE ON CONDUCTOR FOR PREMIUM ELECTRICAL PERFORMANCE.
4. INTERNAL BARREL SERRATIONS ALLOW FOR PREMIUM WIRE PULL-OUT STRENGTH.
5. INSPECTION WINDOW TO VISUALLY ASSURE FULL CONDUCTOR INSERTION.
6. FLAT BOTTOM ALLOWS FOR COMPLETE CONTACT WITH MOUNTING SURFACE.
7. UL LISTED FOR USE UP TO 600V AND TEMPERATURE RATED 90° C.



C41435_00

								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
00	9/04	KF		RELEASED				TWO-HOLE, STRAIGHT TONGUE LUG WITH NEMA HOLE SIZES & SPACING HL-2N FAMILY			
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY KLFU	CHK'D	SCALE NONE	DRAWING NO. C41435