

MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING
602EN67-6B

1 ——— 3
↑
CIRCUIT DIAGRAM

602EN67-6B

M

DRAWING
NUMBER

12

ISSUE

REPLACES

RELEASE NO. PR-3483

CHECK

REVISIONS

A OBS
COS7504
SMA
28 MAY 85
B REINST
PR19059
MAM
20 FEB 91

CHECK



CHECK

CHECK

DDM/CAD

DRAWN

M A M 20FEB91



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS


OPERATING FORCE ——— 6-12 LB
FULL OVERTRAVEL FORCE ——— 30 LB MAX
RELEASE FORCE ——— 4 LB MIN
PRETRAVEL ——— .040 MAX
DIFFERENTIAL TRAVEL ——— .020 MAX
OVERTRAVEL ——— .125 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

LOAD	28 VDC	
	SEA LEVEL	50,000 FT.
RES	7	7
IND	4	2.5
MOTOR	4	
LAMP		

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±
WEIGHT 4.0 OZ MAX

NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
- 3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
- 4 - BOTTOM OF SWITCH COATED WITH RESILIENT POTTING MATERIAL
- 5 - THIS DIMENSION EXCLUDES THE RESILIENT POTTING MATERIAL ON THE BOTTOM OF THE SWITCH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[602EN67-6B](#)