






FCIconnect.com


Copyright FCI

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	TIN LEAD	TIN LEAD	LEAD FREE	LEAD FREE
09	30.81	24.99	18.00	16.21	10.96	D09S81C4GL00	D09S81C6GL00	D09S81C4GL00LF	D09S81C6GL00LF
15	39.14	33.32	26.32	24.54	19.18	D15S81C4GL00	D15S81C6GL00	D15S81C4GL00LF	D15S81C6GL00LF
25	53.03	47.04	40.04	38.25	33.12	D25S81C4GL00	D25S81C6GL00	D25S81C4GL00LF	D25S81C6GL00LF
37	69.32	63.50	56.50	54.71	49.68	D37S81C4GL00	D37S81C6GL00	D37S81C4GL00LF	D37S81C6GL00LF
						Gold flash	0.76 μ gold	Gold flash	0.76 μ gold

view shown without plastic pin and grounding



PC card drilling dimensions(after plating)
(thickness 1.60 ±0.20)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface	tolerance	projection	product family			
-				ISO 1302	ISO 406 ISO 1101		D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title			
G	ELX-I-18050	MP	2014/06/23	angles	linear					
				0°±2°						
				dr	PESSON	1996/12/06	dwg no		sheet 1 of 1	size
				engr	MITHUN PAUL	2014/06/23	C01-8646-0522			A3
				chr	ALIAS BABU	2014/06/23	type Product Customer Drawing			
				appd	BIJU K PAUL	2014/06/23				
sheet index	revision sheet	G	1							