

REFERENCE SPECIFICATIONS

- DIN-41612
- IEC-603-2

PHYSICAL CHARACTERISTICS

- INSULATOR MATERIAL:
 - Polyester thermoplastic UL94V0 - Color grey
- CONTACT MATERIAL: -PHOSPHOR BRONZE : (FEMALE CONTACT)
 - PHOSPHOR BRONZE : (MALE CONTACT -SOLDER BUCKET)
 - PHOSPHOR BRONZE : (MALE CONTACT-WIRE WRAP)

ELECTRICAL CHARACTERISTICS

- CURRENT RATING : 1.5A at 20°C / 1A at 70°C 40A AT 20°C (power contact)
- MAXIMAL CURRENT: 2A
- CONTACT RESISTANCE ≤20mΩ ≤1mΩ under 10 A (power contact)
- VOLTAGE PROOF: contact/contact 1000 V eff (0.5 mA / 50 Hz)
contact/ground 1550 V eff (0.5 mA / 50 Hz)
- INSULATION RESISTANCE: ≥10⁶ MΩ
- CREEPAGE AND CLEARANCE DISTANCE: ≥1.2 mm
- WIPPING/PLUG IN DIRECTION: ≥1.8mm
- ALTERNATIF CURRENT V AC: 330 V
- DIRECT CURRENT V DC: 470 V

MECHANICAL CHARACTERISTICS

- MATING FORCE : ≤ n x 0.94 N (n = NUMBER OF CTS) ≤ 10 N (power contact)
- UNMATING FORCE : ≥ n x 0.15 N (n = NUMBER OF CTS) ≤ 10 N (power contact)
- GAUGE RETENTION FORCE: ≥0.15 N
THICKNESS GAUGE = 0.56 0/-0.02 - SURFACE ROUGHNESS: Ra = 0.25µm MAXI
- CONTACT RETENTION IN INSULATOR: ≥ 20 N according to IEC 512 test 6d
- VIBRATIONS: ≤ 1 µs according to IEC 512.4 test 6d
≤ 40 mΩ according to DIN41640 teil 15 test 6d

DIN class 3	(not applicable)
DIN class 2	10-500 HZ/5g
DIN class 1	10-2000 HZ/20g

- SHOCK: ≤ 1 µs according to IEC 512 test 6c
≤ 40 mΩ according to DIN 41640 teil 14 test 6c

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: TEMPERATURE RANGE -55°C TO +125°C
DAMP HEAT STEADY STATE 56 DAYS Class 1
21 DAYS Class 2
(not applicable) Class 3
- ELECTRICAL LOAD AND TEMPERATURE: T= +70°C / I= 1A PER CTS - 1000 HRS

PERFORMANCE LEVELS TIN LEAD P/N : 8609 XXX XX XX 7XX XXX EX
PURE TIN P/N : 8609 XXX XX XX 7XX XX LF

MECHANICAL ENDURANCE AND INDUSTRIAL ATMOSPHERE TEST ⁽¹⁾		
		PERFORMANCE LEVELS
4	50 OPERATIONS	DIN Class 3
5	200 OP. + TEST(1) 4 DAYS + 200 OP.	DIN Class 2
6	250 OP. + TEST(1) 21 DAYS + 250 OP.	DIN Class 1

TEST ⁽¹⁾ INDUSTRIAL ATMOSPHERE SO₂

CONTACT PLATING FOR SOLDER BUCKET

- TIN LEAD VERSION:
 - MALE AND FEMALE CONTACTS:
 - GOLD OVER NICKEL GOLD+PALLADIUM-NICKEL OVER NICKEL ON MATING SURFACES
 - TIN LEAD OVER NICKEL ON SOLDER BUCKET
- LEAD FREE VERSION:

NOTE:RoHS INFORMATIONS

- The "LF" products meet European Union Directives and other country regulations as described in GS-22-008.
- Termination plating spec: 2 µm Nickel mini, 2 µm Pure Tin mini
- Packaging spec: see GS-14-920

CONTACT PLATING FOR WIRE WRAP

- TIN LEAD VERSION:
 - MALE AND FEMALE CONTACTS:
 - GOLD OVER NICKEL ON MATING SURFACES
 - TIN LEAD OVER NICKEL ON WIRE WRAP
- LEAD FREE VERSION:

NOTE:RoHS INFORMATIONS

- The "LF" products meet European Union Directives and other country regulations as described in GS-22-008.
- Termination plating spec: 1,27 µm Nickel mini, 0,5 to 4 µm Pure Tin maxi
- Packaging spec: see GS-14-920

European Views

www.fciconnect.com				surface ISO 1302 ✓	tolerance std ISO 406 ISO 1101	projection 	mm
				TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	GOISNARD	2005/04/13	ANGULAR	0.X	±0.1	size A3	Scale 1
Eng	TARON	2005/04/13	LINEAR	0.XX	±0.1	ECN LS07-0211	
Chr	LEGARE	2005/04/13		0.XX' ±2"	±0.1		
Appr	LEGARE	2005/04/13	Product family	DIN 8609		Spec ref	-
rev	ecn no	dr	date				
A	LS05-0039	LGO	2005/04/13				
B	LS06-0097	LGO	2006/07/11				
C	LS06-0201	HLE	2006/11/24				
D	LS07-0211	HLE	2007/08/16				
				title DIN 41612 SOLDER BUCKET AND WIRE WRAP			
				CONNECTORS GENERAL CHARACTERISTICS			
				catalog no	-	dwg no C-8609-0000B	Rev. D
				CUSTOMER sheet 1 of 1			

REV F - 2006-04-17