

TENTATIVE

TOSHIBA ZENER DIODE SILICON DIFFUSED TYPE


## 1ZC12~1ZC120

CONSTANT VOLTAGE REGULATION  
TELEPHONE, PRINTER USES

- Average Power Dissipation :  $P = 1.0\text{W}$
- Zener Voltage :  $V_Z = 12\text{~}120\text{ V}$
- Tolerance of Zener Voltage ( $V_Z$ ) :  $\pm 10\%$
- Plastic Mold Package


MAXIMUM RATINGS ( $T_a=25^\circ\text{C}$ )

CHARACTERISTIC	SYMBOL	RATING	UNIT
Power Dissipation	P	1.0	W
Junction Temperature	$T_j$	-40~150	$^\circ\text{C}$
Storage Temperature Range	$T_{stg}$	-40~150	$^\circ\text{C}$






Weight: 0.18g (Typ.)

## MARKING



## ELECTRICAL CHARACTERISTICS (Ta=25°C)

TYPE	ZENER CHARACTERISTICS				MEASURE- MENT CURRENT I <sub>Z</sub> (mA)	TEMPERATURE COEFFICIENT OF ZENER VOLTAGE α <sub>T</sub> (mV / °C)	FORWARD VOLTAGE		REVERSE CURRENT		
	ZENER VOLTAGE V <sub>Z</sub> (V)		ZENER IMPEDANCE r <sub>d</sub> (Ω)	MAX.			V <sub>F</sub> (V)	MEASURE- MENT CURRENT I <sub>F</sub> (A)	I <sub>R</sub> (µA)	MEASURE- MENT VOLTAGE V <sub>R</sub> (V)	
	MIN.	TYP.	MAX.	MAX.		TYP.	MAX.	MAX.	MAX	MAX	
1ZC12	10.8	12	13.2	30	10	8	13	1.2	0.2	10	8.0
1ZC13	11.7	13	14.3	30	10	9	14	1.2	0.2	10	9.0
1ZC15	13.5	15	16.5	30	10	11	17	1.2	0.2	10	10.0
1ZC16	14.4	16	17.6	30	10	12	19	1.2	0.2	10	11.0
1ZC18	16.2	18	19.8	30	10	14	23	1.2	0.2	10	13.0
1ZC20	18.0	20	22.0	30	10	16	26	1.2	0.2	10	14.0
1ZC22	19.8	22	24.2	30	10	18	28	1.2	0.2	10	16.0
1ZC24	21.6	24	26.4	30	10	20	32	1.2	0.2	10	17.0
1ZC27	24.3	27	29.7	30	10	23	36	1.2	0.2	10	19.0
1ZC30	27.0	30	33.0	30	10	25	40	1.2	0.2	10	21.0
1ZC33	29.7	33	36.3	30	10	26	41	1.2	0.2	10	26.4
1ZC36	32.4	36	39.6	30	9	28	45	1.2	0.2	10	28.8
1ZC39	35.1	39	42.9	35	8	30	48	1.2	0.2	10	31.2
1ZC43	38.7	43	47.3	40	7	33	53	1.2	0.2	10	34.4
1ZC47	42.3	47	51.7	65	6	38	60	1.2	0.2	10	37.6
1ZC51	45.9	51	56.1	65	6	43	68	1.2	0.2	10	40.8
1ZC56	50.4	56	61.6	85	5	48	77	1.2	0.2	10	44.8
1ZC62	55.8	62	68.2	105	5	53	85	1.2	0.2	10	49.6
1ZC68	61.2	68	74.8	120	4	57	90	1.2	0.2	10	54.4
1ZC75	67.5	75	82.5	150	4	66	104	1.2	0.2	10	60.0
1ZC82	73.8	82	90.2	170	3	71	113	1.2	0.2	10	65.4
1ZC91	81.9	91	100.1	240	3	79	127	1.2	0.2	10	72.8
1ZC100	90.0	100	110.0	300	3	87	138	1.2	0.2	10	80.0
1ZC110	99.0	110	121.0	300	3	96	152	1.2	0.2	10	88.0
1ZC120	108.0	120	132.0	350	2.5	106	171	1.2	0.2	10	96.0



**RESTRICTIONS ON PRODUCT USE**

000707EAA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.  
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.