





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		N	REVISED PER ECR-13-011489	06DEC2013	KH	PD




- 1 CONTINUOUS STRIP ON REEL.
- 2 NO BURRS PERMISSIBLE AT HOLE. .005 MAX RADIUS PERMISSIBLE ON TOP.



SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1



SECTION C-C
SCALE 10:1

TIN	.120-.150	18-14	60850-2
—	.120-.150	18-14	60850-1
FINISH	INSULATION RANGE	WIRE RANGE	PART NO

0	.180	.218	F	.110	.085	14	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	2/16/89	TE Connectivity					
					.076	16	DIMENSIONS: INCHES	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	CHK	MS FEHER	2/16/89						
					.071	18			APVD	C MEYERS	2/17/89						
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	±.002 HEIGHT	WIRE			PRODUCT SPEC	NAME							
INSUL BARREL CRIMP			WIRE BARREL CRIMP		MATERIAL	FINISH			APPLICATION SPEC								
							BRASS	SEE TABLE	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
									WEIGHT	—	A2	00779	C-60850	—			
									CUSTOMER DRAWING			SCALE	6:1	SHEET	1 of 1	REV	N