



REVISION RECORD		
REV	DESCRIPTION	DRFT



NOTES:

ELECTRICAL:

1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 35 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH : 1000 VDC RMS 60Hz, 1MIN.
6. OPERATING: 750 CYCLES MIN.


MECHANICAL:

1. HOUSING MATERIAL : GLASS FIBER FILLED NYLON, UL94V-0\BLACK.
2. INSERT MATERIAL : GLASS FIBER FILLED NYLON, UL94V-0\BLACK.
3. CONTACT MATERIAL : PHOSPHOR BRONZE 0.35mm THICKNESS.
4. PLATING : GOLD PLATING OVER NICKEL.
5. PCB RETENTION PRE-SOLDER : 1 LB MIN.
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.


ENVIRONMENTAL:

1. STORAGE : -40°C TO +85°C.
 2. OPERATION: -40°C TO +85°C.
 3. WAVE SOLDERING TEMPERATURE: 255°C±5°C (5 SEC MAX).
- MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.

E5J88-00LJG2-L	6u"
PART NO.	Au PLATING



PC BOARD LAYOUT T=1.60mm
COMPONENT SIDE SHOWN
TOLERANCES±0.05mm

DETACHED LISTS	MM (INCH)		RoHS Compliant					
	TOLERANCES EXCEPT AS NOTED		TITLE					
	MM		LED JACK UTP W/O LED					
	.0 ± 0.25	±						
	.00 ± 0.20	±						
	.000 ± 0.10	±						
	ANGLES ± 1°		DFTO :	ELLA	DRAWING NO.	CE5J88-00LJGX-L	SIZE	REV
			DATE :	03/20/2013	/PART NO.	E5J88-00LJG2-L	A3	0
	THIRD ANGLE PROJECTION		SCALE :	4:1	DO NOT SCALE DRAWING		SHEET	1 OF 1