




1. RECOMMENDED SPARE PARTS.
2. GREASE RAM, CAM, CAM FOLLOWER AND FEED ROD LIGHTLY.
3. LUBRICATE DAILY PER THE APPLICATOR INSTRUCTION SHEET SUPPLIED WITH THE APPLICATOR.
4. THIS APPLICATOR HAS BEEN DESIGNED TO APPLY WIRES WITH THIN WALL (FLR) INSULATION. THE INSULATION CRIMP & APPLICABLE INSULATION RANGE MAY NOT CONFORM TO PARAMETERS LISTED IN THE APPLICATION SPECIFICATION.



WIRE SIZE (AWG)	TENSILE STRENGTH (Kg)
14	28 MIN
16	20 MIN
18	70% MIN OF THE AVERAGE OF THE
20	TENSILE STRENGTH OF FIVE WIRES

UNITS: mm (INCHES)	MATL: -	HT TR: -	FIN: -
SCALE PRINT: -	 AMP Incorporated 707-938-2700		
UNITS, UNLESS SPECIFIED: -			
DR: 30APPRO APP: 30APPRO			
M: H. CLIFFORD			
CHK: -	REL: 7-7-09-01	M: G. O'BRIEN	
NAME: END FEED	HD: 1	APPLICATOR:	MACHINE REF: HO-1
SCALE: -	D	DWG NO: 1335557	SHEET 1 of 1
TUR: ☒	BREK: -	REV: A	
GES RO. 38 MAX			