

Features

- Temperature Ranges
 - Industrial: -40°C to 85°C
 - Automotive-A ^[1]: -40°C to 85°C
 - Automotive-E ^[1]: -40°C to 125°C
- Pin and Function compatible with CY7C1041CV33
- High Speed
 - t_{AA} = 10 ns
- Low Active Power
 - I_{CC} = 90 mA at 10 ns (industrial)
- Low CMOS Standby Power
 - I_{SB2} = 10 mA
- 2.0V Data Retention
- Automatic Power Down when deselected
- TTL compatible Inputs and Outputs
- Easy Memory Expansion with $\overline{CE}$ and $\overline{OE}$ features
- Available in Pb-free 48-ball VFBGA, 44-pin (400-mil) molded SOJ, and 44-pin TSOP II Packages

Functional Description

The CY7C1041DV33 is a high performance CMOS Static RAM organized as 256K words by 16 bits. To write to the device, take Chip Enable ($\overline{CE}$) and Write Enable ($\overline{WE}$) inputs LOW. If Byte LOW Enable ($\overline{BLE}$) is LOW, then data from I/O pins (I/O_0 to I/O_7) is written into the location specified on the address pins (A_0 to A_{17}). If Byte HIGH Enable ($\overline{BHE}$) is LOW, then data from I/O pins (I/O_8 to I/O_{15}) is written into the location specified on the address pins (A_0 to A_{17}).


To read from the device, take Chip Enable ($\overline{CE}$) and Output Enable ($\overline{OE}$) LOW while forcing the Write Enable ($\overline{WE}$) HIGH. If $\overline{BLE}$ is LOW, then data from the memory location specified by the address pins appears on I/O_0 to I/O_7 . If $\overline{BHE}$ is LOW, then data from memory appears on I/O_8 to I/O_{15} . See the [Truth Table](#) on page 9 for a complete description of read and write modes.

The input and output pins (I/O_0 to I/O_{15}) are placed in a high impedance state when the device is deselected ($\overline{CE}$ HIGH), outputs are disabled ($\overline{OE}$ HIGH), $\overline{BHE}$ and $\overline{BLE}$ are disabled ($\overline{BHE}$, $\overline{BLE}$ HIGH), or during a write operation ($\overline{CE}$ LOW and $\overline{WE}$ LOW).

The CY7C1041DV33 is available in a standard 44-pin 400-mil wide SOJ and 44-pin TSOP II package with center power and ground (revolutionary) pinout and a 48-ball fine-pitch ball grid array (FBGA) package.

For best practice recommendations, refer to the Cypress application note [AN1064, SRAM System Guidelines](#).

Logic Block Diagram



Note

1. Automotive product information is preliminary.

Selection Guide

Description	-10 (Industrial)	-10 (Automotive-A) ^[1]	-12 (Automotive-E) ^[1]	Unit
Maximum Access Time	10	10	12	ns
Maximum Operating Current	90	90	95	mA
Maximum CMOS Standby Current	10	10	15	mA

Pin Configuration

Figure 1. 48-Ball VFBGA (Pinout 1) ^[2, 3]




Figure 2. 48-Ball VFBGA (Pinout 2) ^[2, 3]





Figure 3. 44-Pin SOJ/TSOP II



Notes

- NC pins are not connected on the die.
- Pinout 1 is compliant with CY7C1041CV33 and pinout 2 is JEDEC compliant. The difference between the two is that the higher and lower byte I/Os (I/O_[7:0] and I/O_[15:8] balls) are swapped.

Maximum Ratings

Exceeding maximum ratings may impair the useful life of the device. These user guidelines are not tested.

Storage Temperature -65°C to +150°C

Ambient Temperature with

Power Applied -55°C to +125°C

Supply Voltage on V_{CC} Relative to GND ^[5].....-0.3V to +4.6V

DC Voltage Applied to Outputs

in High-Z State^[5].....-0.3V to $V_{CC} + 0.3V$

DC Input Voltage^[5]-0.3V to $V_{CC} + 0.3V$

Current into Outputs (LOW)..... 20 mA

Static Discharge Voltage.....>2001V
(MIL-STD-883, Method 3015)

Latch Up Current..... >200 mA

Operating Range

Range	Ambient Temperature	V_{CC}	Speed
Industrial	-40°C to +85°C	$3.3V \pm 0.3V$	10 ns
Automotive-A ^[1]	-40°C to +85°C	$3.3V \pm 0.3V$	10 ns
Automotive-E ^[1]	-40°C to +125°C	$3.3V \pm 0.3V$	12 ns

DC Electrical Characteristics

Over the Operating Range

Parameter	Description	Test Conditions	-10 (Industrial)		-10 (Automotive-A) ^[1]		-12 (Automotive-E) ^[1]		Unit
			Min	Max	Min	Max	Min	Max	
V_{OH}	Output HIGH Voltage	$V_{CC} = \text{Min}, I_{OH} = -4.0 \text{ mA}$	2.4		2.4		2.4		V
V_{OL}	Output LOW Voltage	$V_{CC} = \text{Min}, I_{OL} = 8.0 \text{ mA}$		0.4		0.4		0.4	V
V_{IH} ^[5]	Input HIGH Voltage		2.0	$V_{CC} + 0.3$	2.0	$V_{CC} + 0.3$	2.0	$V_{CC} + 0.3$	V
V_{IL} ^[5]	Input LOW Voltage		-0.3	0.8	-0.3	0.8	-0.3	0.8	V
I_{IX}	Input Leakage Current	$GND \leq V_I \leq V_{CC}$	-1	+1	-1	+1	-1	+1	μA
I_{OZ}	Output Leakage Current	$GND \leq V_{OUT} \leq V_{CC}$, Output Disabled	-1	+1	-1	+1	-1	+1	μA
I_{CC}	V_{CC} Operating Supply Current	$V_{CC} = \text{Max}, f = f_{MAX} = 1/t_{RC}$	100 MHz	90		90		-	mA
			83 MHz	80		80		95	mA
			66 MHz	70		70		85	mA
			40 MHz	60		60		75	mA
I_{SB1}	Automatic CE Power Down Current —TTL Inputs	$\text{Max } V_{CC}, \overline{CE} \geq V_{IH}$ $V_{IN} \geq V_{IH}$ or $V_{IN} \leq V_{IL}, f = f_{MAX}$		20		20		15	mA
I_{SB2}	Automatic CE Power Down Current —CMOS Inputs	$\text{Max } V_{CC},$ $\overline{CE} \geq V_{CC} - 0.3V,$ $V_{IN} \geq V_{CC} - 0.3V,$ or $V_{IN} \leq 0.3V, f = 0$		10		10		15	mA

Note

5. Minimum voltage is -2.0V and $V_{IH}(\text{max}) = V_{CC} + 2V$ for pulse durations of less than 20 ns.

Capacitance^[6]


Parameter	Description	Test Conditions	Max	Unit
C _{IN}	Input Capacitance	T _A = 25°C, f = 1 MHz, V _{CC} = 3.3V	8	pF
C _{OUT}	I/O Capacitance		8	pF

Thermal Resistance^[6]


Parameter	Description	Test Conditions	FBGA Package	SOJ Package	TSOP II Package	Unit
Θ _{JA}	Thermal Resistance (Junction to Ambient)	Still Air, soldered on a 3 × 4.5 inch, four layer printed circuit board	27.89	57.91	50.66	°C/W
Θ _{JC}	Thermal Resistance (Junction to Case)		14.74	36.73	17.17	°C/W

AC Test Loads and Waveforms

The AC test loads and waveform diagram follows.^[7]




(a)



(b)

High-Z Characteristics



(c)

Notes

6. Tested initially and after any design or process changes that may affect these parameters.

7. AC characteristics (except High-Z) are tested using the load conditions shown in [AC Test Loads and Waveforms](#) (a). High-Z characteristics are tested for all speeds using the test load shown in (c).

AC Switching Characteristics Over the Operating Range^[8]

Parameter	Description	-10 (Industrial)		-10 (Automotive-A) ^[1]		-12 (Automotive-E) ^[1]		Unit
		Min	Max	Min	Max	Min	Max	
Read Cycle								
t _{power} ^[9]	V _{CC} (Typical) to the First Access	100		100		100		μs
t _{RC}	Read Cycle Time	10		10		12		ns
t _{AA}	Address to Data Valid		10		10		12	ns
t _{OHA}	Data Hold from Address Change	3		3		3		ns
t _{ACE}	$\overline{CE}$ LOW to Data Valid		10		10		12	ns
t _{DOE}	$\overline{OE}$ LOW to Data Valid		5		5		7	ns
t _{LZOE}	$\overline{OE}$ LOW to Low-Z	0		0		0		ns
t _{HZOE}	$\overline{OE}$ HIGH to High-Z ^[10, 11]		5		5		6	ns
t _{LZCE}	$\overline{CE}$ LOW to Low-Z ^[11]	3		3		3		ns
t _{HZCE}	$\overline{CE}$ HIGH to High-Z ^[10, 11]		5		5		6	ns
t _{PU}	$\overline{CE}$ LOW to Power Up	0		0		0		ns
t _{PD}	$\overline{CE}$ HIGH to Power Down		10		10		12	ns
t _{DBE}	Byte Enable to Data Valid		5		5		7	ns
t _{LZBE}	Byte Enable to Low-Z	0		0		0		ns
t _{HZBE}	Byte Disable to High-Z		6		6		6	ns
Write Cycle ^[12, 13]								
t _{WC}	Write Cycle Time	10		10		12		ns
t _{SCE}	$\overline{CE}$ LOW to Write End	7		7		8		ns
t _{AW}	Address Setup to Write End	7		7		8		ns
t _{HA}	Address Hold from Write End	0		0		0		ns
t _{SA}	Address Setup to Write Start	0		0		0		ns
t _{PWE}	$\overline{WE}$ Pulse Width	7		7		8		ns
t _{SD}	Data Setup to Write End	5		5		6		ns
t _{HD}	Data Hold from Write End	0		0		0		ns
t _{LZWE}	$\overline{WE}$ HIGH to Low-Z ^[11]	3		3		3		ns
t _{HZWE}	$\overline{WE}$ LOW to High-Z ^[10, 11]		5		5		6	ns
t _{BW}	Byte Enable to End of Write	7		7		8		ns


Notes

8. Test conditions assume signal transition time of 3 ns or less, timing reference levels of 1.5V, input pulse levels of 0 to 3.0V, and output loading of the specified I_{OL}/I_{OH} and 30-pF load capacitance.
9. t_{POWER} gives the minimum amount of time that the power supply should be at typical V_{CC} values until the first memory access is performed.
10. t_{HZOE} , t_{HZCE} , t_{HZBE} , and t_{HZWE} are specified with a load capacitance of 5 pF as in part (c) of [AC Test Loads and Waveforms](#). Transition is measured when the outputs enter a high impedance state.
11. At any given temperature and voltage condition, t_{HZCE} is less than t_{LZCE} , t_{HZOE} is less than t_{LZOE} , t_{HZBE} is less than t_{LZBE} , and t_{HZWE} is less than t_{LZWE} for any given device.

Data Retention Characteristics Over the Operating Range


Parameter	Description	Conditions ^[14]	Min	Max	Unit
V_{DR}	V_{CC} for Data Retention		2.0		V
I_{CCDR}	Data Retention Current	$V_{CC} = V_{DR} = 2.0V$, $\overline{CE} \geq V_{CC} - 0.3V$, $V_{IN} \geq V_{CC} - 0.3V$ or $V_{IN} \leq 0.3V$			
		Industrial		10	mA
		Auto-A ^[1]		10	mA
		Auto-E ^[1]		15	mA
$t_{CDR}^{[6]}$	Chip Deselect to Data Retention Time		0		ns
$t_R^{[15]}$	Operation Recovery Time		t_{RC}		ns

Data Retention Waveform





Switching Waveforms

Figure 4. Read Cycle No. 1^[16, 17]



Notes

12. The internal write time of the memory is defined by the overlap of $\overline{CE}$ LOW and $\overline{WE}$ LOW. $\overline{CE}$ and $\overline{WE}$ must be LOW to initiate a write and the transition of either of these signals can terminate the write. The input data setup and hold timing should be referenced to the leading edge of the signal that terminates the write.
13. The minimum write cycle time for Write Cycle No. 4 ($\overline{WE}$ controlled, $\overline{OE}$ LOW) is the sum of t_{HZWE} and t_{SD} .
14. No input may exceed $V_{CC} + 0.3V$.
15. Full device operation requires linear V_{CC} ramp from V_{DR} to $V_{CC(min.)} \geq 50 \mu s$ or stable at $V_{CC(min.)} \geq 50 \mu s$.
16. Device is continuously selected. $\overline{OE}$, $\overline{CE}$, BHE , and $BLE = V_{IL}$.
17. $\overline{WE}$ is HIGH for read cycle.

Switching Waveforms (continued)
Figure 5. Read Cycle No. 2 ($\overline{OE}$ Controlled)^[17, 18]

Figure 6. Write Cycle No. 1 ($\overline{CE}$ Controlled)^[19, 20]

Notes

 18. Address valid prior to or coincident with $\overline{CE}$ transition LOW.

 19. Data I/O is high impedance if $\overline{OE}$ or BHE and BLE = V_{IH} .

 20. If $\overline{CE}$ goes HIGH simultaneously with $\overline{WE}$ going HIGH, the output remains in a high impedance state.

Switching Waveforms (continued)

Figure 7. Write Cycle No. 2 ($\overline{\text{BLE}}$ or $\overline{\text{BHE}}$ Controlled)






Figure 8. Write Cycle No. 3 ($\overline{\text{WE}}$ Controlled, $\overline{\text{OE}}$ HIGH During Write)^[19, 20]



Note

21. During this period the I/Os are in the output state and input signals should not be applied.

Switching Waveforms (continued)

Figure 9. Write Cycle No. 4 ($\overline{WE}$ Controlled, $\overline{OE}$ LOW)

Truth Table

$\overline{CE}$	$\overline{OE}$	$\overline{WE}$	$\overline{BLE}$	$\overline{BHE}$	I/O ₀ –I/O ₇	I/O ₈ –I/O ₁₅	Mode	Power
H	X	X	X	X	High-Z	High-Z	Power Down	Standby (I_{SB})
L	L	H	L	L	Data Out	Data Out	Read All Bits	Active (I_{CC})
L	L	H	L	H	Data Out	High-Z	Read Lower Bits Only	Active (I_{CC})
L	L	H	H	L	High-Z	Data Out	Read Upper Bits Only	Active (I_{CC})
L	X	L	L	L	Data In	Data In	Write All Bits	Active (I_{CC})
L	X	L	L	H	Data In	High-Z	Write Lower Bits Only	Active (I_{CC})
L	X	L	H	L	High-Z	Data In	Write Upper Bits Only	Active (I_{CC})
L	H	H	X	X	High-Z	High-Z	Selected, Outputs Disabled	Active (I_{CC})


Ordering Information

Speed (ns)	Ordering Code	Package Diagram	Package Type	Operating Range
10	CY7C1041DV33-10BVI	51-85150	48-Ball VFBGA	Industrial
	CY7C1041DV33-10BVXI		48-Ball VFBGA (Pb-Free) Pinout - 1 ^[3]	
	CY7C1041DV33-10BVJXI		48-Ball VFBGA (Pb-Free) Pinout - 2 ^[3]	
	CY7C1041DV33-10VXI	51-85082	44-Pin (400-mil) Molded SOJ (Pb-Free)	
	CY7C1041DV33-10ZSXI	51-85087	44-Pin TSOP II (Pb-Free)	
10	CY7C1041DV33-10BVXA	51-85150	48-Ball VFBGA (Pb-Free) Pinout - 1 ^[3]	Automotive-A ^[1]
	CY7C1041DV33-10ZSXA	51-85087	44-Pin TSOP II (Pb-Free)	
12	CY7C1041DV33-12BVXE	51-85150	48-Ball VFBGA (Pb-Free) Pinout - 1 ^[3]	Automotive-E ^[1]
	CY7C1041DV33-12BVJXE		48-Ball VFBGA (Pb-Free) Pinout - 2 ^[3]	
	CY7C1041DV33-12VXE	51-85082	44-Pin (400-mil) Molded SOJ (Pb-Free)	
	CY7C1041DV33-12ZSXE	51-85087	44-Pin TSOP II (Pb-Free)	

Please contact your local Cypress sales representative for availability of these parts

Package Diagrams

Figure 10. 48-Ball VFBGA (6 x 8 x 1 mm) (51-85150)



Package Diagrams(continued)

Figure 11. 44-Pin (400-mil) Molded SOJ (51-85082)





Figure 12. 44-Pin TSOP II (51-85087)



Document History Page

Document Title: CY7C1041DV33 4 Mbit (256K x 16) Static RAM Document Number: 38-05473				
Rev.	ECN No.	Orig. of Change	Submission Date	Description of Change
**	201560	SWI	See ECN	Advance Data sheet for C9 IPP
*A	233729	RKF	See ECN	1.AC, DC parameters are modified as per EROS(Spec # 01-2165) 2.Pb-free offering in the 'Ordering information'
*B	351117	PCI	See ECN	Changed from Advance to Preliminary Removed 15 and 20 ns Speed bin Corrected DC voltage (min) value in maximum ratings section from - 0.5 to - 0.3V Redefined I _{CC} values for Com'l and Ind'l temperature ranges I _{CC} (Com'l): Changed from 100, 80 and 67 mA to 90, 80 and 75 mA for 8, 10 and 12ns speed bins respectively I _{CC} (Ind'l): Changed from 80 and 67 mA to 90 and 85 mA for 10 and 12ns speed bins respectively Added Static Discharge Voltage and latch-up current spec Added V _{IH(max)} spec in Note# 2 Changed Note# 4 on AC Test Loads Changed reference voltage level for measurement of Hi-Z parameters from ±500 mV to ±200 mV Added Data Retention Characteristics/Waveform and footnote # 11, 12 Added Write Cycle (WE Controlled, OE HIGH During Write) Timing Diagram Changed Package Diagram name from 44-Pin TSOP II Z44 to 44-Pin TSOP II ZS44 and from 44-Pin (400-mil) Molded SOJ V34 to 44-Pin (400-mil) Molded SOJ V44 Changed part names from Z to ZS in the Ordering Information Table Added 8 ns Product Information Added Pin-Free Ordering Information Shaded Ordering Information Table
*C	446328	NXR	See ECN	Converted from Preliminary to Final Removed -8 speed bin Removed Commercial Operating Range product information Included Automotive Operating Range product information Updated Thermal Resistance table Updated footnote #8 on High-Z parameter measurement Updated the ordering information and replaced Package Name column with Package Diagram in the Ordering Information Table
*D	480177	VKN	See ECN	Added -10BVI product ordering code in the Ordering Information table
*E	2541850	VKN/PYRS	07/22/08	Added -10BVJXI part
*F	2752971	VKN	08/18/2009	Added Automotive-A information For 12 ns speed, changed I _{SB1} spec from 25 mA to 15 mA For 12 ns speed, changed t _{DOE} and t _{DBE} specs from 6 ns to 7 ns Updated ordering information table

Sales, Solutions, and Legal Information

Worldwide Sales and Design Support

Cypress maintains a worldwide network of offices, solution centers, manufacturer's representatives, and distributors. To find the office closest to you, visit us at cypress.com/sales.

Products

PSoC	psoc.cypress.com
Clocks & Buffers	clocks.cypress.com
Wireless	wireless.cypress.com
Memories	memory.cypress.com
Image Sensors	image.cypress.com

© Cypress Semiconductor Corporation, 2004-2009. The information contained herein is subject to change without notice. Cypress Semiconductor Corporation assumes no responsibility for the use of any circuitry other than circuitry embodied in a Cypress product. Nor does it convey or imply any license under patent or other rights. Cypress products are not warranted nor intended to be used for medical, life support, life saving, critical control or safety applications, unless pursuant to an express written agreement with Cypress. Furthermore, Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress products in life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Any Source Code (software and/or firmware) is owned by Cypress Semiconductor Corporation (Cypress) and is protected by and subject to worldwide patent protection (United States and foreign), United States copyright laws and international treaty provisions. Cypress hereby grants to licensee a personal, non-exclusive, non-transferable license to copy, use, modify, create derivative works of, and compile the Cypress Source Code and derivative works for the sole purpose of creating custom software and or firmware in support of licensee product to be used only in conjunction with a Cypress integrated circuit as specified in the applicable agreement. Any reproduction, modification, translation, compilation, or representation of this Source Code except as specified above is prohibited without the express written permission of Cypress.

Disclaimer: CYPRESS MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARD TO THIS MATERIAL, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Cypress reserves the right to make changes without further notice to the materials described herein. Cypress does not assume any liability arising out of the application or use of any product or circuit described herein. Cypress does not authorize its products for use as critical components in life-support systems where a malfunction or failure may reasonably be expected to result in significant injury to the user. The inclusion of Cypress' product in a life-support systems application implies that the manufacturer assumes all risk of such use and in doing so indemnifies Cypress against all charges.

Use may be limited by and subject to the applicable Cypress software license agreement.