


Fast Switching SCR T607-18

175A Avg.
(275 RMS)
Up to 1200 Volts
10-50 μ s



Conforms to TO-93 Outline

Features:

- Center fire, di/namic gate
- High di/dt with soft gate control
- High frequency operation
- Sinusoidal waveform operation to 20 KHz
- Rectangular waveform operation to 20 KHz
- Low dynamic forward voltage drop
- Low switching losses at high frequency
- Westinghouse Lifetime Guarantee

Symbol	Inches		Millimeters	
	Min.	Max.	Min.	Max.
A	7.750	8.100	196.85	205.74
A ₁	7.750	8.100	196.85	205.74
B	.063	.172	1.60	4.37
ϕ D	.980	1.090	24.89	27.69
E	1.212	1.250	30.78	31.75
F	.250	.630	6.35	16.00
J	3.25		82.55	
M	.530	.755	13.46	19.18
N	1.040	1.077	26.42	27.36
Q		2.250		57.15
ϕ T	.260	.290	6.60	7.37
Z	.340		8.64	
ϕ W	¼-16 UNF-2A			

Creep Distance—.75 in. min. (19.05 mm).

Strike Distance—.69 in. min. (17.53 mm).

(In accordance with NEMA standards.)


Finish—Nickel Plate.

Approx. Weight—8 oz. (227 g).

1. Complete threads to extend to within 2½ threads of seating plane.
2. Angular orientation of terminals is undefined.
3. Pitch diameter of ¼-16 UNF-2A (coated) threads (ASA B1.1—1960).
4. Dimension "J" denotes seated height with leads bent at right angles.

Applications:

- Inverters for UPS
- AC motor control
- Induction heating
- Cycloconverters
- Choppers



Ordering Information

Type	Voltage		Current		Turn-off		Gate Current		Leads	
Code	V _{DRM} and V _{RRM} (V)	Code	I _{T(av)} (A)	Code	t _q μ sec	Code	I _{GT} (ma)	Code	Case	Code
T607	100	01	175	18	10	8	150	4	TO-93	BT
	200	02			15					
	300	03			20					
	400	04			25					
	500	05			30					
	600	06			40					
	700	07			50					
	800	08								
	900	09								
	1000	10								
	1100	11								
	1200	*12								

Example

Obtain optimum device performance for your application by selecting proper Order Code.

Type T 607 rated at 175A average with V_{DRM} = 1000V, I_{GT} = 150 ma, t_q = 30 μ sec and standard flex lead — order as

*for 10 μ sec turn-off, consult factory

Type	Voltage	Current	Turn Off	Gate Current	Leads
T 6 0 7	1 0	1 8	5	4	B T

**175A Avg.
(275 RMS)
Up to 1200 Volts
10-50 μ s**

Fast Switching SCR T607_18

Voltage

Blocking State Maximums $\textcircled{1}$ ($T_J = 125^\circ\text{C}$)

Repetitive peak forward blocking voltage, V ...
Repetitive peak reverse voltage, V ...
Non-repetitive transient peak reverse voltage,
 $t \leq 5.0$ m sec, V

Symbol

V_{DRM}	100	200	300	400	500	600	700	800	900	1000	1100	1200
V_{RRM}	100	200	300	400	500	600	700	800	900	1000	1100	1200
V_{RSM}	200	300	400	500	600	700	800	900	1000	1100	1200	1300

Forward leakage current, mA peak
Reverse leakage current, mA peak

I_{DRM}

25

I_{RRM}

25

Current

Conducting State Maximums
($T_J = 125^\circ\text{C}$)

Symbol

T607_18

RMS forward current, A
Ave. forward current, A
One-half cycle surge current $\textcircled{3}$, A ...
 I_{2t} for fusing (for times ≥ 8.3 ms),
A 2 -sec.
Forward voltage drop at $I_{TM} = 625$ A
and $T_J = 25^\circ\text{C}$, V
Min. repetitive di/dt $\textcircled{1} \textcircled{4} \textcircled{5}$, A/ μ sec ...

$I_{T(rms)}$

275

$I_{T(av)}$

175

I_{TSM}

4500

I_{2t}

84,000

V_{TM}

1.85

di/dt

300

Switching

($T_J = 25^\circ\text{C}$)

Symbol

Max. turn-off time, $I_T = 150$ A,
 $T_J = 125^\circ\text{C}$, $di/dt = 12.5$
A/ μ sec, reapplied $dv/dt =$
20V/ μ sec linear to .8V V_{DRM} , μ sec $\textcircled{5} \textcircled{7}$.
Typ. turn-on-time, $I_T = 100$ A
 $V_D = 100$ V $\textcircled{4}$, μ sec
Min. critical dv/dt , exponential to V_{DRM} ,
 $T_J = 125^\circ\text{C}$, V/ μ sec $\textcircled{2} \textcircled{6}$.
Min. di/dt non-repetitive,
 $\textcircled{1} \textcircled{4} \textcircled{5}$, A/ μ sec

t_q

10 to 50

t_{on}

3.5

dv/dt

300

di/dt

800

Gate

Maximum Parameters
($T_J = 25^\circ\text{C}$)

Symbol

Gate current to trigger at $V_D = 12$ V, mA
Gate voltage to trigger at $V_D = 12$ V, V ...
Non-triggering gate voltage, $T_J = 125^\circ\text{C}$,
and rated V_{DRM} , V
Peak forward gate current, A
Peak reverse gate voltage, V
Peak gate power, Watts
Average gate power, Watts

I_{GT}

150

V_{GT}

3

V_{GDM}

0.15

I_{GTM}

4

V_{GRM}

5

P_{GM}

16

$P_{G(av)}$

3

Thermal and Mechanical

Symbol

Min., Max. oper. junction temp., $^\circ\text{C}$
Min., Max. storage temp., $^\circ\text{C}$
Max. mounting torque, in lb. $\textcircled{1}$
Max. Thermal resistance $\textcircled{1}$
Junction to case, $^\circ\text{C}/\text{Watt}$
Case to sink, lubricated, $^\circ\text{C}/\text{Watt}$

T_J

-40 to +125

T_{stg}

-40 to +150

$R_{\theta JC}$

300



$R_{\theta CS}$

.13

$R_{\theta CS}$

.08


- $\textcircled{1}$ Consult recommended mounting procedures.
- $\textcircled{2}$ Applies for zero or negative gate bias.
- $\textcircled{3}$ Per JEDEC RS-397, 5.2.2.1.
- $\textcircled{4}$ With recommended gate drive.
- $\textcircled{5}$ Higher dv/dt ratings available, consult factory.
- $\textcircled{6}$ Per JEDEC standard RS-397, 5.2.2.6.
- $\textcircled{7}$ For operation with antiparallel diode, consult factory.




Fast Switching SCR T607-18

175A Avg.
(275 RMS)
Up to 1200 Volts
10-50 μ s


Sinusoidal Current Data



ENERGY PER PULSE FOR SINUSOIDAL PULSES




MAXIMUM ALLOWABLE PEAK ON-STATE CURRENT
vs. PULSE WIDTH ($T_C = 65^\circ\text{C}$)




MAXIMUM ALLOWABLE PEAK ON-STATE CURRENT
vs. PULSE WIDTH ($T_C = 90^\circ\text{C}$)


Trapezoidal Wave Current Data



ENERGY PER PULSE FOR TRAPEZOIDAL PULSES
($di/dt = 50\text{A/usec}$)



ENERGY PER PULSE FOR TRAPEZOIDAL PULSES
($di/dt = 100\text{A/usec}$)




ENERGY PER PULSE FOR TRAPEZOIDAL PULSES
($di/dt = 200\text{A/usec}$)

175A Avg.
(275 RMS)
Up to 1200 Volts
10-50 μ s


Fast Switching
SCR
T607_18

Trapezoidal Wave Current Data ($T_C = 65^\circ\text{C}$)




MAXIMUM ALLOWABLE PEAK ON-STATE CURRENT vs. PULSE WIDTH ($dI/dt = 50\text{A}/\mu\text{sec}$)


Trapezoidal Wave Current Data ($T_C = 90^\circ\text{C}$)




MAXIMUM ALLOWABLE PEAK ON-STATE CURRENT vs. PULSE WIDTH ($dI/dt = 50\text{A}/\mu\text{sec}$)




MAXIMUM ALLOWABLE PEAK ON-STATE CURRENT vs. PULSE WIDTH ($dI/dt = 100\text{A}/\mu\text{sec}$)




MAXIMUM ALLOWABLE PEAK ON-STATE CURRENT vs. PULSE WIDTH ($dI/dt = 100\text{A}/\mu\text{sec}$)



MAXIMUM ALLOWABLE PEAK ON-STATE CURRENT vs. PULSE WIDTH ($dI/dt = 200\text{A}/\mu\text{sec}$)



MAXIMUM ALLOWABLE PEAK ON-STATE CURRENT vs. PULSE WIDTH ($dI/dt = 200\text{A}/\mu\text{sec}$)



CASE NUMBER T60
NOMINAL DIMENSIONS

STRIKE DISTANCE = .65 INCH / 16.5 MM MIN.
CREEPAGE DISTANCE = .65 INCH / 16.5 MM MIN.

SYM.	A	B	C	D	E	F	G	H	J	K
INCHES	1.06	.55	1.50	2.25	1.07	7.91	.63	.281	7.91	.146
MM	26.9	14.0	38.1	57.2	27.2	200.9	16.0	7.14	200.9	3.71

ALL DIMENSIONS ARE REFERENCE