

## NC7ST04 TinyLogic® HST Inverter

### General Description

The NC7ST04 is a single high performance CMOS Inverter, with TTL-compatible inputs. Advanced Silicon Gate CMOS fabrication assures high speed and low power circuit operation. ESD protection diodes inherently guard both input and output with respect to the  $V_{CC}$  and GND rails. High gain circuitry offers high noise immunity and reduced sensitivity to input edge rate. The TTL-compatible input facilitates TTL to NMOS/CMOS interfacing. Device performance is similar to MM74HCT but with  $\frac{1}{2}$  the output current drive of HC/HCT.


### Features

- Space saving SOT23 or SC70 5-lead package
- Ultra small MicroPak™ leadless package
- High Speed;  $t_{PD} < 7$  ns typ,  $V_{CC} = 5V$ ,  $C_L = 15$  pF
- Low Quiescent Power;  $I_{CC} < 1$   $\mu A$  typ,  $V_{CC} = 5.5V$
- Balanced Output Drive; 2 mA  $I_{OL}$ , -2 mA  $I_{OH}$
- TTL-compatible inputs

### Ordering Code:

| Order Number | Package Number | Product Code Top Mark | Package Description                   | Supplied As               |
|--------------|----------------|-----------------------|---------------------------------------|---------------------------|
| NC7ST04M5X   | MA05B          | 8S04                  | 5-Lead SOT23, JEDEC MO-178, 1.6mm     | 3k Units on Tape and Reel |
| NC7ST04P5X   | MAA05A         | T04                   | 5-Lead SC70, EIAJ SC-88a, 1.25mm Wide | 3k Units on Tape and Reel |
| NC7ST04L6X   | MAC06A         | XX                    | 6-Lead MicroPak, 1.0mm Wide           | 5k Units on Tape and Reel |

### Logic Symbol



### Pin Descriptions

| Pin Names | Description |
|-----------|-------------|
| A         | Input       |
| Y         | Output      |
| NC        | No Connect  |

### Function Table


$$Y = \overline{A}$$

| Input | Output |
|-------|--------|
| A     | Y      |
| L     | H      |
| H     | L      |


H = HIGH Logic Level  
L = LOW Logic Level

### Connection Diagrams

#### Pin Assignments for SC70 and SOT23



#### Pad Assignments for MicroPak



TinyLogic® is a registered trademark of Fairchild Semiconductor Corporation.  
MicroPak™ is a trademark of Fairchild Semiconductor Corporation.

**Absolute Maximum Ratings** (Note 1)

|                                                                        |                          |
|------------------------------------------------------------------------|--------------------------|
| Supply Voltage ( $V_{CC}$ )                                            | -0.5V to +7.0V           |
| DC Input Diode Current ( $I_{IK}$ )                                    |                          |
| $V_{IN} < -0.5V$                                                       | -20 mA                   |
| $V_{IN} \geq V_{CC} + 0.5V$                                            | +20 mA                   |
| DC Input Voltage ( $V_{IN}$ )                                          | -0.5V to $V_{CC} + 0.5V$ |
| DC Output Diode Current ( $I_{OK}$ )                                   |                          |
| $V_{OUT} < -0.5V$                                                      | -20 mA                   |
| $V_{OUT} > V_{CC} + 0.5V$                                              | +20 mA                   |
| Output Voltage ( $V_{OUT}$ )                                           | -0.5V to $V_{CC} + 0.5V$ |
| DC Output Source or Sink Current ( $I_{OUT}$ )                         | $\pm 12.5$ mA            |
| DC $V_{CC}$ or Ground Current per Supply Pin ( $I_{CC}$ or $I_{GND}$ ) | $\pm 25$ mA              |
| Storage Temperature ( $T_{STG}$ )                                      | -65°C to +150°C          |
| Junction Temperature ( $T_J$ )                                         | 150°C                    |
| DC $V_{CC}$ or Ground Current per (Soldering, 10 seconds)              | 260°C                    |
| Power Dissipation ( $P_D$ ) @ +85°C                                    |                          |
| SOT23-5                                                                | 200 mW                   |
| SC70-5                                                                 | 150 mW                   |

**Recommended Operating Conditions** (Note 2)

|                                         |                |
|-----------------------------------------|----------------|
| Supply Voltage                          | 4.5V–5.5V      |
| Input Voltage ( $V_{IN}$ )              | 0V– $V_{CC}$   |
| Output Voltage ( $V_{OUT}$ )            | 0V– $V_{CC}$   |
| Operating Temperature ( $T_A$ )         | -40°C to +85°C |
| Input Rise and Fall Time ( $t_r, t_f$ ) |                |
| $V_{CC} = 5.0V$                         | 0–500 ns       |
| Thermal Resistance ( $\theta_{JA}$ )    |                |
| SOT23-5                                 | 300°C/W        |
| SC70-5                                  | 425°C/W        |

**Note 1:** Absolute Maximum Ratings are those values beyond which damage to the device may occur. The databook specifications should be met, without exception, to ensure that the system design is reliable over its power supply, temperature, and output/input loading variables. Fairchild does not recommend operation of circuits outside the databook specifications.

**Note 2:** Unused inputs must be held HIGH or LOW. They may not float.

**DC Electrical Characteristics**


| Symbol    | Parameter                 | $V_{CC}$<br>(V) | $T_A = +25^\circ\text{C}$ |      |           | $T_A = -40^\circ\text{C to } +85^\circ\text{C}$ |           | Units         | Conditions                                  |
|-----------|---------------------------|-----------------|---------------------------|------|-----------|-------------------------------------------------|-----------|---------------|---------------------------------------------|
|           |                           |                 | Min                       | Typ  | Max       | Min                                             | Max       |               |                                             |
| $V_{IH}$  | HIGH Level Input Voltage  | 4.5–5.5         | 2.0                       |      |           | 2.0                                             |           | V             |                                             |
| $V_{IL}$  | LOW Level Input Voltage   | 4.5–5.5         |                           |      | 0.8       |                                                 | 0.8       | V             |                                             |
| $V_{OH}$  | HIGH Level Output Voltage | 4.5             | 4.4                       | 4.5  |           | 4.4                                             |           | V             | $I_{OH} = -20 \mu\text{A}, V_{IN} = V_{IL}$ |
|           |                           | 4.5             | 4.18                      | 4.35 |           | 4.13                                            |           | V             | $I_{OH} = -2 \text{ mA}$                    |
| $V_{OL}$  | LOW Level Output Voltage  | 4.5             |                           | 0    | 0.1       |                                                 | 0.1       | V             | $I_{OL} = 20 \mu\text{A}, V_{IN} = V_{IH}$  |
|           |                           | 4.5             |                           | 0.10 | 0.26      |                                                 | 0.33      | V             | $I_{OL} = 2 \text{ mA}$                     |
| $I_{IN}$  | Input Leakage Current     | 5.5             |                           |      | $\pm 0.1$ |                                                 | $\pm 1.0$ | $\mu\text{A}$ | $0 \leq V_{IN} \leq 5.5V$                   |
| $I_{CC}$  | Quiescent Supply Current  | 5.5             |                           |      | 1.0       |                                                 | 10.0      | $\mu\text{A}$ | $V_{IN} = V_{CC}$ or GND                    |
| $I_{CCT}$ | $I_{CC}$ per Input        | 5.5             |                           |      | 2.0       |                                                 | 2.9       | mA            | Input $V_{IN} = 0.5V$ or 2.4V               |

## AC Electrical Characteristics

| Symbol                                 | Parameter                     | V <sub>CC</sub><br>(V) | T <sub>A</sub> = +25°C |      |     | T <sub>A</sub> = −40°C to +85°C |     | Units | Conditions             | Figure Number |
|----------------------------------------|-------------------------------|------------------------|------------------------|------|-----|---------------------------------|-----|-------|------------------------|---------------|
|                                        |                               |                        | Min                    | Typ  | Max | Min                             | Max |       |                        |               |
| t <sub>PLH</sub> ,<br>t <sub>PHL</sub> | Propagation Delay             | 5.0                    |                        | 3.5  | 12  |                                 |     | ns    | C <sub>L</sub> = 15 pF | Figures 1, 3  |
|                                        |                               |                        |                        | 6.0  | 17  |                                 |     |       |                        |               |
|                                        |                               | 4.5                    |                        | 6.2  | 16  |                                 | 20  | ns    | C <sub>L</sub> = 50 pF |               |
|                                        |                               |                        |                        | 11.4 | 27  |                                 | 31  |       |                        |               |
|                                        |                               | 5.5                    |                        | 4.3  | 14  |                                 | 18  |       |                        |               |
|                                        |                               |                        |                        | 11.1 | 26  |                                 | 30  |       |                        |               |
| t <sub>TLH</sub> ,<br>t <sub>THL</sub> | Output Transition Time        | 5.0                    |                        | 4    | 10  |                                 |     | ns    | C <sub>L</sub> = 15 pF | Figures 1, 3  |
|                                        |                               | 4.5                    |                        | 11   | 25  |                                 | 31  | ns    | C <sub>L</sub> = 50 pF |               |
|                                        |                               | 5.5                    |                        | 10   | 21  |                                 | 26  |       |                        |               |
| C <sub>IN</sub>                        | Input Capacitance             | Open                   |                        | 2    | 10  |                                 |     | pF    |                        |               |
| C <sub>PD</sub>                        | Power Dissipation Capacitance | 5.0                    |                        | 6    |     |                                 |     | pF    | (Note 3)               | Figure 2      |


**Note 3:** C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is derived from dynamic operating current consumption (I<sub>CCD</sub>) at no output loading and operating at 50% duty cycle. (See Figure 2.) C<sub>PD</sub> is related to I<sub>CCD</sub> dynamic operating current by the expression:  
 $I_{CCD} = (C_{PD})(V_{CC})(f_{IN}) + (I_{CCstatic})$ .

## AC Loading and Waveforms



C<sub>L</sub> includes load and stray capacitance  
 Input PRR = 1.0 MHz, t<sub>w</sub> = 500 ns

FIGURE 1. AC Test Circuit



Input = AC Waveform; PRR = Variable; Duty Cycle = 50%

FIGURE 2. I<sub>CCD</sub> Test Circuit





FIGURE 3. AC Waveforms

## Tape and Reel Specification

### TAPE FORMAT for SC70 and SOT23

| Package Designator | Tape Section       | Number Cavities | Cavity Status | Cover Tape Status |
|--------------------|--------------------|-----------------|---------------|-------------------|
| M5X, P5X           | Leader (Start End) | 125 (typ)       | Empty         | Sealed            |
|                    | Carrier            | 3000            | Filled        | Sealed            |
|                    | Trailer (Hub End)  | 75 (typ)        | Empty         | Sealed            |

### TAPE DIMENSIONS inches (millimeters)



| Package | Tape Size | DIM A           | DIM B           | DIM F                         | DIM K <sub>0</sub>             | DIM P1       | DIM W                      |
|---------|-----------|-----------------|-----------------|-------------------------------|--------------------------------|--------------|----------------------------|
| SC70-5  | 8 mm      | 0.093<br>(2.35) | 0.096<br>(2.45) | 0.138 ± 0.004<br>(3.5 ± 0.10) | 0.053 ± 0.004<br>(1.35 ± 0.10) | 0.157<br>(4) | 0.315 ± 0.004<br>(8 ± 0.1) |
| SOT23-5 | 8 mm      | 0.130<br>(3.3)  | 0.130<br>(3.3)  | 0.138 ± 0.002<br>(3.5 ± 0.05) | 0.055 ± 0.004<br>(1.4 ± 0.11)  | 0.157<br>(4) | 0.315 ± 0.012<br>(8 ± 0.3) |


# Tape and Reel Specification (Continued)

## TAPE FORMAT for MicroPak


| Package Designator | Tape Section       | Number Cavities | Cavity Status | Cover Tape Status |
|--------------------|--------------------|-----------------|---------------|-------------------|
| L6X                | Leader (Start End) | 125 (typ)       | Empty         | Sealed            |
|                    | Carrier            | 5000            | Filled        | Sealed            |
|                    | Trailer (Hub End)  | 75 (typ)        | Empty         | Sealed            |




## REEL DIMENSIONS inches (millimeters)



| Tape Size | A              | B               | C                | D                | N                | W1                                          | W2               | W3                                     |
|-----------|----------------|-----------------|------------------|------------------|------------------|---------------------------------------------|------------------|----------------------------------------|
| 8 mm      | 7.0<br>(177.8) | 0.059<br>(1.50) | 0.512<br>(13.00) | 0.795<br>(20.20) | 2.165<br>(55.00) | 0.331 + 0.059/-0.000<br>(8.40 + 1.50/-0.00) | 0.567<br>(14.40) | W1 + 0.078/-0.039<br>(W1 + 2.00/-1.00) |



- A) THIS PACKAGE CONFORMS TO JEDEC MO-178, ISSUE B, VARIATION AA, DATED JANUARY 1999.
- B) ALL DIMENSIONS ARE IN MILLIMETERS.




DETAIL A

5-Lead SOT23, JEDEC MO-178, 1.6mm  
Package Number MA05B

MA05BRevC

**Physical Dimensions** inches (millimeters) unless otherwise noted (Continued)




**NOTES:**

- A. CONFORMS TO EIAJ REGISTERED OUTLINE DRAWING SC88A.
- B. DIMENSIONS DO NOT INCLUDE BURRS OR MOLD FLASH.
- C. DIMENSIONS ARE IN MILLIMETERS.

MAA05ARevC

**5-Lead SC70, EIAJ SC-88a, 1.25mm Wide  
Package Number MAA05A**

# Physical Dimensions inches (millimeters) unless otherwise noted (Continued)



## Notes:

1. JEDEC PACKAGE REGISTRATION IS ANTICIPATED
2. DIMENSIONS ARE IN MILLIMETERS
3. DRAWING CONFORMS TO ASME Y14.5M-1994

MAC06ARevB

## 6-Lead MicroPak, 1.0mm Wide Package Number MAC06A

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

[www.fairchildsemi.com](http://www.fairchildsemi.com)