





8 WIRE

Pin No.	Wire
1	White
2	Brown
3	Green
4	Yellow
5	Grey
6	Pink
7	Blue
8	Red

PART No MATRIX

8	0	8	0	0	0	P	0	2	X	X	X	X	X	X	
8=Micro Change	0=Portable	8=8 Core	000 = Female Straight			Cable-PUR, 8 x 0.25mm			M=Metres F=Feet	LENGTH 020=2 METRES 050=5 METRES 200=20 METRES				Coupling Nut Material Blank=Standard 1=Stainless Steel 5=Delrin	

OPTIONS

X	X
Blank=Yellow (Standard) A=Grey	

Specification.

(See alternative variations in matrix key)
Insert Material - PUR (30% Glass Filled)
Contact Material - Brass (CuZn36)
Contact Plating - 2um Ni, 0.70um Gold
Coupling Nuts - Nickel Plated Brass
Seal - Viton O-Ring
Protection Class - IP68
Voltage Rating - 30 VAC / 36 VDC
Contact Current Rating - 4 Amps
Overmoulding - PUR

N/A	A	GG	First Issue	13.05.04	GG	
ECN	Rev	By	Descriptions	Date	Approved	

Third Angle Projection

This drawing and its contents are the proprietary and confidential property of Woodhead Industries Inc. and/or its subsidiaries and may not be used or disclosed to others without the express prior written consent of Woodhead Industries Inc. and/or its subsidiaries.

Applicable Standards	ASME Y14.5M ISO 1660	
Drawn	G.GREEN	13.05.04
Checked	N.WITTS	13.05.04
Approved	N.WITTS	13.05.04
Material	SEE SPECIFICATION	
Finish	SEE SPECIFICATION	

Dimensions In MM
0.0 ± 0.25mm
0.00 ± 0.10mm
0.000 ± 0.025mm
Angles ± 1°

Part No.	808000P02MXXX	Size	A4
Description	MICRO CHANGE 80 SERIES CONNECTOR LEAD		
Drawing No.	808000P02MXXX	Rev	A
Scale	NTS	SHEET 1 OF 1	