

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [0015800083](#)  
**Status:** **Active**  
**Overview:** [C-Grid Connector Products](#)  
**Description:** 2.54mm Pitch C-Grid Header, Through Hole without Peg, Dual Row, Vertical, Shrouded, High Temperature, 8 Circuits, 0.38µm Gold (Au) Selective Plating, Tin (Sn) PC Tail Plating

|                                |                                                                 |
|--------------------------------|-----------------------------------------------------------------|
| <b>Documents:</b>              |                                                                 |
| <a href="#">3D Model</a>       | <a href="#">Product Specification PS-70567-001 (PDF)</a>        |
| <a href="#">3D Model (PDF)</a> | <a href="#">Packaging Specification PK-70873-0018-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a>            |

**Agency Certification**


|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                                           |
|----------------|-------------------------------------------|
| Product Family | PCB Headers                               |
| Series         | <a href="#">70567</a>                     |
| Application    | Signal, Wire-to-Board                     |
| Overview       | <a href="#">C-Grid Connector Products</a> |
| Product Name   | C-Grid                                    |
| UPC            | 800754210812                              |

**Physical**

|                                |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | No                             |
| Circuits (Loaded)              | 8                              |
| Circuits (maximum)             | 8                              |
| Color - Resin                  | Black                          |
| First Mate / Last Break        | No                             |
| Flammability                   | 94V-0                          |
| Glow-Wire Capable              | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | None                           |
| Lock to Mating Part            | Yes                            |
| Material - Metal               | Brass, Phosphor Bronze         |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 1.590/g                        |
| Number of Rows                 | 2                              |
| Orientation                    | Vertical                       |
| PC Tail Length                 | 3.30mm                         |
| PCB Locator                    | No                             |
| PCB Retention                  | Yes                            |
| PCB Thickness - Recommended    | 2.40mm                         |
| Packaging Type                 | Tube                           |
| Pitch - Mating Interface       | 2.54mm                         |
| Pitch - Termination Interface  | 2.54mm                         |
| Plating min - Mating           | 0.381µm                        |
| Plating min - Termination      | 1.905µm                        |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | No                             |
| Shrouded                       | Fully                          |
| Stackable                      | No                             |
| Surface Mount Compatible (SMC) | No                             |
| Temperature Range - Operating  | -55° to +105°C                 |



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

**China RoHS**

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[70567 Series](#)

**Mates With**

SL Crimp Housing [70450](#) , C-Grid PCB  
Receptacle [71395](#)

|                                                |                    |
|------------------------------------------------|--------------------|
| Termination Interface: Style                   | Through Hole       |
| <b>Electrical</b>                              |                    |
| Current - Maximum per Contact                  | 2.5A               |
| Voltage - Maximum                              | 250V               |
| <b>Solder Process Data</b>                     |                    |
| Duration at Max. Process Temperature (seconds) | 005                |
| Lead-freeProcess Capability                    | SMC&WAVE           |
| Max. Cycles at Max. Process Temperature        | 001                |
| Process Temperature max. C                     | 245                |
| <b>Material Info</b>                           |                    |
| Engineering Number                             | A-70567-0070       |
| <b>Reference - Drawing Numbers</b>             |                    |
| Packaging Specification                        | PK-70873-0018-001  |
| Product Specification                          | PS-70567-001       |
| Sales Drawing                                  | SDA-70567-XXXX-001 |

This document was generated on 12/14/2021

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-80-0083