

MATERIALS AND FINISHES

BODY: BRASS
PLATED: SEE TABULATION


OUTER CONTACT: COPPER ALLOY
PLATED: SEE TABULATION

CENTER CONTACT: BRASS
PLATED: GOLD

INSULATOR: TEFLON

CAP: BRASS
PLATED: SEE TABULATION

CRIMP TUBE: BRASS
PLATED: SEE TABULATION



73415-2391	AS89678-2500	ASSEMBLY INSTRUCTIONS	GOLD PLATING (10 MICRO-INCH MIN)
------------	--------------	-----------------------	----------------------------------

73415-2390	AS89678-2500	ASSEMBLY INSTRUCTIONS	NICKEL PLATING
------------	--------------	-----------------------	----------------

PART NUMBER	SPECIFICATION	DESCRIPTION	FINISH
-------------	---------------	-------------	--------

CHG: NEW RELEASE EC NO. URF-0817 DRWN: LMB 08/30/00 CHK: SSS 08/30/00 APPR: GMH 08/30/00	CHG: ADDED PART -2391 & TABULATION CHART DRWN: LMB 08/24/00 CHK: TEF 08/24/00 CHG: XXXXX	EC NO. URF-XXXX DRWN: XXX 00/00/00 CHK: XXX 00/00/00 APPR: XXX 00/00/00	DESCRIPTION REV
A	2	1	

UNLESS OTHERWISE SPECIFIED DIMS ARE INCHES AND ANGLES ARE DEGREES.

1. $\sqrt{63}$ ALL OVER.
2. NO CHATTER OR NON-UNIFORM SURFACE FINISH ALLOWED.
3. PARTS TO BE FREE OF BURRS & SHARP EDGES .005 MAX BREAK.
4. EXTERNAL THREADS TO BE ROLLED OR SINGLE POINT.
5. DIAMETERS TO BE CONCENTRIC WITHIN .003 TIR.

QUALITY SYMBOLS

MAJOR

CRITICAL

C

GENERAL TOLERANCES: (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .0005	± .0005
3 PLACES	± .001	± .001
2 PLACES	± .01	± .01
1 PLACE	± .1	± .1
ANGULAR: ±2°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

SCALE

DESIGN UNITS

☐ mm ☒ INCH

THIRD ANGLE PROJECTION

DIMENSIONS:

☐ mm ☒ INCH ☐ mm ONLY

1	A
SHT	REV
REVISE ON CAD ONLY	

DRAWN BY & DATE

GMH 7/28/00

CHECKED BY & DATE

XXX 00/00/00

APPROVED BY & DATE

XXX 00/00/00

CAD FILENAME

TITLE:
MCX R/A 75 OHM PLUG FOR RD179
MCX-PC/RA

MOLEX INCORPORATED

MATERIAL NO.

SEE NOTE

DRAWING NO.

SD-73415-239

SHEET NO.

1 of 1

SIZE

B