



LOC	DIST	REVISIONS				
CM	0	P	LTR	DESCRIPTION	DATE	APVD
			N2	REVISED PER ECR-15-015654	27JAN2016	GJ



- 1


0.00076 MIN GOLD PLATING IN THIS AREA WITH 0.00381 MIN MATTE TIN LEAD ON THE REMAINDER, BOTH OVER 0.00127 MIN NICKEL UNDERPLATE.
- 2

FITS 1.17 – 1.27 DIAMETER HOLE IN A 1.57 OR 2.39 PRINTED CIRCUIT BOARD.
- 3

PARTS TO COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 4

0.05-0.25 DIAMETER OPENING REQUIRED IN TIP OF PIN.
- 5

0.00076 MIN GOLD PLATING IN THIS AREA WITH 0.00381 MIN MATTE TIN ON THE REMAINDER, BOTH OVER 0.00127 MIN NICKEL UNDERPLATE.



0.13	.005	1.27	.050	2.29	.090	—	—
0.05	.002	1.17	.046	2.16	.085	—	—
0.00381	.000150	1.02	.040	1.57	.062	10.16	.400
0.00127	.000050	0.51	.020	1.52	.060	4.06	.160
0.00076	.000030	0.25	.010	1.47	.058	2.39	.094
MM	IN	MM	IN	MM	IN	MM	IN
CONVERSION TABLE							

SUPERSEDED BY 3-61067-1	5	3-61067-1
	1	61067-1
	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK 8-22-97	TE Connectivity			
DIMENSIONS: mm		CHK R. SWING 8-22-97				
		APVD A. BEDDICK 9-10-97	NAME			
		PRODUCT SPEC 108-1025	PIN, .058 DIAMETER, PHOSPHER BRONZE, PRESS FIT, LOOSE PIECE, P.C. CONTACT			
MATERIAL 0.25 PH BRZ		APPLICATION SPEC 114-1008	SIZE A2	CAGE CODE 00779	DRAWING NO C-61067	RESTRICTED TO —
FINISH SEE TABLE		WEIGHT —	CUSTOMER DRAWING		SCALE 15:1	SHEET 1 of 1
				REV N2		