

4




3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DW		G4	REVISED (ECR-13-017389)	01JUL14	BW SC



- NOTES:
- MATERIAL:
 - HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 - SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 - CAP: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 - CONTACT: PHOSPHOR BRONZE.
 - FRONT SHIELD: BRASS.
 - REAR SHIELD: SPCC.
 - GROUNDING STRIP: BRASS.
 - FINISH:
 - CONTACT: 0.762μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
 - 3.048μm [120μ"] MIN. MATTE TIN PLATING ON SOLDER TAILS, WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
 - FRONT SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
 - 0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
 - REAR SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
 - 0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
 - GROUNDING STRIP: 0.762μm [30μ"] MIN. NICKEL PLATING.
 - 0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

DIM C	DIM B	DIM A	CAP	PACKAGE	PART NUMBER	NOTE
1.90	14.30	0	W/	TAPE & REEL	1734062-3	
2.20	13.95	0.35	W/O	TUBE	1734062-2	OBSOLETE
				TAPE & REEL	1734062-1	OBSOLETE

RECOMMEND P.C.B LAYOUT (THICKNESS 1.2~1.4mm)
(COMPONENT SIDE) TOLERANCE ±0.05mm






THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	F. YANG	10SEP2009	 TE Connectivity	NAME USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE
DIMENSIONS: MM		CHK	S. CHIEN	10SEP2009		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	W. KODAMA	10SEP2009		
0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC		108-57481		
MATERIAL		QUALIFICATION TEST REPORT		501-57557	SIZE	RESTRICTED TO
SEE NOTE		FINISH		SEE NOTE	A3	
		WEIGHT		4.71 GRAMS	CAGE CODE	
		CUSTOMER DRAWING			DRAWING NO	
					1734062	
					SCALE	
					SHEET	
					1 OF 24	
					REV	
					G4	

4

3

2

1



NOTE:

- MATERIAL:
 HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 CONTACT: PHOSPHOR BRONZE.
 FRONT SHIELD: BRASS.
 REAR SHIELD: SPCC.
 GROUNDING STRIP: BRASS.
- FINISH:
 CONTACT: 0.762μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
 3.048μm [120μ"] MIN. BRIGHT TIN PLATING ON SOLDER TAILS,
 WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
 FRONT SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
 REAR SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
 0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
 GROUNDING STRIP: 0.762μm [30μ"] MIN. NICKEL PLATING.
 0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
- REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

RECOMMEND P.C.B LAYOUT (THICKNESS 1.2~1.4mm)
 (COMPONENT SIDE) TOLERANCE ±0.05mm

RECOMMEND P.C.B LAYOUT (THICKNESS 1.2~1.4mm)
 (COMPONENT SIDE) TOLERANCE ±0.05mm

OBSOLETE	TUBE	1-1734062-2
	TAPE & REEL	1-1734062-1
NOTE	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	STE TE Connectivity	
DIMENSIONS: MM		CHK		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME	
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
1 PLC ± 0.35		QUALIFICATION TEST REPORT	SIZE	CAGE CODE
2 PLC ± 0.25			A3	00779
3 PLC ± -			DRAWING NO	RESTRICTED TO
4 PLC ± -			C=1734062	
ANGLES ± 3'		WEIGHT	SCALE	
MATERIAL SEE NOTE		4.71 GRAMS	SHEET 2 OF 24	
FINISH SEE NOTE		CUSTOMER DRAWING	REV G4	


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			

LOGO & DATE CODE






- NOTE:
- MATERIAL:
HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
CONTACT: PHOSPHOR BRONZE.
FRONT SHIELD: BRASS.
REAR SHIELD: SPCC.
GROUNDING STRIP: BRASS.
 - FINISH:
CONTACT: 0.76μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
3.048μm [120μ"] MIN. BRIGHT TIN PLATING ON SOLDER TAIL,
WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
FRONT SHIELD: 0.76μm [30μ"] MIN. NICKEL PLATING.
0.76μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
REAR SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
GROUNDING STRIP: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.



P.C.B. EDGE

RECOMMEND P.C.B LAYOUT (THICKNESS 1.2mm)
(COMPONENT SIDE) TOLERANCE ±0.05mm



OBSOLETE

OBSOLETE	-TRAY	2-1734062-2
OBSOLETE	-TUBE	2-1734062-1
	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE TE Connectivity	
DIMENSIONS: MM		CHK		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME	
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
1 PLC ± 0.35		QUALIFICATION TEST REPORT	SIZE	RESTRICTED TO
2 PLC ± 0.25			A3	
3 PLC ± -		WEIGHT	CAGE CODE	DRAWING NO
4 PLC ± -		4.71 GRAMS	00779	C=1734062
ANGLES ± 3'		CUSTOMER DRAWING	SCALE	SHEET
MATERIAL	FINISH			3 OF 24
SEE NOTE	SEE NOTE			REV G4

4




3

2



1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DW		SEE SHEET 1.			



- NOTES:
- MATERIAL:
 HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 CONTACT: PHOSPHOR BRONZE.
 FRONT SHIELD: BRASS.
 REAR SHIELD: SPCC.
 GROUNDING STRIP: STAINLESS.
 - FINISH:
 CONTACT: 0.762µm [30µ"] MIN. GOLD PLATING ON CONTACT AREA.
 3.048µm [120µ"] MIN. MATTE TIN PLATING ON SOLDER TAILS,
 1.27µm [50µ"] MIN. NICKEL UNDERPLATED WITH ENTIRE CONTACT.
 FRONT SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING.
 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
 REAR SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING.
 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
 - FINISH:
 CONTACT: 0.254µm [10µ"] MIN. GOLD PLATING ON CONTACT AREA.
 3.048µm [120µ"] MIN. MATTE TIN PLATING ON SOLDER TAILS,
 1.27µm [50µ"] MIN. NICKEL UNDERPLATED WITH ENTIRE CONTACT.
 FRONT SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING.
 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
 SPUTTERING/BLACK PLATING IN FRONT SURFACE.
 REAR SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING.
 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
 GROUNDING STRIP: SPUTTERING/BLACK PLATING IN FRONT SURFACE.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.



RECOMMENDED MOUNT DIMENSION

OBSELETE	3	TAPE & REEL	3-1734062-4
OBSELETE		TAPE & REEL	3-1734062-3
	2	TUBE	3-1734062-2
		TRAY	3-1734062-1
	FINISH	PACKAGE	PART NUMBER

RECOMMEND P.C.B LAYOUT (THICKNESS 1.4~1.6mm)
 (COMPONENT SIDE) TOLERANCE ±0.05mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	STE TE Connectivity	
DIMENSIONS: MM		CHK		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME	
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
1 PLC ± 0.35		QUALIFICATION TEST REPORT	SIZE	RESTRICTED TO
2 PLC ± 0.25			CAGE CODE	
3 PLC ± -			DRAWING NO	
4 PLC ± -			1734062	
ANGLES ± 3'				
MATERIAL	FINISH	WEIGHT	DRAWING NO	
SEE NOTE	SEE NOTE	4.71 GRAMS	A300779C-1734062	
		CUSTOMER DRAWING	SCALE	SHEET
				4 OF 24
				REV G4

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- - -

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.

RECOMMENDED MOUNT DIMENSION

NOTES:

- MATERIAL:
 - HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 - SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 - CONTACT: PHOSPHOR BRONZE.
 - FRONT SHIELD: SUS.
 - REAR SHIELD: SPCC.
 - GROUNDING STRIP: SUS.
- FINISH:
 - CONTACT: 0.762µm [30µ"] MIN. GOLD PLATING ON CONTACT AREA.
 - 3.048µm [120µ"] MIN. BRIGHT TIN PLATING ON SOLDER TAILS.
 - WITH ENTIRE CONTACT UNDERPLATED 1.27µm [50µ"] MIN. NICKEL.
 - FRONT SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING OVERALL.
 - REAR SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING.
 - 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
- REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

RECOMMEND P.C.B LAYOUT (THICKNESS 1.6mm)
(COMPONENT SIDE) TOLERANCE ±0.05mm

OBSOLETE	TAPE & REEL	4-1734062-2
	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: MM		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME			
0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
MATERIAL SEE NOTE		QUALIFICATION TEST REPORT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
FINISH SEE NOTE		WEIGHT	A3	00779	C=1734062	
		CUSTOMER DRAWING	SCALE	SHEET	6 of 24	REV G4

AMP 1470-19 REV 31MAR2000

4



3

2

1





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DW	/	SEE SHEET 1.			




- NOTES:
- MATERIAL:
 HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 CONTACT: PHOSPHOR BRONZE.
 FRONT SHIELD: SUS.
 REAR SHIELD: SPCC.
 GROUNDING STRIP: SUS.
 - FINISH:
 CONTACT: 0.762µm [30µ"] MIN. GOLD PLATING ON CONTACT AREA,
 2.540µm [100µ"] MIN. BRIGHT TIN PLATING ON SOLDER TAILS,
 WITH ENTIRE CONTACT UNDERPLATED 1.27µm [50µ"] MIN. NICKEL.
 FRONT SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING OVERALL.
 REAR SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING,
 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

RECOMMEND P.C.B LAYOUT (THICKNESS 1.6mm)
 (COMPONENT SIDE) TOLERANCE ±0.05mm



DETAIL A
 SCALE 2:1

TAPE & REEL	4-1734062-3
PACKAGE	PART NUMBER



RECOMMENDED MOUNT DIMENSION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: MM		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME			
0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
MATERIAL SEE NOTE		QUALIFICATION TEST REPORT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
FINISH SEE NOTE		WEIGHT 4.25 GRAMS	A3	00779	C=1734062	
		CUSTOMER DRAWING	SCALE	SHEET	7 OF 24	REV G4

4

3

2





1

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DW		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



MOUNTING PANEL CUTOUT (INTERNAL SIDE)



RECOMMEND P.C.B LAYOUT (THICKNESS 1.0mm) (COMPONENT SIDE) TOLERANCE ±0.05mm

NOTES:

- MATERIAL:
 - HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 - SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 - CONTACT: PHOSPHOR BRONZE.
 - FRONT SHIELD: BRASS.
 - REAR SHIELD: SPCC.
 - GROUNDING STRIP: BRASS.
- FINISH:
 - CONTACT: 0.762µm [30µ"] MIN. GOLD PLATING ON CONTACT AREA.
 - 3.048µm [120µ"] MIN. BRIGHT-TIN PLATING ON SOLDER TAILS.
 - WITH ENTIRE CONTACT UNDERPLATED 1.27µm [50µ"] MIN. NICKEL.
 - FRONT SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING.
 - 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
 - REAR SHIELD: 0.762µm [30µ"] MIN. NICKEL PLATING.
 - 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
 - GROUNDING STRIP: 0.762µm [30µ"] MIN. NICKEL PLATING.
 - 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
- REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

OBSOLETE	TRAY	5-1734062-2
OBSOLETE	TAPE & REEL	5-1734062-1
	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: MM		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME			
0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
MATERIAL		QUALIFICATION TEST REPORT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE NOTE	SEE NOTE	WEIGHT	A3	00779	C=1734062	
CUSTOMER DRAWING			SCALE	SHEET	REV	
				8 OF 24	G4	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

©

COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR




DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.




LOGO & DATE CODE

NOTES:

1.MATERIAL:
 HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 CONTACT: PHOSPHOR BRONZE.
 FRONT SHELL: BRASS.
 REAR SHELL: SPCC.
 GROUNDING STRIP: STAINLESS.

2.FINISH:
 CONTACT: 0.762μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
 3.048μm [120μ"] MIN. BRIGHT TIN PLATING ON SOLDER TAILS,
 WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
 FRONT SHELL: 0.762μm [30μ"] MIN. NICKEL PLATED.
 0.762μm [30μ"] MIN. Cu UNDERPLATING OVERALL.
 REAR SHELL: 0.762μm [30μ"] MIN. NICKEL PLATED.
 0.762μm [30μ"] MIN. Cu UNDERPLATING OVERALL.
 GROUNDING SHELL: 0.762μm [30μ"] MIN. NICKEL PLATED.
 0.762μm [30μ"] MIN. Cu UNDERPLATING OVERALL.

3. REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.



RECOMMEND P.C.B LAYOUT (THICKNESS 1.2mm)
 (COMPONENT SIDE) TOLERANCE ±0.05mm

OBSELETE	TAPE & REEL	6-1734062-1
	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity	
DIMENSIONS: MM		CHK		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME	
0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
MATERIAL		QUALIFICATION TEST REPORT	SIZE	CAGE CODE
SEE NOTE		WEIGHT	DRAWING NO	
SEE NOTE		4.71 GRAMS	A300779 C=1734062	
		CUSTOMER DRAWING	RESTRICTED TO	
		SCALE	SHEET	REV
			9 of 24	G4

4


3

2

1




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DW	/	SEE SHEET 1.			



- NOTE:
- MATERIAL:
 HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
 CONTACT: PHOSPHOR BRONZE.
 FRONT SHIELD: BRASS.
 GROUNDING STRIP: BRASS.
 - FINISH:
 CONTACT: 0.762µm [30µ"] MIN. GOLD PLATING ON CONTACT AREA.
 3.048µm [120µ"] MIN. BRIGHT TIN PLATING ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED 1.27µm [50µ"] MIN. NICKEL.
 FRONT SHELL: 0.762µm [30µ"] MIN. NICKEL PLATED.
 0.762µm [30µ"] MIN. Cu UNDERPLATING OVERALL.
 GROUNDING STRIP: 0.762µm [30µ"] MIN. NICKEL PLATING.
 0.762µm [30µ"] MIN. Cu UNDER PLATING OVERALL.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

RECOMMEND P.C.B LAYOUT (THICKNESS 1.2mm)
 (COMPONENT SIDE) TOLERANCE ±0.05mm










OBSOLETE	TAPE & REEL	8-1734062-1
	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	STE TE Connectivity	
DIMENSIONS: MM		CHK		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME	
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
1 PLC ± 0.35		QUALIFICATION TEST REPORT	SIZE	RESTRICTED TO
2 PLC ± 0.25			A3	
3 PLC ± -			00779	
4 PLC ± -			C=1734062	
ANGLES ± 3'				
MATERIAL	FINISH	WEIGHT	DRAWING NO	
SEE NOTE	SEE NOTE	4.3 GRAMS	A3 00779 C=1734062	
		CUSTOMER DRAWING	SCALE	SHEET
				11 of 24
				REV G4

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DW		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



140	7	980	8.60	4.62	1-1734062-1
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE				
DIMENSIONS: MM		CHK					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD					
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC					
MATERIAL		FINISH	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
			WEIGHT	A3	00779	1734062	
CUSTOMER DRAWING			SCALE	SHEET	12 of 24	REV	G4

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DW	/	SEE SHEET 1.			

D

D

C





C

B

B

A

A



24	40	960	6.10	4.52	3-1734062-2
PCS/TUBE	TUBS INNER BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	1-1734062-2
					1734062-2
					PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	STE TE Connectivity		
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME		
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE		
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
2 PLC ± -		WEIGHT	A3	00779	C=1734062
3 PLC ± -		CUSTOMER DRAWING	SCALE	SHEET	RESTRICTED TO
4 PLC ± -				13 of 24	REV G4
ANGLES ± -					
MATERIAL					
FINISH					

4

3







2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DW		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



100	7	700	7.28	3.30	1734062-3
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	STE TE Connectivity		
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME		
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE		
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
2 PLC ± -		WEIGHT	A3	00779	C=1734062
3 PLC ± -		CUSTOMER DRAWING	RESTRICTED TO		
4 PLC ± -			SCALE	SHEET	REV
ANGLES ± -				14 of 24	G4
FINISH					

4

3

2


1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
DW	/	SEE SHEET 1.				



50	20	1000	6.82	4.71	2-1734062-2
PCS/ TRAY	TRAY/ BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME	
MATERIAL		FINISH		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
				SIZE	RESTRICTED TO
				A3	
				CAGE CODE	
				00779	
				DRAWING NO	
				C=1734062	
				WEIGHT	
				CUSTOMER DRAWING	
				SCALE	
				SHEET	
				15 of 24	
				REV	
				G4	

4




3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DW		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



25	40	1000	6.27	4.71	4-1734062-1	OBSOLETE
					2-1734062-1	
PCS/TUBE	TUBS INNER BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity	
DIMENSIONS: MM		CHK			
		APVD		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
MATERIAL		FINISH		APPLICATION SPEC	
		WEIGHT		RESTRICTED TO	
		CUSTOMER DRAWING		SIZE: A3 CAGE CODE: 00779 DRAWING NO: 1734062	
		SCALE: -		SHEET 16 of 24 REV G4	

4

3

2



1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DW	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



D

D





C

C





B

B




SHIPPING BOX
7 REELS / SHIPPING BOX



A

A



120	7	840	9.05	3.96	3-1734062-4
					3-1734062-3
PCS/ REEL	REELS/ BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity NAME USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC			
MATERIAL		WEIGHT		APPLICATION SPEC	
FINISH		CUSTOMER DRAWING		RESTRICTED TO	
		SCALE		SHEET 17 of 24	
		REV		G4	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR







DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.



100	10	1000	6.27	4.71	5-1734062-2	OBSOLETE
PCS/ TRAY	TRAY/ BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER	
					3-1734062-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC	± -
		1 PLC	± -
		2 PLC	± -
		3 PLC	± -
		4 PLC	± -
MATERIAL		FINISH	

DWN	TE Connectivity			
CHK				
APVD				
NAME				
PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
WEIGHT	A3	00779	C=1734062	
CUSTOMER DRAWING	SCALE	SHEET	18 of 24	REV G4

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR










DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1.












140	7	980	8.60	4.62	5-1734062-1	OBSOLETE
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: MM		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME			
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ± -		WEIGHT	A3	00779	C=1734062	
3 PLC ± -		CUSTOMER DRAWING	SCALE	SHEET	19 of 24	REV G4
4 PLC ± -						
ANGLES ± -						
FINISH						
MATERIAL						

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DW		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



11.20 Kg	6.10 Kg	200	7	1400 PCS	4-1734062-2	OBSOLETE
GROSS WEIGHT	NET WEIGHT	PCS/REEL	REELS/CARTON	QUANTITY	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: MM		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME			
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
1 PLC ± -		APPLICATION SPEC	RESTRICTED TO			
2 PLC ± -		WEIGHT	SIZE	CAGE CODE	DRAWING NO	
3 PLC ± -			A3	00779	C=1734062	
4 PLC ± -		CUSTOMER DRAWING	SCALE	SHEET	20 of 24	REV G4
ANGLES ± -						
FINISH						
MATERIAL						

4









3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DW		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



7.01 Kg	2.98 Kg	100	7	700 PCS	4-1734062-3
GROSS WEIGHT	NET WEIGHT	PCS/REEL	REELS/CARTON	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity		
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME		
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE		
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
2 PLC ± -		WEIGHT	A3	00779	C=1734062
3 PLC ± -		CUSTOMER DRAWING	SCALE	SHEET	REV
4 PLC ± -				21 of 24	G4
ANGLES ± -					
FINISH					
MATERIAL					

4








3

2






1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
DW		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



ROUND HOLE
OVAL HOLE



150	7	1050	8.93	4.95	6-1734062-1
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity		
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME		
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE		
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
2 PLC ± -		WEIGHT	A3	00779	C=1734062
3 PLC ± -		CUSTOMER DRAWING	RESTRICTED TO		
4 PLC ± -			SCALE	SHEET	REV
ANGLES ± -				22 of 24	G4
MATERIAL					
FINISH					

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION










LOC

DIST

REVISIONS

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



130	7	910	7.94	3.91	7-1734062-1	OBSOLETE
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: MM		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME			
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ± -		WEIGHT	A3	00779	C=1734062	
3 PLC ± -		CUSTOMER DRAWING	SCALE	SHEET	REV	
4 PLC ± -				23 of 24	G4	
ANGLES ± -						
FINISH						

4











3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DW	/	SEE SHEET 1.			



180	7	1260	9.40	5.42	8-1734062-1
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity		
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME		
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE		
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO
2 PLC ± -		WEIGHT	A3	00779	C=1734062
3 PLC ± -		CUSTOMER DRAWING	RESTRICTED TO		
4 PLC ± -			SCALE	SHEET	REV
ANGLES ± -				24 of 24	G4
FINISH					