





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		D	REVISED PER 0G3B-0237-05	9/20/05	SS	CJ



1. 0.00076 [0.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [0.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.0013 [0.000050] MIN NICKEL.
2. WIRE RANGE: 0.05 – 0.15MM² (30–26 AWG).
3. INSULATION RANGE: 0.89–1.27[0.035–.050] DIA.
4. DIMENSIONS IN BRACKETS ARE IN INCHES.
5. 0.00076 [0.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [0.000100] MIN MATTE TIN IN LOCALIZED TIN PLATE AREA OVER 0.0013 [0.000050] MIN NICKEL.



5	0.25[.010] BRASS	1-794224-0
1	0.25[.010] BRASS	794224-3
PRE-TIN	0.25[.010] BRASS	794224-1
MATERIAL	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 1-15-97	tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK R. SWING 1-15-97				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PIN, LOOSE PIECE, MINI UNIVERSAL MATE-N-LOK 2			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.15 [.006] 4 PLC ± - ANGLES ± - FINISH		APVD - PRODUCT SPEC - APPLICATION SPEC - WEIGHT -			
	SEE TABLE		SIZE A2 CAGE CODE 00779 DRAWING NO C=794224 RESTRICTED TO -			
CUSTOMER DRAWING		SCALE 10:1		SHEET 1 of 1		REV D