

REV. BN

NOTES:

1. MINIMUM CONTACT RETENTION: 0.5 LB PER PIN.
2. -01 POSITION OFFERED FOR SINGLE ROW RIGHT ANGLE ONLY.
3. -01, -02 & -03 POSITIONS TO BE LAYER PACKAGED.
4. STOCK TO BE 62 POSITION FOR -D AND 61 POSITION FOR -S, -01 LEAD STYLE ONLY. TO BE CUT TO POSITION FOR CUSTOMER.
5. .005 [.13] MAX SHEAR BURR ALLOWANCE.





DO NOT SCALE
FROM THIS PRINT

FIG. 1

FIG. 2
POLARIZATION OPTION LOCATION
INSERT PK-07 INTO SPECIFIED
POSITION AND BREAK OFF TAB(THIS VIEW DRAWN TO SHOW
HOW PLUG IS ORIENTED IN TUBE
FOR THE -01-D-RA STYLE)

PACKAGING VIEWS

SCALE = .75


(THIS VIEW DRAWN TO SHOW
HOW PLUG IS ORIENTED IN TUBE
FOR THE -02-D STYLE)

TABLE 2			
ROW SPEC.	NO. OF POS.	PKG TUBE	TUBE PLUG
-03-S	04-50	PT-1-24-06-17	TP-24
-02-S	05-50	PT-1-24-10-03	TP-03
-01-S-RA	04-50	PT-1-24-01-43	TP-24
-01-D	04-50	PT-1-24-02-17	TP-09
-02-D	04-50	PT-1-24-01-34	TP-07
-03-D	04-50	PT-1-24-01-22	TP-03
-01-D-RA	04-50	PT-1-24-01-45	TP-03
-01-T	04-50	PT-1-24-05-09	TP-07
-02-T	04-50	PT-1-24-01-102	TP-07
-03-T	04-50	PT-1-24-08-15	TP-07
-01-Q	04-50	PT-1-24-15-29	TP-07
-02-Q	04-50	PT-1-24-02-51	TP-13
-03-Q	04-50	PT-1-24-16-29	TP-07
-01-T-RA	04-50	PT-1-24-06-40	TP-07
-01-S	04-50	PT-1-24-05-15	TP-24
ALL STYLES	-02 & -03	LAYER PACKAGING	

TABLE 1		
LEAD STYLE	'A'	CONTACT
-01	.090 [2.29]	C-79-01-X
-01-S-RA	N/A	C-79-53-X
-01-D-RA	N/A	C-79-12-X
-01-T-RA	N/A	C-79-53-X
-01-Q-RA	N/A	C-79-12-X
-02	.600 [15.24]	C-79-02-X
-03	.208 [5.28]	C-79-53-X

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

MATERIAL:

CONTACT:
PHOS BRONZEINSULATOR:
LCP
COLOR: BLACK

MAX BOW: .004 IN/IN

samtec
520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:

BRATCHER 7-24-95

SQT-1XX-XX-XXX-X-XXX-XXX

SHEET 1 OF 3

UNLESS OTHERWISE NOTED				TITLE: 2MM SOCKET STRIP ASSEMBLY	DWG NO: SQT-1XX-XX-XXX-X-XXX-XXX
DIMENSIONS ARE IN INCHES		TOLERANCES ARE:			
ONE PLACE DECIMALS ±.1[2.5]		THREE PLACE DECIMALS ±.005[.127]		ANGLES ± 2°	SHEET 1 OF 3
TWO PLACE DECIMALS ±.01[.25]		FOUR PLACE DECIMALS ±.0020[.051]			