


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .  
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

| LOC | DIST | P | F | REVISIONS |     |                         |         |      |
|-----|------|---|---|-----------|-----|-------------------------|---------|------|
|     |      |   |   | ZONE      | LTR | DESCRIPTION             | DATE    | APPD |
| AJ  | 16   |   |   |           | C   | OBS -2 PER 0U20-0072-01 | 16APR01 | M0   |
|     |      |   |   |           |     |                         |         |      |
|     |      |   |   |           |     |                         |         |      |

SHELL



ø9.66  
[.380]



3 DIELECTRIC  
1 5 CONTACT

- 1 PHOSPHOR BRONZE PER QQ-B-750
- 2 ZINC PER QQ-Z-363
- 3 POLYMETHYLPENTENE: GENERAL PURPOSE
- 4 NICKEL PLATE PER QQ-N-290, 3.81µm [.000150] MIN THICKNESS
- 5 GOLD PLATE PER MIL-G-45204, 0.38µm [.000015] MIN THICKNESS

|          |             |
|----------|-------------|
| OBSOLETE | 414414-2    |
|          | 414414-1    |
|          | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

|                                                                                                                                                   |                             |  |                                                           |         |              |
|---------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|--|-----------------------------------------------------------|---------|--------------|
|                                                                                                                                                   |                             |  |                                                           | PART NO |              |
| DO NOT SCALE PRINT.<br>UNLESS SPECIFIED<br>DIMENSIONS IN mm [INCHES]<br>TOLERANCES ON:<br>2 PLC DEC ± 0.05 [ø.002]<br>3 PLC DEC ± -<br>ANGLES ± - | DR 9-8-92<br>M.E. COWHER    |  | <b>AMP</b> AMP Incorporated<br>Harrisburg, PA 17105-3608  |         |              |
|                                                                                                                                                   | CHK 9-14-92<br>M. PHILLIPS  |  |                                                           |         |              |
|                                                                                                                                                   | APPD 9-14-92<br>M. PHILLIPS |  | NAME<br><br>JACK ADAPTER ASSEMBLY, COML BNC               |         |              |
|                                                                                                                                                   | APPD 9-14-92<br>M.E. COWHER |  |                                                           |         |              |
| MATERIAL<br><div><div>1</div><div>2</div><div>3</div></div>                                                                                       | PRODUCT SPEC<br>-           |  | SIZE<br>B<br>CAGE CODE<br>00779<br>DRAWING NO<br>C-414414 |         |              |
|                                                                                                                                                   | APPLICATION SPEC<br>-       |  |                                                           |         |              |
| FINISH<br><div><div>4</div><div>5</div></div>                                                                                                     | WEIGHT -                    |  | SCALE 4:1                                                 |         | SHEET 1 OF 1 |