



DESCRIPTION: HIGH DENSITY - FEMALE - RIGHT ANGLE

44 PIN SHOWN



DIMENSIONS (IN.)							
No. OF PINS	A	B	C	D	E	F	G
15	1.213	0.984	0.644	0.090	0.311	0.496	0.639
	30.80	24.99	16.34	2.29	7.90	12.60	16.23
26	1.543	1.312	0.966	0.090	0.311	0.496	0.639
	39.19	33.32	24.53	2.29	7.90	12.60	16.23
44	2.087	1.852	1.512	0.090	0.311	0.496	0.639
	53.00	47.04	38.40	2.29	7.90	12.60	16.23
62	2.732	2.500	2.156	0.095	0.311	0.496	0.639
	69.30	63.50	54.76	2.41	7.90	12.60	16.23

ELECTRICAL:

CURRENT RATING: 3 AMPS
CONTACT RESISTANCE: 15 Milliohms Max.
INSULATION RESISTANCE: 1,000 MEGOhms Min. at 500 VDC
DIELECTRIC WITHSTANDING VOLTAGE: 1,000 VAC FOR 1 MINUTE
WORKING VOLTAGE: 250 VAC
TEMPERATURE: -55°C TO +105°C

MATERIALS:

SHELL: SPCC, NICKEL PLATED
INSULATOR: PA9T-BLACK (UL94-0)
260°C PROCESS TEMPERATURE
CONTACT: BRASS, GOLD ENTIRE CONTACT
RIVET: COPPER ALLOY, NICKEL PLATED
BOARDLOCK: SPCC, TIN PLATED
SCREWLOCK: ZINC ALLOY, NICKEL PLATED

181-YYY-2 1 3 R YY 1


SERIES _____
POSITIONS _____
015 _____
026 _____
044 _____
062 _____
GENDER _____
2 = FEMALE
TERMINATION _____
1 = DIP SOLDER
SHELL PLATING _____
3 = NICKEL PLATED
RoHS COMPLIANT _____
(HIGH TEMP. PROCESS)
HARDWARE OPTIONS _____
16 = $\varnothing$ 0.120 HOLE / INSIDE GND STRAPS
17 = 4-40 INSERTS / INSIDE GND STRAPS
18 = 4-40 SCREWLOCKS / INSIDE GND STRAPS
43 = $\varnothing$ 0.120 HOLE / METAL SHELL
45 = 4-40 INSERTS / METAL SHELL
48 = 4-40 SCREWLOCKS / METAL SHELL
53 = 4-40 INSERTS / BOARDLOCKS
55 = $\varnothing$ 0.120 HOLE / BOARDLOCKS
56 = 4-40 SCREWLOCKS / BOARDLOCKS
PLATING OPTIONS _____
1 = GOLD FLASH
2 = 30u" GOLD PLATING

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 3-15-05	
		CHECKED:		DATE:	
		SCALE:		SHEET 1 OF 3	REV 16
		DWG NO. 181-YYY-213RYY1			

RoHS COMPLIANT


DESCRIPTION: PCB LAYOUT - RIGHT ANGLE - FEMALE




15 POSITION



26 POSITION



44 POSITION



62 POSITION

181 SERIES
HIGH DENSITY
RIGHT ANGLE







HOLE PATTERN SHOWN
ARE FOR FEMALE

* TYP. ON ALL SIZES

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-09-06	
		CHECKED:		DATE:	
NorComp		SCALE: FULL	SHEET 2		OF 3
		REV 16			
		DWG NO. 181-YYY-213RYY1			

DESCRIPTION: HIGH DENSITY R/A HARDWARE OPTIONS

	 0.141 ±0.020 METAL SHELL WITH INSIDE GROUND STRAPS	 METAL SHELL	 METAL SHELL FORK BOARD LOCKS
 .120" DIA. HOLE	16	43	55
 4-40 FLUSH INSERT	17	45	53 BOARD LOCKS
 4-40 HEX STANDOFF FEMALE SCREWLOCK	18	48	56 BOARD LOCKS

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN:
WAYNE ROBBINS

DATE:
3-17-05

CHECKED:

DATE:

SCALE:

SHEET
3

OF
3

REV
16

DWG NO.

181-YYY-213RYY1