







|     |      |           |     |                           |           |     |      |
|-----|------|-----------|-----|---------------------------|-----------|-----|------|
| LOC | DIST | REVISIONS |     |                           |           |     |      |
| GP  | 00   | P         | LTR | DESCRIPTION               | DATE      | DWN | APVD |
|     |      |           | L   | REVISED PER ECO-13-012013 | 09AUG2013 | CJV | CWR  |



- ① CONTACTS DESIGNED FOR 26 & 28 AWG STRANDED OR 26, 28 & 30 AWG SOLID WIRE.
- ② AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- ③ STANDOFFS: POS 10 (2) STANDOFFS AS SHOWN.  
14-16 (3) STANDOFFS, (1) CENTERED BETWEEN (2) SHOWN  
20-26 (4) (2)  
30 (5) (3)  
34 (6) (4)  
40-44 (7) (5)  
50 (8) (6)  
60 (9) (7)  
64 (10) (8)
- ④ .000100-.000200 BRIGHT TIN-LEAD, ALL OVER .000050 NICKEL.
- ⑤ HEIGHT AFTER TERMINATION IS .253 ±.010.
6. FOR USE IN .062 - .093" THICK PCB.
- ⑦ .000005 MIN GOLD ON RIBBON CABLE TERMINATION AREA,  
.000100-.000200 MATTE TIN ON SOLDER TAILS, ALL OVER  
.000050 MIN NICKEL.
- ⑧ MOLDED PARTS, 94V-0 RATED THERMOPLASTIC, COLOR: BLACK  
CONTACTS: PHOS BRONZE.



|          |                                                                                       |    |       |    |    |               |            |
|----------|---------------------------------------------------------------------------------------|----|-------|----|----|---------------|------------|
|          |  | 24 | 2.680 | 48 | 49 | 50            | 2-111382-0 |
|          |  | 16 | 1.880 | 32 | 33 | 34            | 1-111382-9 |
|          |  | 12 | 1.480 | 24 | 25 | 26            | 1-111382-8 |
|          |  | 9  | 1.180 | 18 | 19 | 20            | 1-111382-7 |
|          |  | 7  | 0.980 | 14 | 15 | 16            | 1-111382-6 |
|          |  | 4  | .680  | 8  | 9  | 10            | 1-111382-4 |
| OBSOLETE |  | 21 | 2.380 | 42 | 43 | 44            | 1-111382-3 |
| OBSOLETE |  | 31 | 3.380 | 62 | 63 | 64            | 1-111382-2 |
| OBSOLETE |  | 29 | 3.180 | 58 | 59 | 60            | 1-111382-1 |
| OBSOLETE |  | 24 | 2.680 | 48 | 49 | 50            | 1-111382-0 |
| OBSOLETE |  | 19 | 2.180 | 38 | 39 | 40            | 111382-9   |
| OBSOLETE |  | 16 | 1.880 | 32 | 33 | 34            | 111382-8   |
| OBSOLETE |  | 14 | 1.680 | 28 | 29 | 30            | 111382-7   |
| OBSOLETE |  | 12 | 1.480 | 24 | 25 | 26            | 111382-6   |
| OBSOLETE |  | 11 | 1.380 | 22 | 23 | 24            | 111382-5   |
|          |  | 9  | 1.180 | 18 | 19 | 20            | 111382-4   |
| OBSOLETE |  | 7  | .980  | 14 | 15 | 16            | 111382-3   |
| OBSOLETE |  | 6  | .880  | 12 | 13 | 14            | 111382-2   |
| OBSOLETE |  | 4  | .680  | 8  | 9  | 10            | 111382-1   |
|          | CONTACT<br>FINISH                                                                     | D  | C     | B  | A  | NO OF<br>POSN | PART NO    |

|                                                                                                          |  |                                                                         |  |                                                                                                       |  |
|----------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                   |  | DWN. 11-29-04<br>L. VARELA - DOCKS<br>C. RHODE 11-29-04                 |  |  TE Connectivity |  |
| DIMENSIONS:<br>INCHES                                                                                    |  | TOLERANCES, UNLESS<br>OTHERWISE SPECIFIED:                              |  | NAME                                                                                                  |  |
|                     |  | APVD M. WALMSLEY 11-29-04<br>PRODUCT SPEC 108-40013<br>APPLICATION SPEC |  | KIT, DIP LATCH, PREASSEMBLED,<br>.100 X .100 CENTERLINE, AMP-LATCH                                    |  |
| MATERIAL FINISH<br> |  | 114-40005<br>WEIGHT —                                                   |  | SIZE CAGE CODE DRAWING NO<br>A1 00779 C 111382                                                        |  |
| CONTACTS: SEE TABLE                                                                                      |  | CUSTOMER DRAWING                                                        |  | SCALE 10:1 SHEET 1 OF 1 REV —                                                                         |  |