



Device Boxes, Covers & Accessories

T&B Catalog Number:

UPC Number:

IH3-2-LM

Status:

04226939225

Description:

Active

1-gang 17 cu. in. Universal weatherproof Box with Three 3/4 in. Holes and Mounting Lugs - Silver

Features

Alloy A380 aluminum, certified zinc alloy and stainless steel springs provide increased corrosion resistance

Die Cast construction and industrial design combine to produce a rugged protective enclosure for devices.


Clean cover edges provide good gasket sealing.

Precision cast and machined surfaces permit safer wire pulling.

Clear UL and cubic content markings speed approval by inspectors

Convenient mounting lugs for a variety of mounting methods

Securely fastened mounting plates reduce costly call backs



Application

Dry-tite boxes and covers protect wiring devices, switches, electronic components and terminal blocks in dry, damp and wet locations

Accessible wiring chamber provides a convenient location to maintain or change a system, pull conductors and make splices

Junction box for branch conduits

General

Material	Die Cast Aluminum
Finish	Powder-coated
Color	Silver
Volume (cu.in.)	17
Number of Gangs	One

Dimension Information

Hub Size (inches)	3/4
A (inches)	4 9/16
B (inches)	2 13/16
C (inches)	2
D (inches)	5/8
E (inches)	3 13/16
F (inches)	3 1/2
G (inches)	3 1/4
H (inches)	1 7/8
J (inches)	1 1/2

Packaging

T&B Inner Pack	1
Package in Units	50

T&B Sold in UOM	Each
T&B Weight Per UOM	0.54 lbs. Each

Application Support

D-Pak Merchandising System	Available on Website
Industry Cross Reference	Available on Website

Notes

Rain tight when used with appropriate Red Dot covers.

Certifications

RoHS Compliance	No
-----------------	----

Certifications

File Nbr:
E 28688

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com