





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		G2	REVISED PER ECO-08-019746	13AUG08	HMR	DC
			G3	REV PER ECO-09-021826	08SEP09	KK	AEG




- 1 MATES WITH AMP CONNECTOR PART NO 480704.
- $\triangle 2$ FLAME RETARDANT CLASSIFICATION OF MATERIAL IS 94V-2.
- 3 PARTS MUST COMPLY WITH AMP SOLDERABILITY SPEC 109-11-3.
- $\triangle 4$ CONTACT IS STAMPED FROM PRE-PLATED STOCK WHICH IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN STRIPED WITH 0.00076 [.000030] GOLD IN CONTACT AREA INDICATED AND TIN-LEAD ON SOLDER TAIL END.
- $\triangle 5$ CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- $\triangle 6$ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED LAYOUT FOR 3.18 [.125] THICK PC BOARD

$\triangle 6$	OBSOLETE PH BRZ GOLD $\triangle 5$	NYLON,NATURAL $\triangle 2$	350989-5
	PH BRZ TIN	NYLON,NATURAL $\triangle 2$	350989-4
	PH BRZ GOLD $\triangle 4$	NYLON,NATURAL $\triangle 2$	350989-3
CONTACT		HOUSING	PART NO

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 11OCT2005	 Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608				
DIMENSIONS: mm [INCHES]		CHK S. RIDGILL 11OCT2005					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. RIDGILL 11OCT2005	NAME	SOCKET HEADER ASSEMBLY, 6 CIRCUIT, LONG TAIL, UNIVERSAL MATE-N-LOK (TM)			
		PRODUCT SPEC					
MATERIAL SEE TABLE		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
FINISH SEE TABLE		WEIGHT	A1	00779	C=350989		
CUSTOMER DRAWING			SCALE	5:1	SHEET	1 OF 1	REV G3