


Restricted to: General Release

USED ON

THIS DRAWING IS A CONTROLLED DOCUMENT
PAGE 18
589061



Left Side

Connector(s): LC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Fiber Path

A - _____ - B
B - _____ - A

Right Side

Connector(s): LC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Notes:



- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).
- 3 IL tested at 1300nm.
- 4 Label 2 will not be present on any cable assembly less than 5 meters long.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

	A	Rev Per EC#	None	1/16/2006	-	DF	
P	LTR	REVISION RECORD		DATE	DIN	APVD	



DIN Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Dave Fennell	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	Dave Fennell			
NAME: FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex to LC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1906858	SHEET 1 of 4	REV A

8

7

6

5

4

3

2

1

USED ON

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

Qty	U of M	Description	Item No.
2	piece	Trace Label	6
4	piece	Eyelet/Shrink tube assembly - White	5
AR	meter	2 fiber, 50/125, 1.8mm, Twinzip, Yellow, OFNP (Plenum)	4
4	piece	LC Connector Assy, MM	3
2	piece	LC Duplex clip, black	2
4	piece	LC, SC, FC Straight Boot, Beige	1

DIMENSIONS; meters		TOLERANCES UNLESS OTHERWISE SPECIFIED	
	0 PLC	±	-
	1 PLC	±	-
	2 PLC	±	-
	3 PLC	±	-
	4 PLC	±	-

QW Cable Assy Configurator		MATERIAL -	HEAT TREAT -
CHK Dave Fennell	APVD Dave Fennell	 AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex to LC-Duplex			
SCALE NTS	SIZE A2	DRAWING NO C- 1906858	SHEET 2 of 4
			REV A

LOC
CE
DIST
16

Customer Print

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.
DWG NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Restricted to: General Release

USED ON

Part #	L (meters)	L (feet)	LC-Duplex, Beige		LC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1906858-3	42.570 - 43.430	139.66 - 142.48	0.56	-	0.56	-
4-1906858-4	43.560 - 44.440	142.91 - 145.80	0.57	-	0.57	-
4-1906858-5	44.550 - 45.450	146.16 - 149.11	0.57	-	0.57	-
4-1906858-6	45.540 - 46.460	149.40 - 152.42	0.57	-	0.57	-
4-1906858-7	46.530 - 47.470	152.65 - 155.74	0.57	-	0.57	-
4-1906858-8	47.520 - 48.480	155.90 - 159.05	0.57	-	0.57	-
4-1906858-9	48.510 - 49.490	159.15 - 162.36	0.57	-	0.57	-
5-1906858-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	-
5-1906858-1	50.490 - 51.510	165.64 - 168.99	0.58	-	0.58	-
5-1906858-2	51.480 - 52.520	168.89 - 172.30	0.58	-	0.58	-
5-1906858-3	52.470 - 53.530	172.14 - 175.62	0.58	-	0.58	-
5-1906858-4	53.460 - 54.540	175.39 - 178.93	0.58	-	0.58	-
5-1906858-5	54.450 - 55.550	178.64 - 182.25	0.58	-	0.58	-
5-1906858-6	55.440 - 56.560	181.88 - 185.56	0.58	-	0.58	-
5-1906858-7	56.430 - 57.570	185.13 - 188.87	0.59	-	0.59	-
5-1906858-8	57.420 - 58.580	188.38 - 192.19	0.59	-	0.59	-
5-1906858-9	58.410 - 59.590	191.63 - 195.50	0.59	-	0.59	-
6-1906858-0	59.400 - 60.600	194.88 - 198.81	0.59	-	0.59	-
6-1906858-1	60.390 - 61.610	198.12 - 202.13	0.59	-	0.59	-
6-1906858-2	61.380 - 62.620	201.37 - 205.44	0.59	-	0.59	-
6-1906858-3	62.370 - 63.630	204.62 - 208.75	0.59	-	0.59	-
6-1906858-4	63.360 - 64.640	207.87 - 212.07	0.6	-	0.6	-
6-1906858-5	64.350 - 65.650	211.12 - 215.38	0.6	-	0.6	-
6-1906858-6	65.340 - 66.660	214.37 - 218.70	0.6	-	0.6	-
6-1906858-7	66.330 - 67.670	217.61 - 222.01	0.6	-	0.6	-
6-1906858-8	67.320 - 68.680	220.86 - 225.32	0.6	-	0.6	-
6-1906858-9	68.310 - 69.690	224.11 - 228.64	0.6	-	0.6	-
7-1906858-0	69.300 - 70.700	227.36 - 231.95	0.61	-	0.61	-
7-1906858-1	70.290 - 71.710	230.61 - 235.26	0.61	-	0.61	-
7-1906858-2	71.280 - 72.720	233.85 - 238.58	0.61	-	0.61	-
7-1906858-3	72.270 - 73.730	237.10 - 241.89	0.61	-	0.61	-
7-1906858-4	73.260 - 74.740	240.35 - 245.20	0.61	-	0.61	-
7-1906858-5	74.250 - 75.750	243.60 - 248.52	0.61	-	0.61	-
7-1906858-6	75.240 - 76.760	246.85 - 251.83	0.61	-	0.61	-
7-1906858-7	76.230 - 77.770	250.09 - 255.15	0.62	-	0.62	-
7-1906858-8	77.220 - 78.780	253.34 - 258.46	0.62	-	0.62	-
7-1906858-9	78.210 - 79.790	256.59 - 261.77	0.62	-	0.62	-
8-1906858-0	79.200 - 80.800	259.84 - 265.09	0.62	-	0.62	-

	A	Rev Per EC#	None	1/16/2006	-	DF	
P	LTR	REVISION RECORD		DATE	DIN	APVD	

DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 P.L.C.	± .
		1 P.L.C.	± .
		2 P.L.C.	± .
		3 P.L.C.	± .
		4 P.L.C.	± .

Customer Print

DWG Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Dave Fennell	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Dave Fennell				
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex to LC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1906858	SHEET 3 of 4	REV A

8 7 6 5 4 3 2 1


D

C

B


A

Per specification 107-1645-1



This label is used on all lengths on this drawing.

Per specification 107-1645-1



This label is used on all lengths on this drawing.

THIS DRAWING IS A CONTROLLED DOCUMENT.

CAC Customer Layout Rev: D

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT	
CHK	Dave Fennell	 Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	Dave Fennell			
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex to LC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 1906858	SHEET 4 of 4	REV A

Customer Print

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[1-1905993-5](#)