

GRP Explosion Proof Visual Signal 5 Joule Series FX15



www.stahl.de



15567E00

- > Suitable for offshore / onshore & harsh environments
- > Corrosion resistant light weight GRP enclosure
- > Stainless steel fixings and guard
- > High ingress protection IP66 & IP67
- > Extreme temperature range -55 ... +70 °C
- > Flexible mounting options
- > Light enhancing lens design



E5

Yodalex range -
Flashing visual signal, GRP enclosure designed for use in hazardous and harsh environments.

	ATEX IECEx					
Zone	0	1	2	20	21	22
For use in		x	x		x	x

WebCode FX15A

GRP Explosion Proof Visual Signal 5 Joule

Series FX15



Explosion Protection

Global (IECEX)

Gas and dust

IIB	IECEX BAS 13.0005X
IIC	IECEX BAS 13.0003
IIB, IIC	IEC 60079-0: 2011 / IEC 60079-1: 2007-04 / IEC 60079-31: 2008
IIB	Ex d IIB T* Gb (Ta = -60 ... +** °C)
	Ex tb IIIC T***°C Db IP 66 (Ta = -60 ... +** °C)
IIC	Ex d IIC T* Gb (Ta = -60 ... +** °C)
	Ex tb IIIC T***°C Db IP 66 (Ta = -60 ... +** °C)

* temperature class on the table

Europe (ATEX)

Gas and dust

IIB	Baseefa13ATEX0007X
IIC	Baseefa13ATEX0006
IIB, IIC	EN 60079-0: 2012 / EN 60079-1: 2007 / EN 60079-31: 2009
IIB	⊕ II 2 G Ex d IIB T* Gb (Ta = -60 ... +** °C)
	⊕ II 2 D Ex tb IIIC T***°C Db IP 66 (Ta = -60 ... +** °C)
IIC	⊕ II 2 G Ex d IIC T* Gb (Ta = -60 ... +** °C)
	⊕ II 2 D Ex tb IIIC T***°C Db IP 66 (Ta = -60 ... +** °C)

* temperature class on the table

Product variant table

Power and voltage	Temperature class	Max. surface temperature	Ambient temperature range
5 J 24 V DC	T6	T73 °C	-60 ... +40 °C
	T5	T88 °C	-60 ... +55 °C
	T4	T103 °C	-60 ... +70 °C
5 J 48 V DC	T6	T73 °C	-60 ... +40 °C
	T5	T88 °C	-60 ... +55 °C
	T4	T103 °C	-60 ... +70 °C
5 J 115 V AC	T5	T83 °C	-60 ... +40 °C
	T4	T113 °C	-60 ... +55 °C
5 J 230 V AC	T6	T75 °C	-60 ... +40 °C
	T5	T90 °C	-60 ... +55 °C
	T4	T105 °C	-60 ... +70 °C

Technical Data

Electrical data

Rated operational voltage	24 V DC, 48 V DC, 115 V AC and 230 V AC operational parameters + or -10 %	
Rated operational current	24 V DC	300 mA
	48 V DC	185 mA
	115 V AC	140 mA
	230 V AC	75 mA
Start-up current	24 V DC	500 mA
	48 V DC	250 mA
	115 V AC	900 mA
	230 V AC	100 mA

Luminous Characteristics

Effective candela	49 cd Clear lens
Candela seconds	9.96 cds
Flash energy	5 J
Flash rate	1 per second

Operating temperature range

24 & 48 V DC	-50 ... +70 °C
115 V AC	-55 ... +55 °C
230 V AC	-55 ... +70 °C

Mechanical data

Material	
Enclosure	GRP
Lens cover	polycarbonate
Wire guard	stainless steel
Degree of protection	IP66 & IP67 IEC 60529
Cable entries	3 x M20, product supplied with 3 x dust cover
Weight	2.4 kg

GRP Explosion Proof Visual Signal 5 Joule Series FX15



Selection table

Version	Group	Rated operational voltage	Lens colour	Order number	Art. no.	Weight kg
ATEX & IECEx standard variants	IIC	24 V DC	red	FX15/C-D-050-R-EN-SF-A	217971	2.230
			amber	FX15/C-D-050-A-EN-SF-A	217979	2.230
			clear	FX15/C-D-050-C-EN-SF-A	217989	2.230
		115 V AC	red	FX15/C-L-050-R-EN-SF-A	217973	2.250
			amber	FX15/C-L-050-A-EN-SF-A	217981	2.250
			clear	FX15/C-L-050-C-EN-SF-A	217983	2.250
		230 V AC	red	FX15/C-N-050-R-EN-SF-A	217974	2.250
			amber	FX15/C-N-050-A-EN-SF-A	217982	2.250
			clear	FX15/C-N-050-C-EN-SF-A	217995	2.250

Note FX15 Beacons are supplied without a bracket. These must be ordered separately (see accessories table).

Type Code


Variant	Option	Code	FX15 / C - . - 050 - . - EN - . . - A - . .
Gas group	IIC	C	
Supply voltage	24 V DC	D	
	48 V DC	F	
	115 V AC	L	
	230 V AC	N	
Light output	5 Joule	050	
Lens colour	Red	R	
	Amber	A	
	Clear	C	
	Blue	B	
	Green	G	
	Yellow	Y	
	Magenta	M	
	Opal	O	
Certification	ATEX & IECEx	EN	
Body colour	Standard black	SF	
	Red	RN	
	Yellow	YE	
	Blue	BL	
Cable entries	3 x M20	A	
Optional extras	Telephone initiate	TI	
	Duty label	D	
	Tag label	TL	
	Local Approval	L	

E5

GRP Explosion Proof Visual Signal 5 Joule Series FX15









Accessories and Spare Parts

Designation	Figure	Description	Art. no.	WebCode
Mounting brackets	 15795E00	Stainless steel L-bracket - see dimensional drawings	221711	--
	 15794E00	Stainless steel backstrap mounting bracket - see dimensional drawings	221712	--
Cable glands	 14976E00	Compound barrier cable glands Ex d and Ex e for all types of unarmoured cables	138888	8163J
	 14742E00	Compound barrier cable glands Ex d and Ex e for all types of armoured cables	138875	8163I
Xenon tube	 15798E00	Xenon tube assembly	223636	--
PCB	 15786E00	PCB assembly 24 V DC 5J	223635	--
		PCB assembly 48 V DC 5J	223634	--
		PCB assembly 110 V AC 5J	223632	--
		PCB assembly 230 V AC 5J	223580	--
PCB termination	 15785E00	PCB assembly termination	223579	--
Flange	 15796E00	Flange assembly standard - specify lens colour acc. to type code	223578	--

GRP Explosion Proof Visual Signal 5 Joule Series FX15





Dimensional Drawings (All Dimensions in mm / inches) - Subject to Alterations





FX15 Beacon

FX15 Beacon with 'L' bracket

FX15 Beacon with backstrap bracket



Backstrap bracket



L-shaped bracket

We reserve the right to make alterations to the technical data, dimensions, weights, designs and products available without notice. The illustrations cannot be considered binding.

E5

GRP Explosion Proof Visual Signal 5 Joule Series FX15

