

SCHOTTKY RECTIFIER
HIGH EFFICIENCY SERIES

16SCYQ030C

16 Amp, 30V

Major Ratings and Characteristics


Characteristics	Limits	Units
$I_{F(AV)}$	16	A
V_{RRM} (Per Leg)	30	V
I_{FSM} @ $t_p = 8.3ms$ half-sine (Per Leg)	150	A
V_F @ 16Apk, $T_J = 125^\circ C$ (Per Leg)	0.54	V
T_J, T_{stg} Operating and storage	-55 to 150	$^\circ C$

Description / Features

The 16SCYQ030C center tap Schottky rectifier has been expressly designed to meet the rigorous requirements of high reliability environments. It is packaged in the hermetic isolated TO-257AA package. The device's forward voltage drop and reverse leakage current are optimized for the lowest power loss and the highest circuit efficiency for typical high frequency switching power supplies and resonant power converters. Full MIL-PRF-19500 quality conformance testing is available on source control drawings to TX, TXV and S quality levels.


- Hermetically Sealed
- Center Tap
- Ceramic Eyelets
- Low Forward Voltage Drop
- High Frequency Operation
- Guard Ring for Enhanced Ruggedness and Long term Reliability
- Lightweight

CASE STYLE



NOTES:

1. DIMENSIONING & TOLERANCING PER ANSI Y14.5M-1994.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSIONS ARE SHOWN IN MILLIMETERS (INCHES).
4. OUTLINE CONFORMS TO JEDEC OUTLINE TO-257AA.



Case Outline and Dimensions - TO-257AA

Voltage Ratings

Part number	16SCYQ030C
V_R Max. DC Reverse Voltage (V) (Per Leg)	30
V_{RWM} Max. Working Peak Reverse Voltage (V) (Per Leg)	

Absolute Maximum Ratings

Parameters	Limits	Units	Conditions
$I_{F(AV)}$ Max. Average Forward Current See Fig. 5	16	A	50% duty cycle @ $T_C = 138^\circ\text{C}$, square waveform
I_{FSM} Max. Peak One Cycle Non - Repetitive Surge Current (Per Leg)	150	A	@ $t_p = 8.3$ ms half-sine

Electrical Specifications

Parameters	Limits	Units	Conditions
V_{FM} Max. Forward Voltage Drop (Per Leg) See Fig. 1①	0.57	V	@ 7.5A
	0.65	V	@ 15A
	0.66	V	@ 16A
	0.48	V	@ 7.5A
	0.58	V	@ 15A
	0.60	V	@ 16A
	0.365	V	@ 7.5A
	0.52	V	@ 15A
	0.54	V	@ 16A
I_{RM} Max. Reverse Leakage Current (Per Leg) See Fig. 2①	1.0	mA	$T_J = 25^\circ\text{C}$
	117	mA	$T_J = 100^\circ\text{C}$
	150	mA	$T_J = 125^\circ\text{C}$
C_T Max. Junction Capacitance (Per Leg)	1900	pF	$V_R = 5V_{DC}$ (1MHz, 25°C) ②
L_S Typical Series Inductance (Per Leg)	6.9	nH	Measured from anode lead to cathode lead 6mm (0.025 in.) from package

Thermal-Mechanical Specifications

Parameters	Limits	Units	Conditions
T_J Max. Junction Temperature Range	-55 to 150	$^\circ\text{C}$	
T_{stg} Max. Storage Temperature Range	-55 to 150	$^\circ\text{C}$	
R_{thJC} Max. Thermal Resistance, Junction to Case (Per Leg)	1.6	$^\circ\text{C/W}$	DC operation See Fig. 4
R_{thJC} Max. Thermal Resistance, Junction to Case (Per Package)	0.8	$^\circ\text{C/W}$	DC operation
w_t Weight (Typical)	4.3	g	
Die Size (Typical)	115X170	mils	
Case Style	T0-257AA		

① Pulse Width < 300 μs , Duty Cycle < 2%




Fig. 1 - Max. Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current Vs. Reverse Voltage (Per Leg)






Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)

Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics (Per Leg)Fig. 5 - Max. Allowable Case Temperature Vs.
Average Forward Current (Per Leg)International
IOR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105

IR LEOMINSTER : 205 Crawford St., Leominster, Massachusetts 01453, USA Tel: (978) 534-5776

TAC Fax: (310) 252-7903

Visit us at www.irf.com for sales contact information.

Data and specifications subject to change without notice. 02/2008

www.irf.com