

4		3		2		1	
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
© COPYRIGHT - By -				ALL RIGHTS RESERVED.			
LOC E		DIST B		REVISIONS			
P		LTR		DESCRIPTION		DATE	
		-		SEE SHEET 1		-	
HB01RE 10.4 max 26.5 max 25.4 min 22.9 3.0 max MARKING FACE DESCRIPTION: LEAD MATERIAL: LEAD CROSS-SECTION: HYBRID PROTECTION: MARKING: HIGH VOLTAGE THICK FILM RESISTOR. TINNED COPPER WIRE 0.6 +/-0.5 DIA CONFORMAL EPOXY COATING AS SHOWN BELOW ON MARKING FACE HB01R VAL. DATE CODE TOL. TCR				HB01RS 8.4 max 26.0 max 25.4 min 22.9 1.5 max MARKING FACE DESCRIPTION: LEAD MATERIAL: LEAD CROSS-SECTION: HYBRID PROTECTION: MARKING: HIGH VOLTAGE THICK FILM RESISTOR. TINNED COPPER WIRE 0.6 +/-0.5 DIA SCREEN PRINTED SILICONE COATING AS SHOWN BELOW ON MARKING FACE HB01R VAL. DATE CODE TOL. TCR			
R TYPICAL SCHEMATIC FOR A SPECIFIC PN FOR A RESISTANCE VALUE AND TOLERANCE, PLEASE REFER TO DMF.				RoHS Compliant THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: MM 0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES ± - ± - ± - ± - ± - ± - MATERIAL - TOLERANCES UNLESS OTHERWISE SPECIFIED: ± - ± - ± - ± - ± - ± - FINISH - DWN DAVE KENNEDY CHK J CATCHPOLE APVD J CATCHPOLE PRODUCT SPEC APPLICATION SPEC WEIGHT - CUSTOMER DRAWING SCALE NTS SHEET 2 OF 2 REV B1 31OCT2005 01NOV05 01NOV05 TE Connectivity HB01 - - SIZE A3 CAGE CODE 00779 DRAWING NO C-1625958 RESTRICTED TO -			