






ENTER DESCRIPTION EC NO: DG2006-0186 DRWN:PDAI CHKD: APPR: TKAN			2006/03/09 2006/03/09 2006/03/10			DESCRIPTION	REV	QUALITY SYMBOLS ▽=0 ⌒=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN			SCALE ---		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										mm	INCH	DRAWN BY PDAI		DATE 2006/03/07		TITLE DVI_A(F)-VGA(M) ADAPTER									
									4 PLACES	± ---	± ---	CHECKED BY ZXDENG		DATE 2006/03/07											
									3 PLACES	± ---	± ---	APPROVED BY BORON		DATE 2006/03/07		molex MOLEX INCORPORATED									
									2 PLACES	± ---	± ---														
									1 PLACE	± ---	± ---	DOCUMENT NO. SD-88741-012										SHEET NO. 1 OF 2			
									ANGULAR ± ---°																
MATERIAL NO. 88741-9100			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																						

7	6	5	4	3	2	1																																																															
E	NOTE:1. ADAPTOR COVER MATERIAL 1.1 UL GRADE ABS 1.2 COLOR: PANTONE 661C 2. DVI CONNCETOR SPECIFICATION 2.1 REFER TO PRODUCT SPEC. PS74320-0001. 2.2 CONTACT PLATING: AU FLASH. 3. ELECTRICAL PERFORMANCE 3.1 INSULATION RESISANCE: 20M Ohms Min 3.2 DIELECTRIC STRENGTH: 300V DC FOR 10 MILLISECONDS. 3.3 IMPEDANCE: 75 ± 10%Ohms ON THE CO-AXIAL WIRES. 4. ADAPTOR SPECIFICATION 4.1 REFER TO PRODUCT SPEC. PS88741-8700. 5. THIS PRODUCT MUST MEET MX RoHS COMPLIANCE.						E																																																														
D	6. CONNECTION DIAGRAM <table><tr><td>SHIELD</td><td>SHIELD</td><td>GROUND</td></tr><tr><td>C 5</td><td>PIN R6,G7,B8</td><td>ANLOG GROUND</td></tr><tr><td>C 4</td><td>PIN 13</td><td>HORIZONTAL SYNC</td></tr><tr><td>C 3</td><td>PIN 3</td><td>ANLOG</td></tr><tr><td>C 2</td><td>PIN 2</td><td>ANLOG</td></tr><tr><td>C 1</td><td>PIN 1</td><td>ANLOG</td></tr><tr><td>PIN 15</td><td>PIN 5,10</td><td>GROUND(+5V & HV SYNC)</td></tr><tr><td>PIN 14,16</td><td>PIN 9</td><td>POWER +5V/HOT PLUG DETECT</td></tr><tr><td>PIN 8</td><td>PIN 14</td><td>VERTICAL SYNC</td></tr><tr><td>PIN 7</td><td>PIN 12</td><td>DDC DATA</td></tr><tr><td>PIN 6</td><td>PIN 15</td><td>DDC CLOCK</td></tr><tr><td>DVI-A(F)</td><td>VGA(M)</td><td>CABLE FUNCTION</td></tr></table>						SHIELD	SHIELD	GROUND	C 5	PIN R6,G7,B8	ANLOG GROUND	C 4	PIN 13	HORIZONTAL SYNC	C 3	PIN 3	ANLOG	C 2	PIN 2	ANLOG	C 1	PIN 1	ANLOG	PIN 15	PIN 5,10	GROUND(+5V & HV SYNC)	PIN 14,16	PIN 9	POWER +5V/HOT PLUG DETECT	PIN 8	PIN 14	VERTICAL SYNC	PIN 7	PIN 12	DDC DATA	PIN 6	PIN 15	DDC CLOCK	DVI-A(F)	VGA(M)	CABLE FUNCTION	D																										
SHIELD	SHIELD	GROUND																																																																			
C 5	PIN R6,G7,B8	ANLOG GROUND																																																																			
C 4	PIN 13	HORIZONTAL SYNC																																																																			
C 3	PIN 3	ANLOG																																																																			
C 2	PIN 2	ANLOG																																																																			
C 1	PIN 1	ANLOG																																																																			
PIN 15	PIN 5,10	GROUND(+5V & HV SYNC)																																																																			
PIN 14,16	PIN 9	POWER +5V/HOT PLUG DETECT																																																																			
PIN 8	PIN 14	VERTICAL SYNC																																																																			
PIN 7	PIN 12	DDC DATA																																																																			
PIN 6	PIN 15	DDC CLOCK																																																																			
DVI-A(F)	VGA(M)	CABLE FUNCTION																																																																			
C	7. MATERIAL LIST <table><tr><td>F</td><td>ADAPTER SCREW 887806008</td></tr><tr><td>E</td><td>VGA D-SUB CONNECTOR</td></tr><tr><td>D</td><td>DVI_A FEMALE SCREW 887806066 887899320</td></tr><tr><td>C</td><td>DVI_A FEMALE CONNECTOR 743206001</td></tr><tr><td>B</td><td>DVI_A(F) TO VGA(M) ADAPTER BOTTOM COVER 887899313</td></tr><tr><td>A</td><td>DVI_A(F) TO VGA(M) ADAPTER TOP COVER 887899300</td></tr><tr><td>ITEM</td><td>DESCRIPTION</td></tr></table>						F	ADAPTER SCREW 887806008	E	VGA D-SUB CONNECTOR	D	DVI_A FEMALE SCREW 887806066 887899320	C	DVI_A FEMALE CONNECTOR 743206001	B	DVI_A(F) TO VGA(M) ADAPTER BOTTOM COVER 887899313	A	DVI_A(F) TO VGA(M) ADAPTER TOP COVER 887899300	ITEM	DESCRIPTION	C																																																
F	ADAPTER SCREW 887806008																																																																				
E	VGA D-SUB CONNECTOR																																																																				
D	DVI_A FEMALE SCREW 887806066 887899320																																																																				
C	DVI_A FEMALE CONNECTOR 743206001																																																																				
B	DVI_A(F) TO VGA(M) ADAPTER BOTTOM COVER 887899313																																																																				
A	DVI_A(F) TO VGA(M) ADAPTER TOP COVER 887899300																																																																				
ITEM	DESCRIPTION																																																																				
B							B																																																														
A	<table><tr><td rowspan="5">ENTER DESCRIPTION EC NO: DG2006-0186 DRWN:PDAI CHKD: APPR:TKAN</td><td rowspan="5">2006/03/09 2006/03/09 2006/03/10</td><td rowspan="5">DESCRIPTION REV</td><td>QUALITY SYMBOLS ▽=0 ▽=0</td><td>GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr></table></td><td>DIMENSION STYLE MM/IN</td><td>SCALE ---</td><td>DESIGN UNITS METRIC</td><td>THIRD ANGLE PROJECTION</td></tr><tr><td colspan="3"></td><td>DRAWN BY PDAI</td><td>DATE 2006/03/07</td><td colspan="3" rowspan="2">TITLE DVI_A(F)-VGA(M) ADAPTER</td></tr><tr><td colspan="3"></td><td>CHECKED BY ZXDENG</td><td>DATE 2006/03/07</td></tr><tr><td colspan="3"></td><td colspan="2">APPROVED BY BORON</td><td>DATE 2006/03/07</td><td colspan="3" rowspan="2">MOLEX INCORPORATED</td></tr><tr><td colspan="3"></td><td colspan="2">MATERIAL NO. 88741-9100</td><td>DOCUMENT NO. SD-88741-012</td><td>SHEET NO. 2 OF 2</td></tr><tr><td colspan="3"></td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A4</td><td colspan="3">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>						ENTER DESCRIPTION EC NO: DG2006-0186 DRWN:PDAI CHKD: APPR:TKAN	2006/03/09 2006/03/09 2006/03/10	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr></table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± ---	± ---	1 PLACE	± ---	± ---	DIMENSION STYLE MM/IN	SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				DRAWN BY PDAI	DATE 2006/03/07	TITLE DVI_A(F)-VGA(M) ADAPTER						CHECKED BY ZXDENG	DATE 2006/03/07				APPROVED BY BORON		DATE 2006/03/07	MOLEX INCORPORATED						MATERIAL NO. 88741-9100		DOCUMENT NO. SD-88741-012	SHEET NO. 2 OF 2				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A4	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			A
ENTER DESCRIPTION EC NO: DG2006-0186 DRWN:PDAI CHKD: APPR:TKAN	2006/03/09 2006/03/09 2006/03/10	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>2 PLACES</td><td>± ---</td><td>± ---</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td></tr></table>		mm				INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± ---	± ---	1 PLACE	± ---	± ---	DIMENSION STYLE MM/IN	SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																											
				mm	INCH																																																																
			4 PLACES	± ---	± ---																																																																
			3 PLACES	± ---	± ---																																																																
			2 PLACES	± ---	± ---																																																																
1 PLACE	± ---	± ---																																																																			
			DRAWN BY PDAI	DATE 2006/03/07	TITLE DVI_A(F)-VGA(M) ADAPTER																																																																
			CHECKED BY ZXDENG	DATE 2006/03/07																																																																	
			APPROVED BY BORON		DATE 2006/03/07	MOLEX INCORPORATED																																																															
			MATERIAL NO. 88741-9100		DOCUMENT NO. SD-88741-012				SHEET NO. 2 OF 2																																																												
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A4	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																															
tb_frame_A4_P_ME_T Rev. D 2004/04/02																																																																					
6	5	4	3	2	1																																																																