



FEATURES:

- Replaceable tip probe set with sharp stainless steel tip included. (Other tips are available, see model 6475.)
- Designed for most DMM's including Fluke, Wavetek Meterman, Amprobe, and others with safety-sheath banana jack inputs
- Thermoplastic elastomer outer coat provides comfortable grip and flexible strain relief
- Probe and banana plug are molded directly onto the wire for robust pull strength
- Wire is a high strand count silicone wire for extreme flexibility and high temperature resistance
- Banana plug spring is nickel plated Beryllium Copper for long insertion life

MATERIALS:

Probe:

Outer Insulation: Santoprene® rubber, color: gray

Inner Insulation: Polypropylene, color: one black, one red

Tip: sharp stainless steel

Wire: 18 AWG

Banana Plug: Nickel plated Brass

Spring – Nickel plated Beryllium Copper

Plug Insulation: Polypropylene, color: one black, one red

RATINGS:

IEC 1010-2-031, Category III 1000V

Operating Voltage: 1000 VRMS

Current: 5 Amperes

ORDERING INFORMATION: Model 6477

Includes a set of one black and one red test lead with two replaceable tips

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[6477](#)