



Call Today: 800-423-2734

LOGIN

Sign Up || Forgot Password

HOME

CATALOG

PRICING

TECHNICAL



MANUFACTURING

PARTS

ABOUT

SEARCH

3/16" Hex Male-Female Standoff

Lyn-Tron Part ID: **AA6978-0.625-25**Qty Available: **0**

Pricing & Availability:

[Click to obtain pricing for: AA6978-0.625-25](#)

CAD Drawings:

[View CAD Drawing](#) (Internet Explorer Only)[Download CAD Drawing](#) (Right Click and Save Target As... to download)[Download Autodesk Design Review© 2010](#)

Conformity Statement:

[View conformity statement: AA6978-0.625-25](#)

General Notes

- Material: Please visit our [material specifications](#) section for additional information.
- Thread Size: Variance in sizes between male and female threads are available.
- Thread Size - Body Length:
 - In short body lengths "Y" will be tapped to maximum depth.
 - Threads longer or shorter than "X" length are available
- Standard Finishes:
 - Zinc (Clear Chromate; Plate ID - 34) on brass and steel material.
 - Iridite (Gold Plate ID - 26) on aluminum material.

Material Code	Material Description
☒ AA	Aluminum (RoHS Compliant)
☐ AL	Aluminum
☐ BR	Brass (RoHS Compliant)
☐ SS	Stainless Steel (RoHS Compliant)
☐ ST	Steel (RoHS Compliant)

Basic Part No.	Thread Size	"X" Length	"Y" Min. Full Thd. Depth	Min. Body Length
☒ 6978	2-56	5/32	3/16	5/16
☐ 6979	4-40	3/16	1/4	3/8
☐ 6977	6-32	1/4	3/8	1/2

Length Code	Length Value
☐ 0.187	3/16
☐ 0.250	1/4
☐ 0.312	5/16
☐ 0.375	3/8
☐ 0.437	7/16
☐ 0.500	1/2
☐ 0.562	9/16

Applicable finishes based on material code -- AA

☐ 00	Plain - None
☐ 02	Caustic Etch
☐ 111	Dark Grey Anodize -- Type 2

HOME | CATALOG | CUSTOM | TECHNICAL | MANUFACTURING | ABOUT | SITE MAP

© 2009 Lyn-Tron, Inc. | 6001 S. Thomas Mallen Rd. Spokane WA 99224 | Phone: 800-423-2734 or 509-456-4545 | Fax: 509-456-0946