

**D2L20U****200V 1.5A****特長**

- 低ノイズ
- $t_{rr}=35\text{ns}$

**Feature**

- Low Noise
- $t_{rr}=35\text{ns}$

**用途**

- スイッチング電源
- フライホール
- 家電、OA、照明
- 通信、FA

**Main Use**


- Switching Regulator
- Fly Wheel
- Home Appliance, Office Automation, Lighting
- Communication, Factory Automation

**■外観図 OUTLINE**

Package : AX078

Unit:mm

Weight 0.38g (Typ)



外形図については新電元Webサイトをご参照下さい。捺印表示については捺印仕様をご確認下さい。

For details of the outline dimensions, refer to our web site. As for the marking, refer to the specification "Marking, Terminal Connection".


**■定格表 RATINGS****●絶対最大定格 Absolute Maximum Ratings** (指定のない場合  $T_I = 25^\circ\text{C}$ )

| 項目<br>Item                                | 記号<br>Symbol | 条件<br>Conditions                                                                                                                 | 品名<br>Type No.            | D2L20U  | 単位<br>Unit       |
|-------------------------------------------|--------------|----------------------------------------------------------------------------------------------------------------------------------|---------------------------|---------|------------------|
| 保存温度<br>Storage Temperature               | $T_{stg}$    |                                                                                                                                  |                           | -40~150 | $^\circ\text{C}$ |
| 接合部温度<br>Operation Junction Temperature   | $T_j$        |                                                                                                                                  |                           | 150     | $^\circ\text{C}$ |
| せん頭逆電圧<br>Maximum Reverse Voltage         | $V_{RM}$     |                                                                                                                                  |                           | 200     | V                |
| 出力電流<br>Average Rectified Forward Current | $I_O$        | 50Hz正弦波, 抵抗負荷<br>50Hz sine wave, Resistance load                                                                                 | $T_I = 125^\circ\text{C}$ | 1.5     | A                |
|                                           |              |                                                                                                                                  | $T_a = 25^\circ\text{C}$  | 1.3     |                  |
| せん頭サージ順電流<br>Peak Surge Forward Current   | $I_{FSM}$    | 50Hz正弦波, 非繰り返し1サイクルせん頭値, $T_j = 25^\circ\text{C}$<br>50Hz sine wave, Non-repetitive 1 cycle peak value, $T_j = 25^\circ\text{C}$ |                           | 40      | A                |

**●電氣的・熱的特性 Electrical Characteristics** (指定のない場合  $T_I = 25^\circ\text{C}$ )

|                                |               |                                                  |          |                    |
|--------------------------------|---------------|--------------------------------------------------|----------|--------------------|
| 順電圧<br>Forward Voltage         | $V_F$         | $I_F = 1.5\text{A}$ , パルス測定<br>Pulse measurement | MAX 0.98 | V                  |
| 逆電流<br>Reverse Current         | $I_R$         | $V_R = V_{RM}$ , パルス測定<br>Pulse measurement      | MAX 10   | $\mu\text{A}$      |
| 逆回復時間<br>Reverse Recovery Time | $t_{rr}$      | $I_F = 0.5\text{A}$ , $I_R = 1.0\text{A}$        | MAX 35   | ns                 |
| 熱抵抗<br>Thermal Resistance      | $\theta_{jl}$ | 接合部・リード間<br>Junction to lead                     | MAX 17   | $^\circ\text{C/W}$ |
|                                | $\theta_{ja}$ | 接合部・周囲間<br>Junction to ambient                   | MAX 105  |                    |

# 特性図 CHARACTERISTIC DIAGRAMS



\* Sine waveは50Hzで測定しています。  
 \* 50Hz sine wave is used for measurements.  
 \* 半導体製品の特性は一般的にバラツキを持っています。  
 Typical is a statistical average of the device's ability.  
 \* Semiconductor products generally have characteristic variation.  
 Typical is a statistical average of the device's ability.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Shindengen:

[D2L20U-7060](#) [D2L20U-7000](#) [D2L20U-7070](#) [D2L20U-4060](#) [D2L20U-4070](#) [D2L20U-5070](#) [D2L20U-5000](#)