





$\frac{7}{16}$ - 28 UNEF - 28 THD.

NOTES

1. FOR USE WITH CABLES RG-55, 58 & 223/U
2. FOR CABLING INSTRUCTIONS SEE CP-1004

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES:
FRACTIONS $\pm .010$ DECIMALS $\pm .004$ ANGLES $\pm 0^\circ 30'$
T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED THE SUM OF THEIR TOLERANCES.
2. REMOVE ALL BURRS, BREAK SHARP EDGES .003 MAX.
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.

11	1	BUSHING	
10	1	INSULATOR	
9	1	BNC CONTACT M	1-540-9M07
8	1	GASKET	
7	1	COUPLING	
6	1	C-RING	
5	1	BRAID CLAMP	704-5-MC7
4	1	GASKET	704-6-M39
3	1	WASHER	89C-1-MC7
2	1	BODY ASSEMBLY	
1	1	CLAMP NUT	704-7-MC7

ITEM	REQ'D	DESCRIPTION	DRAWING NO.
------	-------	-------------	-------------

REVISIONS

KA-51-18

CHANGES	
0	ER6355 22 AUG 68 A.M.E.
1	CN 7608C R.H.W. 4 JUN 69
2	CN 8085A W.L.A. 26 NOV 69
3	CN 11892A J.G.L. 2 FEB 73
4	CN 13446A J.L. 24 MAY 74
5	CN 25033C GL 9 SEP 83

REP.

FINISH

SPEC. KER 10004

MATL

SPEC.

TNC PLUG

DRAWN AVE DATE 22 AUG 68

APPR. EGR DATE 22 AUG 68

KINGS ELECTRONICS
40 MARLBOROUGH ROAD
TUCKAHOE, N. Y. 10707

KA-51-18

S-D