



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	POWER		SIGNAL	
		E1	P1 P2	1 2	E2
51952-135-- NOTE ③	D C B A		PA PA		



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
PA	[N/A]	POWER
E	[6.86]	SIGNAL
HA	[N/A]	HOLD-DOWN
H	[5.59]	SIGNAL

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
A	DG08-0209	JW	07/01/08	angles	0.XX ±0.13	projection		title	
					0.XXX ±0.051			2ACP + 8S	
				dr	0° ±2°			VERTICAL SOLDER HEADER	
				enr	JULIA WANG 07/01/08			product family	
				chr	JEROME CHEN 07/01/08			PwrBlade	
				appd	GARY HSIEH 07/01/08			code	
					JOSEPH HSIA 07/01/08			213	
sheet	revision	A	A	A	A	scale	1:1	size	dwg no
index	sheet	1	2	3	4			A	51952-135
									sheet
									1 of 4


cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51952-135--
NOTE 3



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
A				linear	0.XX ±0.13	projection		title 2ACP + 8S VERTICAL SOLDER HEADER	
				angles	0.XXX ±0.051				
				dr	0° ±2°	MIM		product family	PwrBlade
				enrg	JULIA WANG 07/01/08	scale		size	dwg no
				chr	JEROME CHEN 07/01/08	1:1		A	51952-135
				appd	GARY HSIEH 07/01/08				
					JOSEPH HSIA 07/01/08				
sheet index	revision sheet								

cage code 22526

Pro/E

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER																																																																																													
51952-135-- NOTE 3																																																																																													
NOTES:																																																																																													
1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.																																																																																													
CONNECTOR NOTES:																																																																																													
2 HOUSING MATERIAL: UL 94 V-0 GLASS FILLED HIGH-TEMP THERMOPLASTIC POWER CONTACT MATERIAL: COPPER ALLOY SIGNAL PIN MATERIAL: COPPER ALLOY																																																																																													
3. PLATING: 51952-135 ,51952-135LF PLATING SPEC. WAS SHOWN IN THE PRINT OF 10064183.																																																																																													
4 MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.																																																																																													
5. PRODUCT SPECIFICATION GS-12-149. APPLICATION SPECIFICATION BUS-20-067.																																																																																													
6. PACKAGED IN TRAYS.																																																																																													
PCB NOTES:																																																																																													
7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.																																																																																													
8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.																																																																																													
9 $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH 0.008 MIN SnPb OR Sn OVER .001 [0.03] TO 0.08 Cu PLATING TO ACHIEVE $\varnothing 1.02 \pm .07$ HOLE.																																																																																													
10 "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.																																																																																													
11 CONNECTOR KEEP-OUT ZONE.																																																																																													
<table><tr><td colspan="4">mat'l code</td><td colspan="2">tolerances unless otherwise specified</td><td colspan="2">CUSTOMER</td><td colspan="2"> www.fciconnect.com</td></tr><tr><td>ltr</td><td>ecn no.</td><td>dr</td><td>date</td><td rowspan="3">linear</td><td colspan="2">0.X $\pm$ 0.3</td><td colspan="2">COPY</td><td rowspan="3">title 2ACP + 8S VERTICAL SOLDER HEADER</td></tr><tr><td>A</td><td></td><td></td><td></td><td colspan="2">0.XX $\pm$ 0.13</td><td colspan="2">projection </td></tr><tr><td></td><td></td><td></td><td></td><td colspan="2">0.XXX $\pm$ 0.051</td><td colspan="2"></td></tr><tr><td></td><td></td><td></td><td></td><td>angles</td><td colspan="2">0° $\pm$ 2°</td><td colspan="2"></td><td rowspan="5">product family PwrBlade code 213 sheet 4 of 4</td></tr><tr><td></td><td></td><td></td><td></td><td>dr</td><td>JULIA WANG</td><td>07/01/08</td><td colspan="2">scale 1:1</td></tr><tr><td></td><td></td><td></td><td></td><td>enrg</td><td>JEROME CHEN</td><td>07/01/08</td><td colspan="2">size A</td></tr><tr><td></td><td></td><td></td><td></td><td>chr</td><td>GARY HSIEH</td><td>07/01/08</td><td colspan="2">dwg no 51952-135</td></tr><tr><td></td><td></td><td></td><td></td><td>appd</td><td>JOSEPH HSIA</td><td>07/01/08</td><td colspan="2">cage code 22526</td></tr><tr><td colspan="2">sheet index</td><td colspan="2">revision sheet</td><td></td><td></td><td></td><td></td><td></td><td></td></tr></table>		mat'l code				tolerances unless otherwise specified		CUSTOMER		www.fciconnect.com		ltr	ecn no.	dr	date	linear	0.X $\pm$ 0.3		COPY		title 2ACP + 8S VERTICAL SOLDER HEADER	A				0.XX $\pm$ 0.13		projection 						0.XXX $\pm$ 0.051								angles	0° $\pm$ 2°				product family PwrBlade code 213 sheet 4 of 4					dr	JULIA WANG	07/01/08	scale 1:1						enrg	JEROME CHEN	07/01/08	size A						chr	GARY HSIEH	07/01/08	dwg no 51952-135						appd	JOSEPH HSIA	07/01/08	cage code 22526		sheet index		revision sheet							
mat'l code				tolerances unless otherwise specified		CUSTOMER		www.fciconnect.com																																																																																					
ltr	ecn no.	dr	date	linear	0.X $\pm$ 0.3		COPY		title 2ACP + 8S VERTICAL SOLDER HEADER																																																																																				
A					0.XX $\pm$ 0.13		projection 																																																																																						
					0.XXX $\pm$ 0.051																																																																																								
				angles	0° $\pm$ 2°				product family PwrBlade code 213 sheet 4 of 4																																																																																				
				dr	JULIA WANG	07/01/08	scale 1:1																																																																																						
				enrg	JEROME CHEN	07/01/08	size A																																																																																						
				chr	GARY HSIEH	07/01/08	dwg no 51952-135																																																																																						
				appd	JOSEPH HSIA	07/01/08	cage code 22526																																																																																						
sheet index		revision sheet																																																																																											