

## Secondary Side Synchronous Post Regulator

### FEATURES


- Practical Operation at Switching Frequencies up to 1MHz
- Wide Band Error Amplifier
- Undervoltage Lockout with Hysteresis
- Output Active Low During UVLO
- Soft Start/Maximum Duty Cycle Control
- Trimmed Bandgap Reference
- Internally Regulated 15V Boost Supply
- Short Circuit Protection with Programmable Delay

### DESCRIPTION

The UC3584 is a low voltage, Secondary Side Synchronous Post Regulator. It is intended to be used for auxiliary output voltage regulation in single secondary winding, multiple output power supplies (for more details refer to the Application Section of this Data sheet). The UC3584 is most suited for systems where the main output is regulated between 5V and 14V. Output voltages regulated by the UC3584 can range from virtually 0V up to the output voltage of the main output.

Auxiliary output voltage regulation with the UC3584 uses leading edge modulation making it compatible to primary side peak current or voltage mode control. The UC3584 clock circuit is synchronized to the switching frequency utilizing the falling edge of the transformer's secondary winding waveform.

### TYPICAL APPLICATION DIAGRAM.




UDG-99062

## ABSOLUTE MAXIMUM RATINGS

Supply Voltage ..... 20V  
 $V_{FLT}$  Voltage ..... 50V, 30V at 2A  
 Supply Current ..... 50mA  
 Analog Inputs. .... -0.3 to 20V  
 SYNC Maximum Sink Current. .... 600 $\mu$ A  
 PWM Driver,  $I_{OUT}$  .....  $\pm 300$ mA  
 PWM Driver,  $I_{OUT}$  (Peak). ....  $\pm 1.5$ A  
 Maximum Operating Frequency ..... 1MHz

Power Dissipation at  $T_A = 60^\circ\text{C}$  ..... 1W  
 Storage Temperature .....  $-65^\circ\text{C}$  to  $150^\circ\text{C}$   
 Junction Temperature. ....  $-55^\circ\text{C}$  to  $150^\circ\text{C}$   
 Lead Temperature (Soldering, 10 sec.) .....  $300^\circ\text{C}$   
*Currents are positive into, negative out of specified terminal.  
 Consult Packaging Section of Databook for thermal limitations  
 and considerations of packages.*

## CONNECTION DIAGRAMS



## ORDERING INFORMATION

	TEMPERATURE RANGE	PACKAGE
UC1584J	$-55^\circ\text{C}$ to $+125^\circ\text{C}$	CDIP
UC2584DW	$-40^\circ\text{C}$ to $+85^\circ\text{C}$	SOIC-Wide
UC2584N		PDIP
UC3584DW	$0^\circ\text{C}$ to $+70^\circ\text{C}$	SOIC-Wide
UC3584N		PDIP

**ELECTRICAL CHARACTERISTICS:** Unless otherwise specified,  $T_A = 0^\circ\text{C}$  to  $70^\circ\text{C}$  for the UC3584,  $-40^\circ\text{C}$  to  $85^\circ\text{C}$  for the UC2584, and  $-55^\circ\text{C}$  to  $125^\circ\text{C}$  for the UC1584,  $V_{CC} = 15\text{V}$ .  $T_A = T_J$ .


PARAMETERS	TEST CONDITIONS	MIN	TYPE	MAX	UNITS
<b>Error Amplifier</b>					
FB	COMP = FB	1.468	1.5	1.532	V
$I_{FB}$	$V_{COMP} = V_{FB}$	150	300	450	nA
COMP $V_{OL}$	FB = 1.6V, $I_{COMP} = 200\mu\text{A}$		50	400	mV
COMP $V_{OH}$	FB = 1.4V, $I_{COMP} = -200\mu\text{A}$	5.1	5.5	7	V
AVOL		60	80		dB
PSRR (COMP)	COMP = FB, $V_{CC} = 14\text{V}$ to $16\text{V}$	60			dB
GBW Product	F = 100kHz	5	10		MHz
<b>Oscillator</b>					
Frequency	$R_T = 3.75\text{k}\Omega$ , $C_T = 400\text{pF}$ , No Synchronization		500		kHz
Ramp Low	$R_T = 3.75\text{k}\Omega$ , $C_T = 400\text{pF}$ , No Synchronization		1.75		V
Ramp High	$R_T = 3.75\text{k}\Omega$ , $C_T = 400\text{pF}$ , No Synchronization		3.5		V
Ramp Amplitude	$R_T = 3.75\text{k}\Omega$ , $C_T = 400\text{pF}$ , No Synchronization		1.75		V
<b>PWM</b>					
Maximum Duty Cycle	COMP = 4.5V	90			%
Minimum Duty Cycle	COMP = 0V			0	%
<b>PWM DRIVER</b>					
$V_{SAT}$ High	$V_{FLT} - V_{OUT}$ , $I_{OUT} = -100\text{mA}$		2.5	3	V
$V_{SAT}$ Low	$V_{OUT} - V_{SRC}$ , $I_{OUT} = 50\text{mA}$		0.8	2.2	V
$T_{RISE}$	Load = 1nF, SRC = 0V, Measure $V_{OUT}$ 1V to 9V		75	100	ns
$T_{FALL}$	Load = 1nF, SRC = 0V, Measure $V_{OUT}$ 9V to 1V		25	100	ns

**ELECTRICAL CHARACTERISTICS:** Unless otherwise specified,  $T_A = 0^\circ\text{C}$  to  $70^\circ\text{C}$  for the UC3584,  $-40^\circ\text{C}$  to  $85^\circ\text{C}$  for the UC2584, and  $-55^\circ\text{C}$  to  $125^\circ\text{C}$  for the UC1584,  $V_{CC} = 15\text{V}$ .  $T_A = T_J$ .

PARAMETERS	TEST CONDITIONS	MIN	TYPE	MAX	UNITS
<b>Soft Start</b>					
Charge Current			30		$\mu\text{A}$
Discharge Current			1		$\text{mA}$
SS Delay	$C_{SS} = 500\text{nF}$		50		$\text{ms}$
<b>Fault Latch</b>					
Charge Current			30		$\mu\text{A}$
Discharge Current			5		$\text{mA}$
Fault Latch Delay	$CDLY = 500\text{nF}$		50		$\text{ms}$
<b>UVLO</b>					
VCC On			10.5		V
Hysteresis			1.7		V
<b>Regulated Voltage</b>					
VREG	$I_{REG} = 0\text{mA}$ to $1\text{mA}$	4.8		5.2	V
<b>VCC Regulator</b>					
VCC	Boost inductor connected to 5V	14	15	16	V
Icc	No Load, Boost Circuitry Inactive		12	40	$\text{mA}$
	No Load, Boost Circuitry Active (Note 1)		55		$\text{mA}$

Note 1: Guaranteed by design. Not 100% tested in production.

## BLOCK DIAGRAM



## PIN DESCRIPTIONS

**BST1:** Collector of the boost switch. This is the connection point of the external boost inductor and boost diode. The boost converter generates the bias supply for the UC3584 from the regulated 5V output.

**BST2:** See BST1. BST2 must be connected externally to BST1 pin.

**CDLY:** Delay Set. External CDLY capacitor sets the delay from the time Short Circuit condition is detected and Fault Condition is asserted.

**COMP:** Output of the Voltage Error Amplifier.

**CT:** Connect the Timing Capacitor between CT and GND.

**FB:** Inverting Input of the Voltage Error Amplifier.

**GND:** Analog System Ground.

**OUT:** Output of the floating driver for an external, N-channel MOSFET.

**PGND:** Power Ground. This is the reference node for the boost bias supply regulator. PGND and GND must be connected externally.

**RT:** A Timing Resistor connected between RT and GND sets the discharge current of the timing capacitor.

**SRC:** Source connection of the floating driver to the external switch.

**SS:** Soft Start. An external capacitor is connected between SS and GND to set the duration of the Soft Start cycle.

**SYNC:** Synchronization Pin. The UC3584 is synchronized from the falling edge of the transformer's secondary winding. Voltage must exceed 1V at minimum input line.

**VCC:** Bias supply of the chip, approximately 15V. This is also the output of the boost regulator. The VCC pin must be decoupled to PGND.

**VFLT:** Positive rail of the floating driver's bias supply. Decouple to SRC using a high frequency (ceramic) capacitor.

**VREG:** Output of the internal 5V regulated supply. Must be decoupled to GND.

## APPLICATION INFORMATION

### Biasing the UC3584

Bias supply for the UC3584 is generated from the main output of the power supply by a boost regulator. The inductor, diode and capacitor of the boost converter are external components, while the boost switch is internal to the chip. The boost converter operates in a burst mode with a built-in hysteresis of approximately 1V centered at 15V. This is a bang-bang controller and when enabled has a fixed duty cycle of 75%.

### Undervoltage Detection

The UVLO circuit of the UC3584 monitors the voltage on VCC. During power up and power down, the pulse width modulator and the output driver are disabled and OUT is held active low. Operation is enabled when VCC reaches 10.5V. The UVLO circuitry has a built-in hysteresis of 1.7V (10.5V to 8.8V) thus VCC must drop below 8.8V in order to assert UVLO again.

### Precision Reference

An internal precision bandgap reference provides accurate voltages to the error amplifier and other control sections of the IC. A buffered 5V regulated voltage is also available for external circuitry on the VREG pin. This pin must be decoupled to the signal GND connection by a good quality high frequency capacitor.

### Oscillator and Trailing Edge Synchronization

The UC3584 is outfitted with a synchronizable oscillator which also generates a ramp signal across the CT capacitor for the PWM comparator. For easy implementation of the leading edge pulse width modulation technique, the oscillator has an inverted ramp waveform as shown in Fig. 1. The free running oscillator frequency is determined by the timing components, RT and CT, according to the following approximate equations:

$$R_T = \left( \frac{9.3}{1 - D_{MAX}} \right)^{1.7}$$

$$f_{OSC} = \frac{2 - (8.2 \times 10^8 \cdot C_T)}{(R_T \cdot C_T)^{0.9}}$$

where

RT is the timing resistor, its value should be between 1kΩ and 100kΩ,

CT is the timing capacitor,

DMAX is the desired maximum duty cycle, and

fosc is the free running oscillator frequency.

Figure 2 graphically depicts the measured frequency data.

## APPLICATION INFORMATION (cont.)




Figure 1. Trailing edge synchronization, leading edge modulation.

### Edge Modulation

During normal operation the oscillator must be synchronized to the falling edge of the transformer secondary waveform. Synchronization is achieved by connecting SYNC to the secondary winding via a resistor divider. The resistor divider must be chosen to provide a SYNC pin voltage in excess of 1V at the lowest operating voltage on the transformer secondary winding. The UC3584 will generate a narrow internal synchronization pulse which will synchronize the oscillator to the switching frequency of the main converter.

### PWM and Output Driver

The UC3584 employs leading edge modulation technique to set the required on time of its output. Leading edge modulation is preferred for secondary side regulation in multiple output converters to prevent ambiguity in the primary current waveform. In fact, this is the only feasible technique to preserve compatibility with primary side peak current mode control.

As Fig. 1 depicts the UC3584 utilizes voltage mode control to regulate output voltage. The output pulse width (the on-time of the MOSFET switch) is determined on a cycle-by-cycle basis by comparing the output of the voltage error amplifier and the ramp waveforms across the timing capacitor. OUT is asserted when the voltage on COMP exceeds the voltage on CT. There are three more conditions which must be satisfied to obtain an active high on the OUT pin. These conditions are:

1. VCC within normal range (UVLO is inactive),
2. No fault condition is detected,
3.  $C_T$  is discharging.

During the fast charging time of the  $C_T$  capacitor is held low.

Ultimately, the output of the PWM circuitry controls the conduction interval of an external N-channel MOSFET switch in the power supply. The UC3584 employs an on-board, floating gate driver circuit to interface to the external switch. An external capacitor connected between VFLT and SRC acts as a floating power supply for




Figure 2. Oscillator frequency vs.  $R_T$  with  $C_T$  as a parameter.

## APPLICATION INFORMATION (cont.)

the driver during the on-time of the switch. Charge is being replenished to the bootstrap capacitor during the off-time of the switch through the bootstrap diode connected between VCC and VFLT as shown in the typical application diagram.

### Soft Start

The UC3584 Soft Start circuitry is designed to implement closed loop startup of the power supply output. During Soft Start, the reference to the noninverting input of the error amplifier is controlled by the voltage across the soft start capacitor on SS. As this voltage rises, it provides an increasing reference to the error amplifier. Once the soft start capacitor charges above the 1.5V precision reference of the error amplifier, SS gets disconnected from the noninverting input of the error amplifier. This technique allows the error amplifier to stay in its linear mode and to regulate the output voltage of the power supply according to the gradually increasing reference voltage on its noninverting input. Further advantage of the closed loop start up scheme is the absence of output voltage overshoot during power up of the power supply output.

### Fault Detection

Fault Detection feature is implemented to detect excessive overload conditions. Under these conditions the error amplifier output goes high to command the maximum duty cycle. As soon as the error amplifier's output exceeds 5V, the fault delay capacitor connected to the CDLY pin starts charging. If  $C_{DLY}$  capacitor voltage reaches 2V before the error amplifier output falls back

below 5V, a fault condition is declared, the PWM output is disabled and soft start cycle is initiated. Under persistent fault conditions the UC3584 will continuously cycle through soft start sequence, attempting to bring the output to its regulated, nominal voltage. The value of  $C_{DLY}$  capacitor should be chosen large enough to delay the activation of the fault sequence in case of load transients which can also cause the error amplifier output to go high temporarily.

### Error Amplifier

The Error Amplifier of the UC3584 is used to regulate the voltage of an auxiliary output in a power supply. The noninverting input of the error amplifier is connected to an internal, 1.5V reference. The inverting input (FB pin) is tied to an output voltage divider. The compensation network of the negative feedback loop is connected between the amplifier's output (COMP pin) and FB. The noninverting input of the error amplifier is also connected to the SS node through a diode. This arrangement allows closed loop soft start for the output of a power supply regulated by the UC3584. Closed loop soft start assures that the error amplifier is kept in active mode and the output voltage of the converter follows the reference voltage on its noninverting input as it ramps up (following the SS node). If a fault condition is detected, SS node gets pulled to ground, forcing the error amplifier's reference low. Consequently, the error amplifier's output voltage goes low and duty cycle is reduced.

## PACKAGING INFORMATION

Orderable Device	Status <sup>(1)</sup>	Package Type	Package Drawing	Pins	Package Qty	Eco Plan <sup>(2)</sup>	Lead/Ball Finish	MSL Peak Temp <sup>(3)</sup>
UC3584DW	OBSOLETE	SOIC	DW	16		TBD	Call TI	Call TI
UC3584DWTR	OBSOLETE	SOIC	DW	16		TBD	Call TI	Call TI
UC3584N	OBSOLETE	PDIP	N	16		TBD	Call TI	Call TI

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>

### Applications

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Broadband	<a href="http://www.ti.com/broadband">www.ti.com/broadband</a>
Digital Control	<a href="http://www.ti.com/digitalcontrol">www.ti.com/digitalcontrol</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Military	<a href="http://www.ti.com/military">www.ti.com/military</a>
Optical Networking	<a href="http://www.ti.com/opticalnetwork">www.ti.com/opticalnetwork</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Telephony	<a href="http://www.ti.com/telephony">www.ti.com/telephony</a>
Video & Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless">www.ti.com/wireless</a>

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2008, Texas Instruments Incorporated