








PIN NUMBER	DIM. L(PIN LENGTH)
25, 26	3.50
ALL OTHER PINS	4.25
1,13,38,50	5.00



THE PUSH BUTTON POSITION



mot'l. code			tolerances unless otherwise specified			CUSTOMER COPY			title		
lir	ecn no	dr	date	linear	angles	projection	scale	product family	code	sheet	code
A	T05-0258	A.C.	11/21/05	.XX ± 0.20	0° ± 2°	MM	NA	CF ASS'Y,BELOW MOUNT	TWN	1 of 4	
B	T06-0038	A.C.	3/03/06	.XXX ± 0.10				LEFT PUSH, S/O=0mm			
C	T08-1174	S.LIN	10/12/08								
sheet revision			C	C	C	C	C	C	C	C	C
index			1	2	3						



Recommended PCB Pattern

mot'l. code		tolerances unless otherwise specified		CUSTOMER COPY		title	
l/r	ecn no	dr	date	linear	projection	product family	code
A	T05-0258	A.C.	11/21/05	.XX ± 0.20	MM	CF ASS'Y,BELOW MOUNT	TWN
B	T06-0038	A.C.	3/03/06	.XXX ± 0.10	MM	LEFT PUSH, S/O=0mm	sheet
C	T08-1174	S.LIN	10/12/08	0° ± 2°	MM	10061862	3 of 4
sheet		revision	C	C	C	scale	code
index		sheet	1	2	3	NA	code

1 | 2

ACAD

3 |


4

NOTES :

1. THIS IS THE ASSEMBLY TYPE WHICH INCLUDES HEADER 10053868-E1501 AND EJECTOR 10053869-0050LF.
2. MATERIAL :
INSULATOR : HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING: UL94V-0
COLOR: IVORY
CONTACT : COPPER ALLOY
GROUND MOUNTING EAR: COPPER ALLOY
COVER: STAINLESS STEEL.
ARM: STAINLESS STEEL.
PUSH ROD : HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING: UL94V-0
COLOR: BLACK.
RIVET : COPPER ALLOY
3. PLATING :
CONTACT AREA: SELECTIVE GOLD (SEE P/N DESCRIPTION)
UNDER PLATING: 50u" NICKEL OVERALL
SOLDER TAIL AREA: 100u" TIN/LEAD OR 100u" MATTE TIN
GROUND MOUNT EAR AREA: 100u" TIN/LEAD OR 100u" MATTE TIN
4. SOLDER TAILS TO BE WITHIN 0.05 UPWARD AND 0.2 DOWNWARD FROM Z-DATUM PLACE, AND COPLANARITY OF SOLDER TAILS TO BE WITHIN 0.10mm.
5. PRODUCT SPEC: GS-12-240.
6. PACKAGING SPEC: GS-14-1040.

7. Part Number Description:



P/N: 10061862-X150 X 0 X




8. THIS PRODUCT (10061862-XXXXXXLF) MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008.
9. THIS PRODUCT (10061862-XXXXXX) MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008 EXCEPT FOR Pb.
10. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, IR OR VAPER PHASE REFLOW OVEN.
11. THE PRODUCTS WHERE THE PART NUMBER ENDS IN "LF" MEET THE CRITERIA SHOWN IN THE NOTES 8 AND 10.



mot'l. code				tolerances unless otherwise specified				CUSTOMER COPY		FCI	
litr	ecn no	dr	date	linear				projection	title	www.fciconnect.com	
A	105-0258	A.C.	11/21/05	.XX ± 0.20					CF ASS'Y,BELOW MOUNT		
B	106-0038	A.C.	3/03/06	.XXX ± 0.10					LEFT PUSH, S/O=0mm		
C	108-1174	S.LIN	10/12/08	0° ±2°							
				dr ALLEN CHANG	11/03/05			MM	product family	CF	code
				engr ALLEN CHANG	11/03/05			scale	size	dwg no	TWN
				chr STERLING LIN	11/03/05			NA			sheet
				oppl H.C LIU	11/03/05						2 of 4
sheet	revision	C	C	C							
index	sheet	1	2	3							




NOTES:
1.CARRIER TAPE: PS T=0.4MM
2.COVER TAPE: PE
3.PLASTIC HUB: PS



COMPOSITION OF PACKAGING

CONNECTOR PACKAGING
AREA QUANTITY:150PCS



mot'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
lir	ech no	dr	date	linear	.XX ± 0.30	projection	title
A	T05-0258	A.C.	11/21/05		.XX ± 0.20		CF ASS'Y,BELOW MOUNT
B	T06-0038	A.C.	3/03/06		.XX ± 0.10		LEFT PUSH, S/O=0mm
C	T08-1174	S.LIN	10/12/08	angles	0° ± 2°		
		dr	allen chang	11/03/05			
		eng	allen chang	11/03/05			
		chr	STERLING LIN	11/03/05			
		appd	H.C LIU	11/03/05			
sheet	revision	C	C	C		scale	product family
index	sheet	1	2	3		NA	CF

1 | 2

1 | 2

3 |

4