



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Single-Phase Basic PDU, 3.3/3.8kW 20A 208/240V, 1U Horizontal Rackmount, 2 C19 and 12 C13 outlets, NEMA L6-20P input plug

MODEL NUMBER: PDUH20HVL6



Highlights

- Basic single phase 20A 208/240V PDU
- 1U horizontal rackmount installation
- L6-20P input; 15 ft. / 4.5m line cord
- 2 C19 and 12 C13 outlets
- Reversible housing; 3.75 in. / 9.5cm depth

Applications

- Ideal for datacenters, network closets, equipment racks and a wide variety of other application types

Package Includes

- PDUH20HVL6 PDU rackmount PDU
- Owner's manual

Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution for critical IT equipment in wiring closets, server rooms and equipment racks. Supplies continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Features

- 20A single phase 208/240V Basic Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- Attached NEMA L6-20P input with 15 ft. / 4.5m line cord
- 1U horizontal rackmount format installs in one rack space
- 14 outlets (2 C19, 12 C13)
- Adjustable mounting brackets enable installation in 2 or 4 post racks, plus additional support for wallmount and under-counter mounting
- Mounting ears are reversible for front or rear facing rackmount installation
- Back panel grounding lug

Specifications

General Info	
Product Group	PDUS
OVERVIEW	
PDU Type	Basic
OUTPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Output Capacity Details	3.3kW (208V input), 3.8kW (240V input), 3.2kW (200V input); 20A maximum (Agency de-rated to 16A continuous)
Frequency Compatibility	50 / 60 Hz
Output Nominal Voltage	200-240V nominal, single phase
Overload Protection	n/a
Outlet Quantity / Type	2 C19, 12 C13
Outlet Type	IEC-C13, IEC-C19
INPUT	
PDU Input Voltage	200; 208; 240
Maximum Input Amps	20
Maximum Input Amps Details	Agency de-rated to 16A continuous
PDU Plug Type	NEMA L6-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.5
Input Cord Details	Input cable is attached
Input Phase	Single-Phase
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.25 x 20.5 x 9.5
Shipping Dimensions (hwd / cm)	5.7 x 52.1 x 24.1
Shipping Weight (lbs.)	5.9
Shipping Weight (kg)	2.7
Unit Dimensions (hwd / in.)	1.75 (1U) x 17.25 x 3.75
Unit Dimensions (hwd / cm)	4.45 x 43.8 x 9.5
Unit Weight (lbs.)	3.75
Unit Weight (kg)	1.7
Material of Construction	Sheet Metal
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
Form Factors Supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
PDU Form Factor	Horizontal (1U, 2U, etc)
Outlets Measurement (Center to Center)	Distance between front (C13) outlets = 28.75mm; Distance between rear (C19) outlets = 55mm; Distance between rear (C13) outlets = 28.75mm
SPECIAL FEATURES	
Appearance	All black color scheme
TVSS Grounding	Rear grounding lug



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CERTIFICATIONS	
Certifications	Tested to UL 60950 (USA), CSA (Canada), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.