



SERIES 125 AND 126 RETAINERS

WEIGHT

.40 g/cm (.036 oz/in)

MATERIALS AND FINISH

Material:

.41 (.016) thick Stainless
Steel Type 301, Cond.
1/2 H, ASTM -A240

Finish:


Passivated per MILS-5002

SPRING RATE

60.4N/cm (34.5lbs/in)
of deflection per spring finger

Dash No.	PCB Thickness	B Dimension +0.38 (.015) -0.0 (.000)	G Dimension +0.0 (.00) -0.80 (.03)
-06	1.6 (1/16)	1.91 (.075)	1.14 (.045)
-09	2.4 (3/32)	2.67 (.105)	1.91 (.075)

125 Shown, 126 Opposite



Part Number Code Example:

125-06-4.25

Series 125 passivated stainless steel,
107.95 (4.25) long designed for 1.6 (.063)
thick printed circuit boards

Part Number Code

125 or 126	-06	- 3.25
PCB Thickness		
1.6 (.063)		06
2.4 (.094)		09
Length		
31.75 (1.25) to 311.15 (12.25)		3.25
in 25.4 (1.00) increments		
Other lengths available on request		

