



DO NOT
SCALE FROM
THIS PRINT



NOTES:

1. MINIMUM CONTACT RETENTION: 6 OZ
2. MINIMUM GROUND PLANE RETENTION: 8 OZ
3. © REPRESENTS A CRITICAL DIMENSION.
4. PARTS ARE MOLD TO POSITION.
5. NOTE DELETED.
6. MAXIMUM VARIANCE OF .002[0.05].
7. DIMENSION APPLIES TO CONTACTS AND GROUND PLANES, INDEPENDENT OF GROUND PLANES AND CONTACTS RESPECTIVELY.
8. -L PLATING CAN BE SUBSTITUTED FOR -F PLATING.
9. GROUND PLANE PRESS HEIGHT MUST BE .003[0.08] LESS THAN THE MAX HEIGHT OR .001[0.03] GREATER THAN THE MINIMUM HEIGHT OF THE TERMINALS.
10. NOTE DELETED.
11. FOR -100 AND -125 POSITIONS USE C-269-11-X, DO NOT SUB C-126-01-X.
12. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.
13. CHECK ONCE PER BANK ALTERNATING SIDES FOR MULTIPLE BANK PARTS.
14. AVAILABLE FOR EXISTING CUSTOMERS ONLY.

FIG 1

-A: ALIGNMENT PIN OPTION
(QSS-075-01-XXX-D-A SHOWN)

QSS-XXX-XX-XXX-D-XXX

No OF POSITIONS

-025, -050, -075,
*-100, *-125

*SEE NOTES 11 & 14

LEAD STYLE

-01: .1430[3.632]

PLATING SPECIFICATION

(SEE NOTES 8 & 11)

-F: 3µ" FLASH SELECTIVE GOLD IN
CONTACT AREA, MATTE TIN ON TAIL
(USE C-126-21-F & T-1G2-01-F)
(SEE NOTE 8)

-L: 10µ" LIGHT SELECTIVE GOLD, IN
CONTACT AREA, MATTE TIN ON TAIL
(USE C-126-21-L & T-1G2-01-L)

-H: 30µ" HEAVY GOLD IN CONTACT
AREA, 3µ" GOLD ON TAIL
(USE C-126-21-H & T-1G2-01-G)

-C: 50µ" HEAVY GOLD IN CONTACT
AREA, MATTE TIN ON TAIL
(USE C-126-21-C & T-1G2-01-L)

-STL: 30µ" HEAVY SELECTIVE GOLD IN
CONTACT AREA, TIN LEAD ON TAIL
(USE C-126-21-STL & T-1G2-01-STL)

-FTL: 3µ" FLASH SELECTIVE GOLD IN
CONTACT AREA, TIN LEAD ON TAIL
(USE C-126-21-FTL & T-1G2-01-FTL)


OPTION

- A: ALIGNMENT PINS
(USE QSS-25-XX-D-XX-A)
(NOT AVAILABLE WITH -LC)
- LC: LOCKING CLIPS (SEE NOTE 12)
(USE LC-08-TM-01, SEE FIG 2, SHT 2)
(NOT AVAILABLE WITH -A)
- K: POLYIMIDE FILM PAD
(USE K-DOT-.325-.450-.005)
(SEE FIG 3, SHT 2)
- TR: TAPE & REEL (75 POS MAX)
(50 POS MAX FOR -GP)
- GP: GUIDE POSTS
(USE QSS-25-01-D-XX-X-GP)
(SEE FIG 4, SHT 3)
(NOT AVAILABLE WITH -LS2)
- LS2: LOCKING SCREW
(USE QSS-25-01-D-XX-LS2)
(SEE FIG 5, SHT 3)
(NOT AVAILABLE WITH -GP)
(FOR MATING WITH
QTS-...-RA-...-LS2)

ROW SPECIFICATION

-D: DOUBLE (USE QSS-25-XX-D-XX)

No OF BANKS



SECTION "A"- "A"
SCALE 3:1

TABLE 2

No OF POS	"A"	"B"
-025	.838 [21.27]	.788 [20.00]
-050	1.625 [41.28]	1.575 [40.01]
-075	2.413 [61.28]	2.363 [60.01]
*-100	3.200 [81.28]	3.150 [80.01]
*-125	3.988 [101.28]	3.938 [100.01]

* = SEE NOTES 11 & 14

TABLE 1

No OF POSITIONS	COPLANARITY (INCLUDING GND PLANE)
-025 THRU -050	.0040[.102]
-075, *-100, *-125	.0060[.152]

* = SEE NOTES 11 & 14

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES[MM]

TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.01[.3] 2°
.XXX: ±.005[.13]
.XXXX: ±.0020[.051]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING
INSULATOR: LCP, UL94V-0; COLOR: BLACK
CONTACT: PHOS BRONZE
GROUND PLANE: PHOS BRONZE

SHEET SCALE: 1.5:1

DESCRIPTION:

.635mm DOUBLE ROW HS SOCKET ASSEMBLY

DWG. NO.

QSS-XXX-XX-XXX-D-XXX

BY: DEAN P

6/28/1999

SHEET 1 OF 3

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322




FIG 2
-LC: LOCKING CLIP OPTION
(QSS-075-01-XXX-D-LC SHOWN)
(DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)




FIG 3
-K: POLYIMIDE FILM PAD
(USE K-DOT-.325-.450-.005)

TABLE 3						
No OF POS	"R"			"S"		
	-LC, -A	-GP	-LS2	-LC, -A	-GP	-LS2
-025	.838 [21.27]	1.217 [30.90]	1.338 [33.97]	.256 [6.51]	.446 [11.32]	.506 [12.86]
-050	1.625 [41.28]	2.004 [50.90]	2.125 [53.98]	.650 [16.51]	.840 [21.32]	.900 [22.86]
-075	2.413 [61.28]	2.792 [70.90]	2.913 [73.98]	1.044 [26.51]	1.233 [31.32]	1.294 [32.86]
*-100	3.200 [81.28]	3.579 [90.91]	3.700 [93.98]	1.438 [36.51]	1.627 [41.33]	1.688 [42.86]
*-125	3.988 [101.28]	4.367 [110.91]	4.488 [113.98]	1.831 [46.51]	2.021 [51.33]	2.081 [52.86]

* = SEE NOTES 11 & 14

• PROPRIETARY NOTE •

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DO NOT SCALE DRAWING

SHEET SCALE: 2:1

DESCRIPTION:
.635mm DOUBLE ROW HS SOCKET ASSEMBLY

DWG. NO.
QSS-XXX-XX-XXX-D-XXX

BY: DEAN P 6/28/1999 SHEET 2 OF 3




TABLE 4		
POS	"C"	"D"
-025	1.217 [30.90]	1.013 [25.72]
-050	2.004 [50.90]	1.800 [45.72]
-075	2.792 [70.90]	2.588 [65.72]
*-100	3.579 [90.91]	3.375 [85.73]
*-125	4.367 [110.91]	4.163 [105.73]

* = SEE NOTES 11 & 14




TABLE 5		
POS	"E"	"F"
-025	1.338 [33.97]	1.118 [28.38]
-050	2.125 [53.98]	1.905 [48.39]
-075	2.913 [73.98]	2.693 [68.39]
*-100	3.700 [93.98]	3.480 [88.39]
*-125	4.488 [113.98]	4.268 [108.39]

* = SEE NOTES 11 & 14

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DO NOT SCALE DRAWING

SHEET SCALE: 2.5:1

DESCRIPTION:
.635mm DOUBLE ROW HS SOCKET ASSEMBLY
DWG. NO. QSS-XXX-XX-XXX-D-XXX
BY: DEAN P 6/28/1999 SHEET 3 OF 3