


TENTATIVE

Light Source for Bar Code Reader

- Lasing Wavelength : $\lambda_p = 650 \text{ nm (typ.)}$
- Optical Output Power : $P_o = 5 \text{ mW}$
- Operation Case Temperature : $T_c = -10 \sim 60^\circ\text{C}$


PIN CONNECTION



1. LASER DIODE CATHODE
2. LASER DIODE ANODE
3. PHOTODIODE CATHODE

Maximum Ratings ($T_c = 25^\circ\text{C}$)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Optical Output Power (CW)	P_o	5	mW
LD Reverse Voltage	$V_R(\text{LD})$	2	V
PD Reverse Voltage	$V_R(\text{PD})$	30	V
Operation Case Temperature	T_c	$-10 \sim 60$	$^\circ\text{C}$
Storage Temperature	T_{stg}	$-40 \sim 85$	$^\circ\text{C}$



Optical-Electrical Characteristics ($T_c = 25^\circ\text{C}$)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Threshold Current	I_{th}	CW Operation	—	30	55	mA
Operation Current	I_{op}	$P_o = 5 \text{ mW}$	—	35	60	mA
Operation Voltage	V_{op}	$P_o = 5 \text{ mW}$	—	2.2	3.0	V
Lasing Wavelength	λ_p	$P_o = 5 \text{ mW}$	640	650	660	nm
Beam Divergence	$\theta_{ }$	$P_o = 5 \text{ mW}$	5	8	12	$^\circ$
	$\theta_{\perp}$	$P_o = 5 \text{ mW}$	24	28	35	$^\circ$
Monitor Current	I_m	$P_o = 5 \text{ mW}$	0.07	0.25	0.5	mA
PD Dark Current	$I_D(\text{PD})$	$V_R = 5 \text{ V}$	—	—	100	nA
PD Total Capacitance	$C_T(\text{PD})$	$V_R = 5 \text{ V}, f = 1 \text{ MHz}$	—	—	20	pF

© The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others. These TOSHIBA products are intended for use in general commercial applications (office equipment, communication equipment, measuring equipment, domestic appliances, etc.) please make sure that you consult with us before you use these TOSHIBA products in equipment which requires extraordinarily high quality and/or reliability, and in equipment which may involve life threatening or critical application, including but not limited to such uses as atomic energy control, airplane or spacecraft instrumentation, traffic signals, medical instrumentation, combustion control, all types of safety devices, etc. TOSHIBA cannot accept and hereby disclaims liability for any damage which may occur in case the TOSHIBA products are used in such equipment or applications without prior consultation with TOSHIBA.

TOLD9442M-1
1997-02-07

TOSHIBA CORPORATION