



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG


REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1891	A	RELEASED	EO	06/27/06	SA	7/25/06	HO	7/25/06



RoHS
Compliant



FEATURES:

Double tuning fork type contact guarantees high reliability
2.54mm pitch
Low-profile mini type Males to 0.64mm sq. posts.

MATERIAL:

Insulator: 30% Glass fiber + P.B.T. (UL 94V-0)
Terminal: Phosphor bronze Finishing Gold-plated

SPECIFICATIONS:

Current Rating: 3 A max
Contact Resistance: 20 Milliohms Max
Insulation Resistance: 100 Megohms Min
Dielectric Withstanding voltage: 650 VAC RMS at sea level.

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

Unless Otherwise
Specified

.X ± 0.2 [0.008]
.XX ± 0.12 [0.005]

DRAWN BY:

EKLAS ODISH

CHECKED BY:

SAMI ALNADI

APPROVED BY:

HISHAM ODISH

DATE:

06/27/06

DATE:

7/25/06

DATE:

7/25/06

DRAWING TITLE:

Mini Jumper, Closed Type, 8 mm

SIZE

A

DWG. NO.

SPC19806

ELECTRONIC FILE

84K8568.DWG

REV

A

SCALE: NTS

U.O.M.: mm [INCHES]

SHEET: 1 OF 1