







LAY-OUT
P.C.B.- HOLE



PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE : 500 V AC (CONT /CONT)

OPERATING TEMPERATURE : -55°C TO 125°C

CONTACT RESISTANCE 20 M Ω MAX

INSERTION FORCE : 0.75N MAX/CONT

EXTRACTION FORCE : 0.15N MIN/CONT

INSULATION RESISTANCE : 10⁴ M Ω MIN

NOTES

1. LEAD FREE INDICATOR :LF=LEAD FREE
PERFORMANCE LEVEL INDICATOR
(REF DWG NO.BSC 201844.003)

2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.

3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :
BSA201572.001

4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND
OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

rev	ecn no	dr	date
A	CONVERSION REVISION 06	KN	14-09-01
B	DG05-0278	Kason	02-08-05
C	DG07-0362	Kason	05-09-07
D	DG08-0159	NZ	06-12-08
E	DG10-0110	NZ	05-30-10

Material			Spec ref					
Mat code				tolerance	projection			
Heat treat				1DEC $\pm$ 0.2 1DEC				
Plating/Finish				2DEC $\pm$ 0.1 2DEC				
				ANGLES $\pm$ 1° HOEKEN				
Dr	W.Panis	10-01-95				size A4	Scale 2.000	
Eng			Product family MILLIPACS					
Chr			Model Name			ECN		
Appr			Model Revision			REL Level		
		title			MPACS 5+2R RA RCP CONN TYPE CR		dwg no BSC201418023	Rev. E
Pro/E file		catalog no			HM2R20PA5100----			
						CUSTOMER DRAWING		sheet 1 of 1