

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0681620960

Status:

Obsolete

Overview:

sherlock

Description:

2.00mm (.079") Pitch Sherlock™ II Wire-to-Board Header, Vertical, with Positive Lock, Lead-free, 9 Circuits

Replacement Part Number:

681620960

Documents:

[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	68162
Application	Signal, Wire-to-Board
Obsolete Date	2004/12/01
Overview	sherlock
Product Name	Sherlock™
Replacement Part Number	681620960

Physical

Breakaway	No
Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-0
Glow-Wire Compliant	No
Material - Resin	Nylon
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Pitch - Mating Interface	2.00mm (.079")
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C


Electrical

Current - Maximum per Contact	2A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-68162-001
Product Specification	PS-35585-002
Sales Drawing	SD-68162-002



Series
image - Reference only

EU RoHS	China RoHS
---------	------------

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

68162Series

Mates With

35585

This document was generated on 02/24/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION