

PRODUCT NUMBER

95000-XXXXLF

PLATING

0 = 0.2µm GOLD/GXT
1 = 0.76µm GOLD/GXT
3 = 0.38µm GOLD/GXT
5 = 0.38µm GXT
6 = 0.76µm GXT
T = FULL MATTE TIN 2µm-5µm

UNDERPLATING 1.27µm Ni MIN






WHEN REQUIRED, ADD SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 6 & 7

PACKAGING TYPE, NOTE 3

TOTAL NB OF POSITIONS, 3 TO 17

NOTES:

- 1 - HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: CREAM
- 2 - PIN MATERIAL : COPPER ALLOY
- 3 - PACKAGING :
= POLY BAGS
T = TUBE, FROM 04 POS UP TO 17 POS
TR = TAPE & REEL
SEE TAB45 FOR PRODUCT AVAILABILITY
- 4 - 7N MIN RETENTION IN EITHER DIRECTION
- 5 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS
- 6 - 95000-XXXXLF IS SIMILAR TO 95000-XXXX, THE SUFFIX "LF" IS ADDED FOR EASY LEAD FREE IDENTIFICATION
- 7 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - MANUFACTURING PROCESS COMPATIBILITY
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 30 SECONDES MAX IN A CONVECTION, INFRA-RED OR VAPOR PHASE OR REFLOW OVEN.
 - b - LABELLING:
- MEETS PACKAGING SPECS AS PER GS-14-920
 - c - THIS PRODUCT MEETS EUROPEAN DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBED IN GS-22-008.
- 8 - HOLE DIMENSION TO BE $\phi 1.60 \pm 0.07$ FOR INTERFERENCE FIT APPLICATIONS
HOLE DIMENSION TO BE $\phi 1.95 \pm 0.07$ FOR NON INTERFERENCE FIT (LOCATIONAL) APPLICATIONS



mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406 ISO 1101		MINITEK		
lfr	ecn no	dr	date	tolerances unless otherwise specified			title		
J	F06-0193	LMU	06.06.105	angles	.X ± 0.3		MINITEK SMT HDR SR POLARIZATION & LATCHING		
K	F07-0179	LMU	07.04.24	linear	.XX ± 0.13				
L	F08-0145	ELA	17.04.08	$\pm 2'$	XXX ± 0.05	scale 7:1	dwg no		
M	F11-0023	JCO	11.02.07	dr	JL CORDIER 97.07.26		sheet 1 of 1		
				engom	COMPAGNON 97.07.26		size		
G	F20554	LMU	02.10.10	chr	JL CORDIER 97.07.26		95000		
H	F05-0128	LMU	05.02.21	appd	JMC 97.07.26		A3		
sheet index		revision sheet				type		CUSTOMER Drawing	