




REV. 0

DCO 141534


COIL: @ 25°C
 RESISTANCE _____ 1560 OHMS ±10%
 NOMINAL VOLTAGE _____ 26.5 VDC
 MUST OPERATE _____ 14.2 VDC
 _____ TURN-ON BASE CURRENT 0.13 mADC
 MUST RELEASE _____ 8.0 VDC MAX, 1.37 VDC MIN.

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
 SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: _____ TURN-ON TIME 2.0 MS MAX
 _____ TURN-OFF TIME 7.5 MS MAX
 _____ CONTACT STABILIZATION TIME 2.0 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: _____ LOW LEVEL TO 1A
 _____ 28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 12/3/99

CK. *[Signature]* 12/3/99



COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. _____ QPL
 CUST. NO. M28776/1-030M REV. _____

JMAT RELAY

JMACT-26XM