







spec ref -				dr		Louis Ng	2010/10/27	projection 	MM 	size	A3	scale	10:1	
tolerance std				eng		Andrew Yong	2011/06/02			ecn no				ELX-S-003356-1
ISO 406 ISO 1101				chr		Aik-Peng Lim	2011/06/03			rel level				Released
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr		Chen-Hong Tan	2011/06/03	product family			MINITEK			
surface 		linear	0.X	±0.25		title	POL. MINITEK VCC WITH LATCHING			dwg no	63440		rev	L
			0.XX	±0.13										
			0.XXX	±0.05										
ISO 1302		angular	0°	±3°	www.fci.com		cat. no.		-	Product - Customer Drw			sheet 1 of 2	



Copyright FCI.

A

B

C

D

PRODUCT NO. NOTE 8	POS.	DIM A	DIM B	DIM C	POL. POS	TERM. DELETED
63440-X01	2 X 16	30.00	32.80	16.40	1,2,31,32	1,2,31,32
63440-X02	2 X 3	4.00	6.80	3.40	3	3
63440-X03	2 X 16	30.00	32.80	16.40	1,31	1,31
63440-X04	2 X 3	4.00	6.80	3.40	3	 3,4
63440-X05	2 X 6	10.00	12.80	6.40	1,2,11,12	1,2,11,12

NOTES:

- HOUSING: PCT BEIGE UL 94V-0
- TERMINAL MATERIAL: PHOS BRONZE.
- SITE CODE TO BE LOCATED AS SHOWN.
- PLATING: Au OVER 1.27µm/50µ" Ni AT CONTACT.
- POLARISED POS REFER TO TABLE. SEE FIG.1 FOR SECTIONAL VIEW.
- TERMINALS TO BE DELETED REFER TO TABLE FOR POS.
- POLARISED AND TERMINAL DELETED IN THE SAME POSITION REFER TO FIGURE2.

- ⑧ PRODUCT DESCRIPTION CODE:
XXXXX-XXXLF
- LEAD FREE (SEE NOTES 9 & 12)
TOTAL POSITIONS
CONTACT AREA PLATING
BASE NUMBER
- ⑨ SOLDERTAIL PLATING:
a) SOLDERTAIL OF P/N:63440-XXX IS TIN/LEAD PLATED.
b) SOLDERTAIL OF P/N:63440-XXXLF IS 100% MATTE TIN PLATED.

- 10 THE HOUSING WILL WITHSTAND EXPOSURE TO 250°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

- 11 THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57MM MINIMUM THICK CIRCUIT BOARD.

- ⑫ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

- 13 A  SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.




FIG.2





FIG.1

spec ref		-		dr	Louis Ng	2010/10/27	projection		MM		size	A3	scale	10:1
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Andrew Yong	2011/06/02					ecn no	ELX-S-003356-1		
				chr	Aik-Peng Lim	2011/06/03								
ISO 406				appr	Chen-Hong Tan	2011/06/03	product family		MINITEK		rel level		Released	
surface		linear	0.X	±0.25		title	POL. MINITEK VCC			dwg no	63440		rev	L
			0.XX	±0.13										
			0.XXX	±0.05										
ISO 1302	angular	0°	±3°	www.fci.com	cat. no.	-	Product - Customer Drw					sheet 2 of 2		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

63440-001